



FM2027-01 Soldering Iron Handpiece Mini Conversion Kit

SKU: HFM2027-01

- Soldering iron in lock-type sleeve assembly
- Mini Conversion Kit Contains Soldering Iron, Sleeve and Heat Proof Mat (Tips NOT included)
- Includes LED status indicator light



Model No.	
Power consumption	70W (24V)
Temperature range	200 to 450°C
Tip to ground resistance	<2Ω
Tip to ground potential	<2mV
Heating element	Composite heater



Model No.	
Cord length	1.2m
Total length	188mm (with 2.4D tip)
Weight	30g (with 2.4D tip)

- Connector Piece (FM2027-02)
- Yellow Sleeve Assembly (B3216)
- Heat Resistant Pad (B2300)

New Tip Shape Concave type

This type has a concave (or V-groove) at the end.

It provides excellent heat supply to solder joint and ensures sufficient solder flow-up.

Concave type