OPTICAL FIBER CLEAVER

FCL200

CI FAVE FIBER THE RIGHT WAY!

FAST

Cleaved Fiber remains in the adapter ready to splice and is compatible with the 910FS, 915FS, and FSP200 models.

ACCURATE

Precision-engineered blades accurately cleave fibers for minimal loss.

RELIABLE

Field tested to perform the dust bin safely collects end cuts.



1390 Aspen Way Vista, CA • 92081 TC-FCL200 11/19

Latin America Phone: 1.760.510.0558 | EMEA Phone: +44 (0) 1633 927 050 @2019 Tempo Communications, Inc. • An ISO 9001 Company

EMEA Address: Tempo Europe Limited • Brecon House, William Brown Close, Cwmbran • NP44 3AB, UK













FCL200

OPTICAL FIBER CLEAVER

FEATURES:

SPECIFICATIONS

- Accurate Cleaves. Cleave multi-mode and single-mode fiber optic cables.
- Long Life. Blades rotate for longer life over 48,000 cleaves.
- Adaptable. Supports 200um, 250um, 900um fibers, ribbon and loose tube fibers.
- Fast. For use with the 910FS, 915FS or FSP200 Optical Fusion Splicers for maximum speed and efficiency with auto return mechanism.
- **Dust bin.** Safely and automatically collects end cuts during the cleaving process.
- **Fixed Clamp.** Allows the technician to use the FCL200 as a standalone cleaver.

Applicable Fibers:	SM (G.652); MM (G.651); DS (G.653); NZDS (G.655); BIF (G.657)
Fiber Cleaved Length:	5mm - 25mm
Cladding Diameter:	125µm
Coating Diameter:	0.20 mm and 0.9 mm
Fiber Count:	Single and Ribbon (12)
Cleaving Angle:	< 1.5°
Blade Life:	48,000 Cleaves
Weight:	0.77lbs (350g)
Dimensions:	2.55 x 3.85 x 2.55" (65 x 98 x 65mm)



FOR USE WITH THE 910FS, 915FS AND FSP200 FUSION SPLICERS

ORDERING INFORMATION:

CAT. NO.	DESCRIPTION
FCL200	FCL200 Optical Fiber Cleaver
01640	Cleaving Wheel
01332	250µm Adapter (Pair)
01333	900µm Adapter (Pair)
05801	Loose Tube Adapter (Pair)
03245	3mm Adapter (Pair)

CAT. NO.	DESCRIPTION
PA1171	ProGrip 5-in-1 Fiber Optic Stripper
PA1177	ProGrip 3-in-1 Fiber Optic Stripper
10997	Economy Fiber Optic Stripper
PA1511	Kevlar Cutter
MSS100	Mid Span Slitter

1390 Aspen Way Vista, CA • 92081 TC-FCL200 04/20

Latin America Phone : 1.760.510.0558 | EMEA Phone: +44 (0) 1633 927 050 @2019 Tempo Communications, Inc. • An ISO 9001 Company

EMEA Address: Tempo Europe Limited • Brecon House, William Brown Close, Cwmbran • NP44 3AB, UK













