


PANEL MOUNT 16 Port Panel



This 19" rack mountable 16 port panel designed for our successful range of PANEL MOUNT type connectors is available with or without cable management bar (FFPM16CM and FFPM16). Perfect for multimedia installations.

Features

- Designed to complement our hugely popular range of Panel Mount connectors: https://tuk.co.uk/tuk_live/product_details.php?category_id=&pld=204
- Robust "U" shaped quality steel construction ensures rigidity
- 19" rack mountable
- Optional removable cable management bar with cable tie slots
- Threaded for M3 screws to facilitate rapid mounting
- Supplied with cage nut set
- Printed with numbered ports

Specifications

- Net weight with primary packaging: FFPM16 364g; FFPM16CM 474g
- Dimensions: FFPM16 300mm x 55mm x 90mm; FFPM16CM 300mm x 55mm x 90mm (in primary packaging)
- Panel Colour: Black matt finish



Packaging: Product supplied in individual carton.

EAN Numbers: FFPM16 - 5055386508805 FFPM16CM - 5055386508812

Commodity code: 85177090 County of origin: China



FFPM16 (front)




FFPM16 (back)





ROHS Compliant Code: FFPM16








Parts included - 4 x M6 cage nut set (nut, bolt, washer) in black



ROHS Compliant Code: FFPM16CM









Parts included - 4 x M6 cage nut set (nut, bolt, washer) in black