

# Han 6M HBM-Rear Fit-SL-w/o frame



Part number	09 37 006 0392
Specification	Han 6M HBM-Rear Fit-SL-w/o frame
HARTING eCatalogue	https://b2b.harting.com/09370060392

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> M
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Rear mounting
Туре	Low construction

#### Version

Locking type	Single locking lever
Size	6 B
Field of application	Hoods/housings for rough environments

#### Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP66
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM



# Material properties

Material (locking)	Stainless steel
--------------------	-----------------

# Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes

### Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors