

Han 10M HBM-Rear Fit-DL-w/o frame



Part number	09 37 010 0392
Specification	Han 10M HBM-Rear Fit-DL-w/o frame
HARTING eCatalogue	https://b2b.harting.com/09370100392

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Rear mounting
Туре	Low construction

Version

Locking type	Double locking lever
Size	10 B
Field of application	Hoods/housings for rough environments

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP66
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM



Material properties

Material (locking) Stainless steel

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors