

# Han TC300 male contact 120mm<sup>2</sup>



Part number	09 11 000 7537
Specification	Han TC300 male contact 120mm²
HARTING eCatalogue	https://b2b.harting.com/09110007537

Image is for illustration purposes only. Please refer to product description.

## Identification

Category	Contacts
Type of contact	Crimp contact

#### Version

Gender	Male
Manufacturing process	Turned contacts

# Technical characteristics

Conductor cross-section	120 mm²
Operating current	≤300 A
Contact resistance	≤0.3 mΩ
Stripping length	22.5 mm
Limiting temperature	-40 +125 °C

# Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated

## Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

#### Commercial data

Packaging size	1	

Product data sheet 09 11 000 7537 Han TC300 male contact 120mm<sup>2</sup>



## Commercial data

Net weight	40 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors