

Han 200A crimp module, female



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 3103
Specification	Han 200A crimp module, female
HARTING eCatalogue	https://b2b.harting.com/09140013103

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® 200 A module

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	1
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	16 ... 70 mm ²
Rated current	200 A
Rated voltage	1,000 V
Rated voltage	1,000 V AC 1,300 V DC
Rated impulse voltage	8 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	EN 50124-1
	EN 60664-1
	IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	20 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440217 Module for industrial connectors (power/signals)