

TECHNICAL DATA SHEET

Part#: 36-SE

Hemostats - 5" 25°Curved - SS

Ideal for clamping parts for inspection

The 36-SE stainless steel locking hemostat with 25°curved serrated jaws is clean room safe. The overall length is 5".

• Precision Level	★★
• Material	SS (AISI 440)
• Surface Resistivity	Conductive
• Shape	Curved
• Tip Size	
• Tip Angle	25°
• Tip Length	
• Body Width	0.262" (6.55mm)
• Body Height	0.155" (3.88mm)
• OAL	5" (125mm)
• Weight (OZ)	2
• UPC	662847003820
• Schedule B	9018.90.80.00
• ECCN	EAR99
• UNSPSC Code	42151685
• Country of Origin	Pakistan
• Group	Curved

