

Home ▶ Products ▶ Accessories ▶ **Adapters and cables**

Fluke BP880 BNC to Female Double Stacking Banana Plug



(0) [Write a review](#)



Buy now

Key features

- Allows for hands-free testing in controlled voltage environments 500 VRMS maximum

- Banana plug is nickel-plated, beryllium copper for low contact resistance
- The BNC shell is plated for tarnish resistance
- Operating temperature +50 °C (+122 °F) maximum

Product overview

Models

Reviews

Resources

Compatible products

Product overview: Fluke BP880 BNC to Female Double Stacking Banana Plug

Converts a BNC scope lead to a dual banana plug for connection to a DMM. Required when adapting a shielded BNC cable, found on high-end low current clamps such as the Fluke 80i-110s, to a DMM.

About Fluke

About us

Careers

Press

Supplier handbook

Contact us

Contact us

Repair

Technical support

Resources

[Promotions](#)

[Manuals](#)

[Product registration](#)

[Safety notices](#)

[Test tools catalog](#)

[Where to buy](#)

[Fluke Newsletters Signup](#)



Fluke. *Keeping your world up and running.®*

[Privacy policy](#)

[Fluke terms of use](#)

[Fluke terms and conditions of sale](#)

[Fluke terms and conditions of service](#)

[Feedback](#)

[Site map](#)

©1995 - 2021 Fluke Corporation