

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2152743605](#)
Status: **Active**
Overview: Temperature Sensor Cable Assemblies
Description: Epoxy Coated NTC Thermistor Cables, 40.00mm Length, 3694 Beta Value, 10k# Resistance at 25°C with 1% Tolerance, Green

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	215274
Application	Temperature Sensing
Assembly Configuration	Single Ended Connector
Beta Value (K)	3694
Connector to Connector	NTC Thermistor-to-Pigtail
Overview	Temperature Sensor Cable Assemblies
Product Name	NTC Temperature Sensor
Resistance Tolerance (%)	1
Resistance at 25°C (kohms)	10
UPC	195842044593


Physical

Cable Length	40.00mm
Circuits (Loaded)	1
Color - Resin	Green
Gender	N/A
Lock to Mating Part	Yes
Net Weight	0.150/g
Packaging Type	Bag
Single Ended	Yes
Wire Size AWG	28
Wire/Cable Type	N/A

Material Info

Reference - Drawing Numbers

Sales Drawing	2152743605-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 15(a)**

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[215274](#) Series