Protective PFA Tubing

Used For Research And Development On Bare Wire Thermocouples, RTDs And Fiber Optics.



30 m (100') Spool

- ✓ Thin Wall Construction
- Extruded PTFE Rated to 260°C (500°F)
- ✓ Color Coded for Easy Identification
- ✓ Non-Flammable

TFE tubing offers superior abrasion protection and is excellent in insulating wires in moist or corrosive environments where temperatures do not exceed 260°C (500°F). All colors and gages are in stock for fast delivery!

Available in
Convenient 25' and 100'
Pre-Spooled Lengths
For Fast Off-the-Shelf
Delivery.

Available! For long, continuous lengths—consult factory for pricing and delivery!





Discount Schedule				
1 to 10 feet	Net			
11 to 24 feet	10%			
25 to 99 feet	20%			
100 to 499 feet	30%			
≥500 feet	35%			



To Order						
Color	20 AWG	24 AWG	26 AWG	28 AWG	30 AWG	
Black	TF-BK-20	TF-BK-24	TF-BK-26	TF-BK-28	TF-BK-30	
Blue	TF-B-20	TF-B-24	TF-B-26	TF-B-28	TF-B-30	
Purple	TF-P-20	TF-P-24	TF-P-26	TF-P-28	TF-P-30	
Red	TF-R-20	TF-R-24	TF-R-26	TF-R-28	TF-R-30	
White	TF-W-20	TF-W-24	TF-W-26	TF-W-28	TF-W-30	
Yellow	TF-Y-20	TF-Y-24	TF-Y-26	TF-Y-28	TF-Y-30	

To order, specify model no. and length. 25 and 100' spools stocked for fast delivery. Other lengths available for additional cost. Minimum order, 10'. Consult sales for delivery. **Ordering Example: TF-R-24-25**, red PFA tubing for 24 gage wire, 25 feet long.

Dimensions: mm (inch)

Emonorous min (mon)							
	Inside Diameter	Wall Dimensions					
AWG Size	(Nominal)	Nominal	Tolerance				
30	0.30 (0.012)	0.23 (0.009)	0.05 (0.002)				
28	0.38 (0.015)	0.23 (0.009)	0.05 (0.002)				
26	0.46 (0.018)	0.23 (0.009)	0.05 (0.002)				
24	0.56 (0.022)	0.25 (0.010)	0.08 (0.003)				
20	0.86 (0.034)	0.38 (0.015)	0.08 (0.003)				