

Plug SEA-3GS-M8-S

Part number: 192009

FESTO



Data sheet

| Feature | Value |
|--|---|
| Type code | SEA |
| Based on norm | EN 61076-2-101 EN 61984 |
| Type of mounting | With threaded sleeve |
| Mounting position | Any |
| Product weight | 11 g |
| Electrical connection | 3-pin M8x1 Straight plug/screw terminal |
| DC operating voltage range | ≤60 V |
| Operating voltage range AC | ≤60 V |
| Current rating at 40°C | 3 A |
| Surge resistance | 1.5 kV |
| Cable fitting | Pg7 |
| Approved cable diameter | 2.5 mm ... 5 mm |
| Connection cross section | 0.14 mm ² ... 0.5 mm ² |
| Degree of protection | IP65 |
| Ambient temperature | -40 °C ... 85 °C |
| CE marking (see declaration of conformity) | As per EU low voltage directive |
| Note on materials | RoHS-compliant |
| Contamination level | 3 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Housing material | PA |
| Housing colour | Black |
| Material of union nut | Brass Chrome-plated Nickel-plated |
| Material of pin contacts | Brass Gold-plated |