

PRODUCT SPECIFICATION

Multiuse Work Light Model: C33

Revision History

Revision	Date	Initiator	Reason for Change
1.0	4 th Jan 2019		First Release

Prepared By	Approved By
Wallace Tso	Wallace Tso
Date: 4 th Jan 2019	Date: 4 th Jan 2019

GPI International Limited

7/F, Building 16W, 16 Science Park West Avenue Hong Kong Science Park, New Territories, Hong Kong, Tel: (852) 2484 3333 Fax: (852) 24805912 Email: gpii@goldpeak.com

Website: http://www.gpbatteries.com

GP Batteries

Product Specifications





Model no.: C33

Product Name : Multiuse Work Light

Lumen output* : Front LED: 150lm / 30lm (+/- 15%)

Side COB: 180lm (+/- 15%)

Beam Distance* : Max 100m (+/- 15%)

Runtime : Front LED

150lm: 2.5 hours / 30lm: 20 hours

Side COB

180lm: 2 hours

Battery type : 2 x AA (Alkaline / NiMH)

LED chip : CREE LED

IP rate* : IPX4

Shock proof* : Impact resistant, 1m

Dimensions : 26 x 163 mm (Include keyring)

Weight : 82.2 g (without batteries), 128 g (with batteries)

Accessories Included : 2 x AA Batteries

Certification : CE, ROHS