

DATA SHEET

NO MERCURY & CADMIUM ADDED				
Description	: Extra Heavy Duty Battery, 3R12			
Chemical System	: Zinc-Manganese dioxide (Zinc Chloride)			
Nominal Voltage	: 4.5 Volts			
Max. Dimensions	: 22.0 mm x 62.0 mm x 67.0 mm			
Terminals	: stainless steel(+) and			
	stainless steel(—)			
Jacket	: Plastic Jacket, ultrasonic welded			
Warranty Period	: 24 months (Storing at -10°C to 25°C and 60±10%RH)			
Weight(Reference)	: 105g			


Cross References:

GP	IEC	JIS	
312G	3R12	3R12	

Estimated Service Life:


U	Discharge Condition		Service Life	
220 Ohms	4 hr/day	2.7V	120 hrs	





At 20 ± 2 °C, RH55 \pm 20% within 30 days of manufacture

Model No.: GP312G



The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors

www.gpbatteries.com

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice. Copyright@ GPI International Ltd. - All rights reserved



Unit: mm