ΕN



6

0

Wiha tools for electricians



Wiha – our goal: your success

- Your guarantee for quality Winner of the Manufacturing Excellence Awards 2014 as the best SME in Germany.
- Reliable and dependable German family-owned company with more than 80 years of experience.
- Your advantage Customised problem-solving for professionals.
- Cutting-edge technology Award-winning innovations valued by professionals throughout the world.

What makes your work easier? Tools that increase your efficiency, reduce costs and preserve your health. This is why Wiha develops, designs and manufactures products that meet the highest functionality, durability and ergonomic demands.

Founded over 80 years ago as a small family-owned business for standard parts and screws, Wiha has grown to become a global company with factories all over Europe, Asia and the United States and are still owner-operated by the Hahn family.

Wiha offers the professional a wide range of high-quality premium tools, characterized by their use of the latest manufacturing technologies, application-oriented innovations, ergonomic superiority, top quality, absolute reliability and long service life. In short, tools that make your work noticeably easier - tools that work for you.

Learn more about Wiha on our website: www.wiha.com

VDE-insulated tools from Wiha

To work safer, more efficiently and with less strain on the body.



Certified safety – from our own safety testing procedure according to IEC standards.

wiha (

Voltage testing: All Wiha VDE-tools, which have special markings, are individually tested at 10,000 V AC and are approved for 1,000 V AC and 1,500 V DC.

Cold shock test: Cooling down to -25° C. The skinning material must retain its toughness, so that it doesn't break when subjected to shock and knocks. **Test of electrical skinning properties:** 24 hours storage in water, then 3 minutes test at 10,000 V AC. There must neither be flashover nor disruptive discharge.

Test of the adhesion of the skinning material coating: 168 hours storage at 70° C, then test of adhesion at 500 N.

Pressure tests: Test at 20 N pressure load, 70° C temperature and 5,000 V AC test voltage. No disruptive discharge may occur.

Test of combustion behaviour: The tools are subjected to a flame for 10 seconds. The skinning material must then extinguish and not continue to burn.

Safety note

-1-

The following equipment is required for all work on or around live components and should be appropriate for the specific task

- insulating personal protective equipment
- insulating safety mechanisms

insulated tools

Before starting work, you must disconnect all active, live components of electrical machines and equipment and ensure that they remain disconnected while you carry out the work.

- This is achieved by complying with the five safety rules:
- disconnect
- ensure power is switched off

- secure against reconnection
- earth and short-circuit
- cover or block off adjacent live components



As an internationally recognized institute, the VDE is responsible for the testing and certification of electrotechnical products. Wiha provides the professional with a broad range of VDE products, developed and continuously optimized specifically for electricians, which also provide applicationoriented solutions for everyday use.

The Wiha quality-management system according to ISO 9001:2015 ensures that only first-class products are manufactured – and that you can work with products of excellent quality. To ensure maximum safety for the user, the entire Wiha VDE range must undergo the most stringent inspections and individual tests. All Wiha VDE-tools hold multiple certifications: The VDE-GSmark stands for safety with regard to any risk, from electrical right up to radiological. Products labelled with a double triangle and a voltage range are suitable for work with live parts.

The international standard IEC 60900 defines the construction, safety as well as single, series, andrandom testing of insulated tools. But with Wiha you don't just work safer, but also healthier and moreefficiently. Specially developed ergonomic geometries ensure comfortable handling that protects body from strain. The result: easier work, less signs of fatigue, more efficiency.



83 professionals. One system.

ElectricVario family by Wiha.




There has never been a team with so many exceptional players: the ElectricVario Family by Wiha unites all fastening tools that electricians need for all the challenges in their job. These include many new members to complete the team. The best thing about them: Thanks to the countless combination possibilities, the tools can be used flexibly and thus save valuable time and space. Combinable with one another, the tools also ensure safe screw-fastening on live parts thanks to their insulation. The ergonomically shaped screwdriver handles also help to protect the user's muscles. Professional users play in the Premier League when they use ElectricVario Family products. They can always be identified via the ElectricVario Family logo.


- Increases your efficiency Various usage options for all fastening procedures and application fields.
- Offers you full protection Internationally award-winning VDE-insulated tools, each individually tested at 10,000 V AC and approved for use at 1,000 V AC.

• Increases your safety

Wiha slimBits ensure unrestricted and fully insulated access to low-lying screws.



Content





Bit set for mountin Page 23	g Ratchet w 1/2" Page 24		Single open-end spanner set, insulated 6-32 mm Page 25	Range of Applications From page 10
Screwdriver with I magnetic bit maga Page 68	LiftUp 25 Izine Screwdri magnetic Page 80		L-key set in ErgoStar holder Page 96	Fastening / jamming From page 26
	riha 🕤 👘 wiha 🖛			
Schraubendreher n Magazin LiftUp 25 Page 80		⁰ TY bit set, 29 mm		
Precision mechanic cutters Classic Page 109	Shear for Page 109		Hacksaw electric Page 109	Trimming / cutting From page 96
37		B		
Long flat-nose plie Professional electr Page 113	rs Pliers wre ic Page 114		Classic circlip pliers with MagicTips®, straight Page 119	Supplying / holding From page 106
		atte		
Automatic crimp to Page 127	ol Stripping 4-pcs. Page 132		Wire end sleeves with plastic collar set Page 136	Stripping/ insulating / crimping From page 116
anda - Co		7		
Electrician's Longl ruler, 2 m Page 152	fe[®] folding Electricia Page 152	n's spirit level		Surveying / marking / measuring / checking
Ling wiha⊜ f	THE REAL PROPERTY AND ADDRESS OF THE PARTY			From page 126
				Striking / chiselling From page 134
				From page 134
				From page 154

Stripping/ insulating / crimping

Surveying / marking / measuring / checking

Increases your efficiency

A wide range of tools – so the right one is always to hand when you need it.

at work for you

Protect your health

The patented and multiple award-winning Wiha SoftFinish® handle size concept prevents occupational illnesses as work is kind to hands and muscles. Recommended by German doctors and therapists from the AGR! (Healthy back association)

Offers you full protection

Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Increases your safety

Wiha slim tools ensure full and fully-insulated access to low-lying screws.



The range. Cases that really deliver.

The professional often has reservations about conventional tool boxes: too inaccessible, little storage space, not robust enough. Deficiencies that Wiha has taken to heart – and eliminated –in the development of its case sets.

Wiha cases therefore combine many good qualities: Stable inline rollers allow easy and stress-free transportation of tools. The durable PP-plastic with reinforced plastic elements ensures a longlifespan. Gas-filled shock absorbers hold the cover in all positions and reduce the risk of injury when closing. Tool trays ensure quick and easy access to the tool, the case itself provides a lot of extra storage space for small items and machines. And, last but not least, you can easily access the right tool, whenever it is needed.

"A case with all major Wiha tools and innovations - like Christmas for the electrician!" Rolf Muschal





Whether next door or at the most remote site: It's greatif the tool you need is quickly at hand. Compact, handyand robust, the Wiha toolbox set ensures access tothe tools you require, at any time and in any situation. Specially compiled according to varying requirementsand applications, the Wiha toolbox sets have one thingin common: All include high-quality tools in provenWiha quality, guaranteeing easy and efficient working. Ergonomic in design, durable in material and processing, and safe thanks to rigorous and extensive safety test procedures, Wiha tools prove to be a practical and indispensable companion for the electrician, especially in their toolbox set.

- Increases your efficiency
 A wide range of tools so the right one is always
 to hand when you need it.
- Meets your requirements Robuust, groot, duurzaam en veilig met dekseluithouder
- Lowers your costs The correct torque avoids damaging material and no follow-up work is necessary.

• Offers you full protection

Internationally award-winning VDE-insulated tools, each individually tested at 10,000 V AC and approved for use at 1,000 V AC.







Meets your requirements: Case: robust, large, stable and secure with lid brake. **Lowers your costs:** The correct torque protects material from damage and ensures no additional follow-up work. **Increases your safety:** Internationally award-winning VDE-insulated tools, each individually tested at 10,000 V AC and approved for use at 1,000 V AC. Gas-filled shock absorbers hold the lid in all positions and reduce the risk of injury when closing. **Protect your health:** Wiha pliers require less force and reduce pressure on wrists. Ergonomic handle design makes work easier and prevents occupational illnesses. Trolley with stable in-line rollers allow easy and stress-free transportation of tools to the work area. **Increases your efficiency:** A comprehensive tool assortment, always providing you with the right tool when it is needed. The design and function of the tool trays guarantee quick and easy access to tools. **Increases your flexibility:** Ample space for additional tools and lots of storage for small parts and machines.



assorted in case 115-pcs.

9500-704

	9500-70
Order-No.	
12069	1
Fastening	/ jamming
⊖ \$ \$ \$ \$	Torque screwdriver set TorqueVario®-S electric (36791) 0,8-5,0 Nm 1 x Torque screwdriver TorqueVario®-S electric Variable torque limit settings, VDE and GS tested / 1 x Adjusting tool for torque screwdriver with long handle / 1 x Adapter TorqueVario-S electric for slimBits 1 x 2,5 / 1 x 3,5 / 1 x 5,5 / 1 x 6,5 / 1 x PH1 / 1 x PH2 / 1 x PZ1 / 1 x PZ2 / 1 x SL/PZ1 / 1 x SL/PZ2 / 1 x T9 / 1 x T10 / 1 x T15 / 1 x T20 / 1 x T25
∋***	Screwdriver with bit magazine LiftUp electric (41234) 1 x 2,5 / 1 x 3,5 / 1 x 5,5 / 1 x PZ1 / 1 x PZ2 / 1 x SL/PZ2
0	Screwdriver with bit holder SoftFinish® electric slimVario Stubby für slimBits, VDE and GS tested (41229)
₽	PZ2 x 75
Э	Screwdriver SoftFinish® electric slimFix Slotted, VDE and GS tested / 3,5 x 100 (35446) / 5,5 x 125 (35391) / 6,5 x 150 (35392)
Ð	Screwdriver SoftFinish® electric slimFix Phillips, VDE and GS tested / PH1 x 80 (35393) / PH2 x 100 (35394)
₽	Screwdriver SoftFinish® electric slimFix Pozidriv, VDE and GS tested / PZ1 x 80 (35395) / PZ2 x 100 (35396)
₽	Screwdriver SoftFinish® electric slimFix PlusMinus/Pozidriv, VDE and GS tested / SL/PZ1 x 80 (36329) / SL/PZ2 x 100 (36330)
۲	Screwdriver SoftFinish® electric slimFix TORX® Tamper Resistant (with hole), VDE and GS tested / T10H x 100 (41141) / T15H x 100 (41142) / T20H x 100 (41143) / T25H x 125 (41144)
C	Screwdriver SoftFinish® electric Hex nut driver, VDE and GS tested / 5,5 x 125 (00856) / 7 x 125 (00858) / 8 x 125 (00859) / 10 x 125 (00861) / 13 x 125 (00864)
Ð	Fine screwdriver PicoFinish electric Phillips, VDE and GS tested / PH0 x 60 (38880)
Ð	Fine screwdriver PicoFinish electric Schlitz, VDE and GS tested / 2,5 x 60 (38876)
∋⊕ ०० 0	Switch cabinet key pen shape 1/4" in blister pack 5-8 x 9 (39076)
Ð	Screwdriver SoftFinish® Slotted with one-piece hexagonal blade and solid steel cap 3,5 x 75 (03223) / 12,0 x 200 (03231)
₽ € \$	XLSelector Y bit set, 25 mm (41832) 1 x PH1/4 x PH2/1 x PH3/2 x PZ1/4 x PZ2/2 x PZ3/2 x T10/3 x T15/3 x T20/3 x T25/3 T30/2 x T40/1 x Bit holder magnetic extra strong magnet, 1/4"
•	L-key set in ErgoStar holder (41979) 1,5 / 2 / 2,5 / 3 / 4 / 5 / 6 / 8 / 10
Γrimming	/ cutting
<u> </u>	Professional BiCut® high-performance diagonal cutters with DynamicJoint® Switchable, VDE and GS tested 200mm, 8" (38191)
<u> </u>	Professional electric diagonal cutters with DynamicJoint® 160 x 6 1/2" (43335)
	Cable cutter Professional electric, VDE and GS tested / 200mm, 8" (34744)
·	Precision mechanic's diagonal cutters Classic with opening spring 125mm, 5" (36189)
Supplying	/ holding
	Combination pliers Professional electric with DynamicJoint® and OptiGrip with extra long cutting edge, VDE and GS tested / 180 mm, 7" (26708)
	Needle nose pliers Professional electric with cutting edge curved shape, approx. 40°, VDE and GS tested / 200mm, 8" (26729)
•	Needle nose pliers Professional electric with cutting edge straight shape, VDE and GS tested / 200 mm, 8" (26727)
	Water pump pliers Professional electric with push button adjustment, VDE and GS tested / 250mm, 10" (37450)
Stripping/	insulating / crimping
	Installation pliers TriCut Professional electric 170mm, 7" (38552)
	Stripping tool with self-rotating trailing blade 165mm, 61/2" (35969)
	Stripping tool automatic up to 16 mm ² in blister pack 200mm, 8" (42062)
•	Automatic crimp tool for wire-end sleeves hex crimping 210mm, 0,08-16mm ² (41246)
•	Crimp tool for insulated terminals and connectors 220mm, 0,5-6mm ² (33841)
	Shear for electricians with crimp function in blister pack 160mm, 50mm ² (41923)
Surveying	/marking/measuring/checking
	Single-pole, non-contact volt detector, 90–1,000 VAC Includes two AAA batteries (43798)
	Flashlight with LED, laser and UV light in blister pack, including 3 AAA batteries 100 / 310 lm x 390 - 400 nm (41286)
	Electrician's spirit level 40 cm (42074)
	Electrician's Longlife® folding ruler, 2 m metric, 10 segments (42068)
€	SoftFinish® dowel racket set with dowels (41289) 1 x Dowel racket / 2 x 30 mm Dowel / 2 x 40 mm Dowel
Striking /	chiselling
	Electrician's hammer with 300 g hammer head, in blister pack 23,9 x 283 (42071)





Meets your requirements: Case: robust, large, stable and secure with lid brake. **Lowers your costs:** The right tool protects you from damaging materials and avoids subsequent work. **Increases your safety:** Internationally award-winning VDE-insulated tools, each individually tested at 10,000 V AC and approved for use at 1,000 V AC. Gas-filled shock absorbers hold the lid in all positions and reduce the risk of injury when closing. **Protect your health:** Wiha pliers require less force and reduce pressure on wrists. Ergonomic handle design makes work easier and prevents occupational illnesses. Carry belt enables the simple transport of the tool case and keeps hands free for other materials. **Increases your efficiency:** A comprehensive tool assortment, always having the right tool at hand when needed. The design and function of the tool trays guarantee quick and easy access to tools. **Increases your flexibility:** Ample space for additional tools and lots of storage for small parts and machines.



ssorted 80-pcs, in case

<u> </u>	9300 9300
Order-No.	
40523	1
Fastenin	g / jamming
0	Screwdriver SoftFinish® electric Hex nut driver, VDE and GS tested / 5,5 x 125 (00856) / 7 x 125 (00858) / 8 x 125 (00859) / 10 x 125 (00861
\ominus	Screwdriver SoftFinish® electric slimFix Slotted, VDE and GS tested / 3,5 x 100 (35446) / 4,0 x 100 (35390) / 5,5 x 125 (35391) / 6,5 x 150 (35392)
Ð	Screwdriver SoftFinish® electric slimFix electric PlusMinus/Phillips, VDE and GS tested / SL/PH1 x 80 (35502) / SL/PH2 x 100 (35503)
*	Screwdriver SoftFinish® electric slimFix PlusMinus/Pozidriv, VDE and GS tested / SL/PZ1 x 80 (36329) / SL/PZ2 x 100 (36330)
Ð	Screwdriver SoftFinish® electric slimFix Phillips, VDE and GS tested / PH1 x 80 (35393) / PH2 x 100 (35394)
*	Screwdriver SoftFinish® electric slimFix Pozidriv, VDE and GS tested / PZ1 x 80 (35395) / PZ2 x 100 (35396)
\ominus	Screwdriver SoftFinish® Slotted with one-piece hexagonal blade and solid steel cap 12,0 x 200 (03231)
⊖⊕००(D Switch cabinet key cross shape (36114)
⊖⊕⊛	Screwdriver with bit magazine LiftUp electric (38611) 1 x 3,0 / 1 x 4,0 / 1 x 5,5 / 1 x PH1 / 1 x PH2 / 1 x SL/PZ2
•	L-key set in Compact holder (01418) 1,5 / 2 / 2,5 / 3 / 4 / 5 / 6 / 8 / 10
⊖⊕⊛⊛	Bit set XLSelector Standard 25 mm (29417) 1 x 4,5 / 1 x 5,5 / 1 x 6,5 / 2 x PH1 / 4 x PH2 / 1 x PH3 / 2 x PZ1 / 5 x PZ2 / 1 x PZ3 / 2 x T10 / 2 x T15 / 2 x T20 / 3 x T25 / 2 x T30 1 x T40 / 1 x Bit holder magnetic, 58 mm 1/4"
Trimming	g / cutting
X	Professional BiCut® high-performance diagonal cutters with DynamicJoint® Switchable, VDE and GS tested / 200mm, 8" (38191)
X	Professional electric diagonal cutters with DynamicJoint [®] 180 x 7" (43340)
Κ	Precision mechanic's diagonal cutters Classic with opening spring 125mm, 5" (36189)
Supplyin	g / holding
	Combination pliers Professional electric with DynamicJoint® and OptiGrip with extra long cutting edge, VDE and GS tested / 180 mm, 7" (267
•	Needle nose pliers Professional electric with cutting edge curved shape, approx. 40°, VDE and GS tested / 200mm, 8" (26729)
•	Needle nose pliers Professional electric with cutting edge straight shape, VDE and GS tested / 200 mm, 8" (26727)
	Water pump pliers Professional electric with push button adjustment, VDE and GS tested / 250mm, 10" (37450)
Stripping	/ insulating / crimping
X	Installation pliers TriCut Professional electric 170mm, 7" (38552)
	Stripping tool automatic up to 6 mm ² in blister pack 190mm, 7 ½" (36050)
	Stripping tool with self-rotating trailing blade 165mm, 61/2" (35969)
•	Crimp tool for wire-end sleeves 220mm, 0,14-16mm ² (33844)
Surveyin	g/marking/measuring/checking
	Single-pole, non-contact volt detector, 90–1,000 VAC Includes two AAA batteries (43798)
	Folding ruler Longlife 2 m metric, 10 segments (27057)
	Switch cabinet spirit level 20 cm (36859)





Meets your requirements: Carefully selected tool ranges for the most common applications. **Increases your safety:** Wiha slim blades ensure unlimited, protected access to deep-set screws. Internationally award-winning VDE-insulated tools, each individually tested at 10,000 V AC and approved for use at 1,000 V AC. **Increases your efficiency:** Compact and space-saving tool range.

45501	ted 29-pcs. in bag	9300-0
Order-I	No.	(1)
43879		1
Faster	ning / jamming	
θ	Screwdriver SoftFinish® electric slimFix Slotted, VDE and GS tested / 3,5 x 100 (35446) / 5,5 x 125 (35391)	
Ð	Screwdriver SoftFinish® electric slimFix Phillips, VDE and GS tested / PH1 x 80 (35393) / PH2 x 100 (35394)	
\$	Screwdriver SoftFinish® electric slimFix Pozidriv, VDE and GS tested / PZ1 x 80 (35395) / PZ2 x 100 (35396)	
θ	PicoFinish® fine screwdriver Slotted 1,5 x 40 (42384) / 2,0 x 40 (42388) / 2,5 x 50 (42391) / 3,0 x 50 (42394)	
Ð	PicoFinish® fine screwdriver Phillips PH00 x 40 (42402) / PH0 x 50 (42401)	
⊖⊕०	• • Switch cabinet key cross shape (36114)	
۲	L-key set in Compact holder (01418) 1,5 / 2 / 2,5 / 3 / 4 / 5 / 6 / 8 / 10	
Trimm	ning / cutting	
ζ	Diagonal cutters Electronic wide, pointed head without bevelled edge 130mm, 5 1/2" (26818)	
X	Professional electric diagonal cutters with DynamicJoint® 160 x 6 1/2" (43335)	
Suppl	ying / holding	
•	Needle nose pliers Professional electric with cutting edge straight shape, VDE and GS tested / 200 mm, 8" (26727)	
	Needle nose pliers Electronic narrow, short head straight form 150mm, 6" (26801)	
Stripp	ing/ insulating / crimping	
	Stripping tool with self-rotating trailing blade 165mm, 61/2" (35969)	
	Stripping tool automatic up to 6 mm ² in blister pack 190mm, 7 1/2" (36050)	
Surve	ying/marking/measuring/checking	
	Single-pole, non-contact volt detector, 90–1,000 VAC Includes two AAA batteries (43798)	





19

Tool set slimVario[®] electric





/ARIO FAM

Functional bag

Simplifies your work: All tools securely arranged in a robust, orderly bag. Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. Increases your efficiency: Space saved thanks to extensive interchangeable bit system and nut driver inserts. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. Protects your material: Fully insulated nut driver reduces the risk of short circuits.

Simplifies your work: Robust, orderly bag offers a great deal of space
to store Wiha tools. Increases your efficiency: Opened bag acts as a
workbench stand to remove tools easily.

mixed, 3	31-pcs. in functional bag	7209N
Order-No	o. 🔛	
43465	1	
\ominus	2,0 x 75 / 3,5 x 75 / 5,5 x 75 / 6,5 x 75	
Ð	PH0 x 75 / PH1 x 75 / PH2 x 75	
۲	SL/PZ1 x 75 / SL/PZ2 x 75	
*	PZ1 x 75 / PZ2 x 75	
0	5 x 42 / 5,5 x 42 / 6 x 42 / 7 x 42 / 8 x 42 / 10 x 11 x 42 / 13 x 42	42 /
	3 x 75 / 4 x 75 / 5 x 75	
۲	T10 x 75 / T15 x 75 / T20 x 75 / T25 x 75	
	slimVario® electric adapter for 1/4" nut driver	
	Extension slimVario® electric for slimBits	
Manufactur	Screwdriver with bit holder SoftFinish® slimVario® electri screwdriver PicoFinish® slimVario® electric / Screwdrive holder SoftFinish® electric slimVario red acc. to IEC 60900.	

Empty 7209E Order-No. 43474 1 Functional bag Empty

nplifies your work: Robust, orderly bag offers a great deal of spaces store Wiha tools. Increases your efficiency: Opened bag acts as rkbench stand to remove tools easily.

Tool set electrician





Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. Increases your efficiency: Compact and space-saving tool range. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Screwdriver, diagonal cutters, 6-pcs. in tool pouch

pouon	9300-018
Order-No.	
33969	1
Fastening	g / jamming
\ominus	Screwdriver SoftFinish® electric Slotted, VDE and GS tested $/$ 3,5 x 100 (00822) / 4,5 x 125 (00824) / 5,5 x 125 (00826)
Ð	Screwdriver SoftFinish® electric Phillips, VDE and GS tested $/$ PH1 x 80 (00847) $/$ PH2 x 100 (00848)
Trimming	/ cutting
X	Professional electric diagonal cutters with DynamicJoint $^{\odot}$ 160 x 6 1/2" (43335)



Increases your efficiency: Compact and space-saving tool range. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Screwdriver, needle nose pliers, diagonal cutters, 5-pcs. in tool pouch

	Z99 0 002 06
Order-N	o. 🔛
26755	1
Fasteni	ing / jamming
θ	Screwdriver SoftFinish® electric Slotted, VDE and GS tested $/$ 3,5 x 100 (00822) / 5,5 x 125 (00826)
Ð	Screwdriver SoftFinish® electric Phillips, VDE and GS tested $/$ PH2 x 100 (00848)
Supplyi	ing / holding
•	Needle nose pliers Professional electric with cutting edge straight shape, VDE and GS tested / 200 mm, 8" (26727)
Trimmi	ng / cutting
X	Professional electric diagonal cutters with DynamicJoint [®] 160 x 6 1/2" (43335)



Tool set electrician

Tool set electrician



Meets your requirements: Carefully selected tool ranges for the most common applications. **Increases your safety:** Internationally award-winning VDE-insulated tools, each individually tested at 10,000 V AC and approved for use at 1,000 V AC. **Protect your health:** With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. **Increases your efficiency:** Compact and space-saving tool range.

		9300-02
Order-No	Э.	
36389		1
Fasteni	ng / jamming	
ə	Screwdriver SoftFinish [®] electric slimFix Slotted, VE tested / 3,5 x 100 (35446) / 4,5 x 125 (35501) / (35391)	
#	Screwdriver SoftFinish® electric slimFix Pozidriv, V tested / PZ1 x 80 (35395) / PZ2 x 100 (35396)	DE and GS
Trimmir	ng / cutting	
5	Cable cutter Professional electric with switchable VDE and GS tested / 210mm, 8 ¼" (43662)	opening spring
Supplyi	ng / holding	
•	Needle nose pliers Professional electric with cuttin shape, VDE and GS tested / 200 mm, 8" (2672)	0 0 0
Trimmir	ng / cutting	
X	Heavy-duty diagonal cutters Professional electric wit DynamicJoint [®] with switchable opening spring 180n	
Strippin	ng/ insulating / crimping	
	Stripping tool automatic up to 6 mm ² in blister pace 1/2" (36050)	ck 190mm, 7
	Stripping tool with self-rotating trailing blade 165m (35969)	1m, 6½"
Surveyi	ng/marking/measuring/checking	
	Folding ruler Longlife 2 m metric, 10 segments (27	7057)
Trimmir	ng / cutting	
5	Cable cutter Professional electric, VDE and GS tes 200mm, 8" (34744)	sted /



Increases your safety: Wiha slim blades ensure unlimited, protected access to deep-set screws. **Protect your health:** With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. **Increases your efficiency:** Compact and spacesaving tool range. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Screwdriver, heavy-duty diagonal cutters, 7-pcs. in tool pouch

in toor p	9300-031
Order-No). 🖬
38020	1
Fastenir	ng / jamming
θ	Screwdriver SoftFinish® electric slimFix Slotted, VDE and GS tested / 3,5 x 100 (35446) / 4,0 x 100 (35390) / 5,5 x 125 (35391)
Ð	Screwdriver SoftFinish [®] electric slimFix Phillips, VDE and GS tested / PH2 x 100 (35394)
*	Screwdriver SoftFinish® electric slimFix Pozidriv, VDE and GS tested / PZ2 x 100 (35396)
*	Screwdriver SoftFinish® electric slimFix PlusMinus/Pozidriv, VDE and GS tested / SL/PZ2 x 100 (36330)
Trimmin	ng / cutting
X	Heavy-duty diagonal cutters Professional electric with DynamicJoint [®] with switchable opening spring 160mm, 6,5" (40921)







Simplifies your work: Free hands and no damage to work trousers thanks to pouch attached to belt. Increases your safety: Wiha slim blades ensure unlimited, protected access to deep-set screws. Internationally award-winning VDE-insulated tools, each individually tested at 10,000 V AC and approved for use at 1,000 V AC. Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. Increases your efficiency: All main tools quickly accessible, always at hand.

assorted slotted, Phillips, 10-pcs. in belt pouch

assorted	d slotted, Phillips, 10-pcs. in belt pouch	9300-012-01
Order-No	. (
40948		1
Fastenir	ng / jamming	
θ	Screwdriver SoftFinish® electric slimFix Slotted, V tested / 3,5 x 100 (35446) / 4,0 x 100 (35390) / (35391)	
Ð	Screwdriver SoftFinish® electric slimFix Phillips, V tested / PH1 x 80 (35393) / PH2 x 100 (35394)	DE and GS
Strippin	g/ insulating / crimping	
	Stripping pliers Professional electric 160mm, 6 1/2	" (26847)
	Stripping tool with self-rotating trailing blade 165r (35969)	nm, 6½"
Supplyir	ng / holding	
•	Needle nose pliers Professional electric with cutti shape, VDE and GS tested / 200 mm, 8" (2672	0 0 0
Surveyir	ng/marking/measuring/checking	
	Measuring tape 5 m (33251)	



Simplifies your work: Free hands and no damage to work trousers thanks to pouch attached to belt. Increases your safety: Wiha slim blades ensure unlimited, protected access to deep-set screws. Internationally award-winning VDE-insulated tools, each individually tested at 10,000 V AC and approved for use at 1,000 V AC. Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. Increases your efficiency: All main tools quickly accessible, always at hand.

assorted	slotted, Pozidriv, 10-pcs. in belt pouch	9300-013-02
Order-No.	(.)
40282	-	1
Fastenin	g / jamming	
θ	Screwdriver SoftFinish® electric slimFix Slotted, V tested / 3,5 x 100 (35446) / 4,0 x 100 (35390) / (35391)	
*	Screwdriver SoftFinish® electric slimFix Pozidriv, V tested / PZ1 x 80 (35395) / PZ2 x 100 (35396)	/DE and GS
Stripping	/ insulating / crimping	
۵	Stripping pliers Professional electric 160mm, 6 1/2	" (26847)
	Stripping tool with self-rotating trailing blade 165r (35969)	nm, 6½"
Supplyin	g / holding	
•	Needle nose pliers Professional electric with cuttin shape, VDE and GS tested / 200 mm, 8" (2672	3 - 3 3
Surveyin	g/marking/measuring/checking	
	Measuring tape 5 m (33251)	





Simplifies your work: Utmost accessibility thanks to long, 70 mm bits. Also ideal for machine operation. Makes handling easier: Variably adjustable blade length depending on application. Increases your efficiency: All common blades in one compact set.

19-pcs. ir	n roll-up bag	79187 T04
Order-No.		
41223	1	
۲	1 x T15 / 1 x T20 / 1 x T25 / 1 x T30 / 1 x T40	
Ð	1 x PH0 / 1 x PH1 / 1 x PH2	
*	1 x SL/PZ1 / 1 x SL/PZ2	
\ominus	1 x 3,5 / 1 x 4,0 / 1 x 5,5	
۲	1 x 4,0 / 1 x 5,0 / 1 x 6,0	
0	1 x Bit holder magnetic, 74 mm 1/4"	
0	1 x Screwdriver handle SoftFinish®-telescopic for SYS® interchangeable blade	TEM 6
0	1 x Bit holder SYSTEM 6 clamping with ball	

Ratchet wrench set insulated 3/8"

Ratchet wrench set insulated 1/2"







Increases your efficiency: Various usage options for all fastening procedures and application fields. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. **Increases your flexibility:** Adjustable right or left rotation through switching lever. **Protects your material:** Fully insulated tool reduces the risk of short circuits.

20-pcs. ir	1 case	7207NK2001
Order-No.	í)
43023	-	I
	T-handle insulated for nut driver (43062)	
	Ratchet wrench insulated for nut drivers Switchat (43052)	ole 3/8" x 200
0	Insulated extension 3/8" square adapter for nut di insulated 3/8" x 125 (43057) / 3/8" x 250 (43058)	river inserts,
0	Insulated nut driver insert 3/8" hexagon head 8 / 10 / 11 / 12 / 13 / 14 / 16 / 17 / 18 / 19 / 21 /	22
٠	Insulated nut driver insert 3/8" internal hexagon 4 5 x 75 (43106) / 6 x 75 (43107) / 8 x 75 (43108)	x 75 (43105) /
Manufactured	according to EN/IEC 60900.	

Increases your efficiency: Various usage options for all fastening procedures and application fields. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. **Increases your flexibility:** Adjustable right or left rotation through switching lever. **Protects your material:** Fully insulated tool reduces the risk of short circuits.

20-pcs. ii	n case 7208NK20	01
Order-No.		
43024	1	
	T-handle insulated for nut driver (43063)	
	Ratchet wrench insulated for nut drivers Switchable 1/2" x 250 (43053)	
0	Insulated extension 1/2" square adapter for nut driver inserts, insulated 1/2" x 250 (43056) / 1/2" x 125 (43055)	
0	Insulated nut driver insert 1/2" hexagon head 10 / 11 / 12 / 13 / 14 / 17 / 19 / 22 / 24 / 27 / 32	
۲	Insulated nut driver insert 1/2" internal hexagon 4 x 120 (43100 / 5 x 120 (43101) / 6 x 120 (43102) / 8 x 120 (43103) / 10 x 120 (43104)	'

Manufactured according to EN/IEC 60900.







Increases your efficiency: Improved accessibility to restricted spaces thanks to 15° jaw positioning. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. **Protects your material:** Fully insulated tool reduces the risk of short circuits.

20-pcs. in case	
Order-No.	
43022	1
0	Single, insulated open-end spanner 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13 / 14 / 15 / 16 / 17 / 18 / 19 / 22 / 24 / 27 / 30 / 32
0	Adjustable spanner electric Adjustable between 0-30 mm 0 - 30 x 250 (43061)
Manufactured	according to EN/IEC 60900.

Increases your efficiency

Wiha screwdrivers offer an optimal balance between power and control thanks to their unique handle size concept.

Saves money

1111

TIM

By using the correct torque value, torque tools protect against material damage and reworking.

Protect your health

The patented and multiple award-winning Wiha SoftFinish® handle size concept prevents occupational illnesses as work is kind to hands and muscles. Recommended by German doctors and therapists from the AGR! (Healthy back association)

Offers you full protection

Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Increases your safety

Wiha slim tools ensure full and fully-insulated access to lowlying screws.

Fastening / jamming

We have the know-how at the tip of our fingers.

The ergonomic quality of a tool is never quite so apparent as when fastening and clamping. Underthe motto "A grasp on turning" Wiha presents an innovative handle size concept which breaks newground in terms of individual user comfort.

Many commonly available screwdrivers are not designed to meet the needs of users. This results in disadvantages in guiding the tool as well as in transmitting force while fastening. In contrast, the-Wiha SoftFinish[®] concept works with four different handle sizes: Thus, each handle has a perfectlycorrelated ratio of guidance, speed and torque for any task.

The Wiha slimTECHNOLOGY offers additional comfort, permitting unrestricted access to eachscrew with 33 % slimmer blades.


The speedE[®] II e-screwdriver proves itself to be the ideal tool for virtually every screw-fastening task. Whether handling delicate fastenings, long screws or an extremely large number of screws, professionals can do their job faster while working with the e-screwdriver.

"The speedE[®] II is my most trusted partner in my daily work. Especially at the end of a long workday, it not only saves energy but also time, as I can work significantly faster with it. In addition, it has two power transmission levels* and due to the different colours of the bits, I immediately know which one to use without damaging the material. Thanks to the speedE[®] II, working error-free and gently is no longer the exception but the rule." Simon Furrer, WorldSkills 2017 World

Champion in Abu Dhabi, Industrial Control Category



Fast has never been this unique.



- Increases your speed Work completed 3 times as fast thanks to the electric drive.
- Protect your health Gentle on hands and muscles. Recommended by doctors and therapists at the German Campaign for Healthier Backs!
- Offers you full protection slimBits tested at 10,000 V AC and approved for 1,000 V AC.
- Protects your material Electric screw fastening with protective function to prevent damage to materials.

NEW MORE POWER



Several fastenings per day, hundreds of fastenings per week. Professional craftspeople invest a great amount of time and energy in recurring fastening tasks. The resulting pain in wrists is the body's natural reaction. Thanks to the electric drive of the e-screwdriver speedE[®] II, joints and tendons are protected, especially during continuous use. In addition, the required time is reduced to one-third. An extra highlight of the speedE[®] II is the integrated material function. Sensitive fastenings, for example, plastic socket covers, must not be tightened too hard or the material will be damaged. In such cases, the speedE II automatically switches off at 0.4 Nm and gives the user full control to carefully carry out the final fastening by hand. If there are fastening tasks that require more force, the second generation speedE® offers the option of increasing the electric force to 1.0 Nm via a sliding switch. The colour of the slimBits serves as an aid for adjusting the correct force level to the respective application. The red slimBits with the smaller profiles are used in the red slide position, while the yellow Power SlimBits with the larger profiles indicate that in this case, the more powerful yellow slide position can be used. However, if more force is required, the speedE[®] can be manually used up to 12 Nm without incurring any damage. During the fastening, the integrated LED light provides permanent illumination for an optimal view of the

screw. This way, in poorly lit work environments the powerful LED can be used as a flashlight by tapping on the ring switch. The enlarged ring switch and smooth rotation ensure even easier handling. Thanks to the combination of facilitated handling and the ergonomic SoftFinish® handle design, the e-screwdriver speedE® II is recommended by doctors and therapists from the German Campaign for Healthier Backs. The set contains both a red and yellow slimBit, a USB battery charger, as well as two standard 18500 batteries, which ensures continuous working.



E-screwdriver, speedE[®] II electric







Meets your requirements: Quality and robustness made in Germany. Simplifies your work: Maximum illumination of the working area thanks to the LED ring light. Makes handling easier: Unique ring switch allows operation in all working positions. Protect your health: Gentle on hands and muscles. Recommended by doctors and therapists at the German Campaign for Healthier Backs! Increases your efficiency: 100% compatible with the Wiha Electric Vario family. Offers you full protection: slimBits tested at 10,000 V AC and approved for 1,000 V AC. Increases your speed: Work completed 3 times as fast thanks to the electric drive. Protects your material: Electric screw fastening with protective function to prevent damage to materials.

7 pcs with slimBits, batteries and USB charger in L Boxx Mini

Order-No	
44318	1
*	SL/PZ2 x 75
\ominus	3,5 x 75
	E-screwdriver handle speedE®
	Charger for 18500 Li-ion batteries with USB
	Battery set, 18500 Li-ion 2 units in box



Protect your health: Recommended by German doctors and therapists from German Campaign for Healthier Backs. Increases your control: Fixing by hand with a deft touch. Offers you full protection: slimBits tested at 10,000 V AC and approved for 1,000 V AC. Increases your speed: Work twice as fast thanks to three-step process. Protects your material: Electric screw fastening with protection function to prevent damage to materials (max. 0.4 Nm).

E-screwdriver, starter set speedE[®] I electric



591

4-part	with slimBit, battery and USB charger	590
Order-N	lo. 🗎	
44351	1	
۲	SL/PZ1 x 75	
	E-screwdriver handle speedE®	
	Charger for 18500 Li-ion batteries with USB	
	18500 Li-lon battery in box	







Simplifies your work: Offers room for a Wiha e-screwdriver as well as 4 slimBits. Eyelet at the bottom of the pouch allows storage of the e-screwdriver with inserted bit. Makes handling easier: Simple to hook on to work trousers thanks to the high quality clip holder.

Battery set, 18500 Li-ion



2 units in box

2 units in box	5991
Order-No.	
41914	6

Charger for 18500 Li-ion batteries



for e-screwdriver speedE [®]	5994E
Order-No.	
44367	

with USB and Europlug 599		
Order-No.		
41915	Power plug EU	1
42766	Power plug UK	

Power plug



EU	5992
Order-No.	
44363	

Power plug



UK	59925992
Order-No.	
44364	

INFOBOX: Wiha speedE[®] II





E-screwdriver speedE®

- 3x faster than manual fastening.
- Two material protection levels: 0.4 Nm and 1.0 Nm.
- Made in Germany.
- Safe working up to 1,000 V AC.
- Manual torque fastening up to 12 Nm.
- Powerful ring LED light.
- Replaceable standard battery.
- Kind to hands and muscles.
- Fully compatible with the Wiha slimBit system.









2831

Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. Makes handling easier: Compact slimBit box with easy access and an optimal view of profiles. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.



Slotted, Phillips, Pozidriv 6-pcs. in SlimBit box

Order-No		
43160		6
\ominus	2,0 / 2,5	
Ð	PH0 / PH1	
*	PZ0 / PZ1	
	slimBit box	

Manufactured acc. to IEC 60900.



access to deep-set screws. Makes handling easier: Compact slimBit box with easy access and an optimal view of profiles. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.



Mixed 6-pcs. in slimBit box

Power slimBit electric bit set

Order-No	
44106	1
\ominus	5,5
\oplus	PH2
۲	SL/PZ2
۲	T15 / T20 / T25
	slimBit-Box
	ed acc. to IEC 60900.

Mixed 6-pcs. in slimBit box 280		
Order-No		
44366		1
\ominus	2,5	
Ð	PH1	
*	PZ1	
۲	SL/PZ1	
۲	T9 / T10	
	slimBit-Box	
Manufacture	ed acc. to IEC 60900.	

Slotted, hex, 6-pcs. in slimBit box 2831		
Order-No).	
44107		1
\ominus	6,5	
۲	2,5 / 3 / 4 / 5 / 6	
	slimBit-Box	
	red acc. to IEC 60900	


Manufactured acc. to IEC 60900.





2831





There are moments when you need to control your power.





Power is good. Controlled power is better. The fully certified Wiha VDE torque screwdriver systems TorqueVario[®]-S and TorqueVario[®]-S TR combine precision with safety: With a distinctly audible and perceptible click signal when the torque value is reached. With a release accuracy of +/-6 % of the set scale value, Wiha VDE screwdrivers meet the accuracy requirements of EN ISO 6789. Uncompromising safety is ensured in production and testing according to IEC 60900, VDE/GS certification and individual product testing at 10,000 V AC.

- Increases your efficiency Using the correct torque prevents from rework and damaged material.
- Lowers your costs The correct torque protects you from warranty claims.
- Offers you full protection Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.
- Increases your safety

Wiha slimBits grant unhindered, fully insulated access to deeplying screws.









Meets your requirements: A variably settable torque covers a large application area. **Simplifies your work:** All tools securely arranged in a robust, orderly bag. **Lowers your costs:** The correct torque protects you from warranty claims. **Increases your safety:** Wiha slimBits ensure good, protected access to deep-set screws. **Protect your health:** With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. **Increases your efficiency:** The correct torque avoids damaging material and no follow-up work is necessary. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Mixed,	, variably adjustable torque limit, 18 pcs. in folding bag	2872 T18
Order-N	No.	
36791		1
0	1 x Torque screwdriver TorqueVario®-S electric Variable torque limit settings, VDE and GS tested / 0,8-5,0 Nm	
	1 x Adjusting tool for torque screwdriver with long handle	
0	1 x Adapter TorqueVario-S electric for slimBits	
Θ	1 x 2,5• / 1 x 3,5 / 1 x 5,5 / 1 x 6,5	
Ð	1 x PH1 / 1 x PH2	
*	1 x PZ1 / 1 x PZ2	
۲	1 x SL/PZ1 / 1 x SL/PZ2	
no slim	1 x T9 / 1 x T10• / 1 x T15 / 1 x T20 / 1 x T25	

Manufactured acc. to IEC 60900. DIN EN ISO 6789.









Meets your requirements: A variably settable torque covers a large application area. **Simplifies your work:** All tools securely arranged in a robust, orderly bag. **Lowers your costs:** The correct torque protects you from warranty claims. **Increases your safety:** Wiha slimBits ensure good, protected access to deep-set screws. **Protect your health:** With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. **Increases your efficiency:** The correct torque avoids damaging material and no follow-up work is necessary. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Mixed,	variably adjustable torque limit, 13 pcs. in folding bag	2872 T13
Order-N	lo.	
40674		1
0	1 x Torque screwdriver TorqueVario®-S electric Variable torque limit settings, VDE and GS tested / 0,8-5,0 Nm	
	1 x Adjusting tool for torque screwdriver with long handle	
0	1 x Screwdriver with bit holder SoftFinish® electric slimVario for slimBits, VDE and GS tested	
0	1 x Adapter TorqueVario-S electric for slimBits	
Θ	1 x 2,5• / 1 x 3,5 / 1 x 5,5	
Ð	1 x PH1 / 1 x PH2	
*	1 x PZ1 / 1 x PZ2	
۲	1 x SL/PZ1 / 1 x SL/PZ2	
 no slim 	version	

Manufactured acc. to IEC 60900. DIN EN ISO 6789.









Simplifies your work: All tools securely arranged in a robust, orderly bag. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. Increases your flexibility: Nut driver inserts can be used with speedE®, slimVario® and TorqueVario®-S tools thanks to the enclosed adapters. Protects your material: Fully insulated nut driver reduces the risk of short circuits.

Mixed, 10-pcs., with adapters in folding bag

Mixed,	10-pcs., with adapters in folding bag 7209N
Order-N	lo.
43466	1
	1 x slimVario® electric adapter for 1/4" nut driver
0	1 x Adapter TorqueVario-S electric for 1/4" nut driver
0	1 x 5 / 1 x 5,5 / 1 x 6 / 1 x 7 / 1 x 8 / 1 x 10 / 1 x 11 / 1 x 13



Meets your requirements: A variably settable torque covers a large application area. Lowers your costs: The correct torque protects you from warranty claims. Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. Increases your efficiency: The correct torque avoids damaging material and no follow-up work is necessary. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Order-No	0.	
38074		1
0	1 x Torque screwdriver TorqueVario®-S electric Variable torque limit settings, VDE and GS tested / 0,8-5,0 Nm	
	1 x Adjusting tool for torque screwdriver with long handle	
0	1 x Adapter TorqueVario-S electric for slimBits	
*	1 x SL/PZ1 / 1 x SL/PZ2	





Meets your requirements: A variably settable torque covers a large application area. Lowers your costs: The correct torque protects you from warranty claims. Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. Increases your efficiency: The correct torque avoids damaging material and no follow-up work is necessary. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

OVariable torque limit settings

Torque screwdriver TorqueVario®-S electric

Variable	Ovariable torque limit settings								
Best. Nr.	Nm	₩2%	0		+				
26625	0,5-2,0	6 %	- , -		30	1			
26626	0,8-5,0	6 %			36	1			
26627	2,0-7,0	6 %	3,8	142	41	1			
Manufactured acc. to IEC 60900, DIN EN ISO 6789,									

Adjusting tool

					11	wiho		
for torque		driver	with lon	g hand	le			2859
Order-No.	i ∗ mm [™]	—				Ĺ	•	
26864	146	90					1	

Increases your efficiency

Fast, easy checking of your torque tool thanks to mobile, compact shape.

wiha 2.8 Nm

1

10

2 2.8 Nm

000=

Increases your safety

Checking your torque tool regularly guarantees safe, precise work with the correct torque.

Saves time

LED traffic light system displays results in a way which is quick and easy to understand.










2909

Increases your safety: Checking your torque tool regularly guarantees safe, precise work with the correct torque. **Saves time:** LED traffic light system displays results in a way which is quick and easy to understand. **Increases your efficiency:** Fast, easy checking of your torque tool thanks to mobile, compact shape.

with adapter blades and batteries in box

Best. Nr.	Nm	+/- %	SB	
	******	•••••••••••••••••••••••••••••••••••••••	********	
42086	2,8	2	Х	1



INFOBOX: Torque QuickCheck



Wiha Torque QuickCheck

- The Wiha torque screwdriver can quickly and easily test torque screwdrivers to check the precision of the configured torque value before each use.
- Checking tools regularly ensures reliable, precise work.
- The device offers user-friendly operation, clear test readings and easy to understand LED traffic light signals.
- Thanks to a compact, handy shape, it is the ideal companion when out on jobs.
- Suitable for all Torque Vario[®]-S and iTorque[®] torque screwdrivers whose torque range included 2.8 Nm.





Lowers your costs: The correct torque protects you from warranty claims. Increases your efficiency: The correct torque avoids damaging material and no follow-up work is necessary. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

with slimVario® holder and SL/PZ slimBits, 4-pcs. in blister pack

		29701 080 S4
Order-No.		
41476		1
	1 x 0,8 Nm ±10%	
*	1 x SL/PZ1 / 1 x SL/PZ2	
Manufacture	1 x SoftFinish® electric screwdriver handle	

for slimBits and slimVario[®] holder, 5-pcs. in blister pack 29701 S5 Order-No <u>(</u>)

Lowers your costs: Torque tool extension for LiftUp and slimVario®

Lowers your costs: Torque tool extension for LiftUp and slimVario®

tested at 10,000 V AC and approved for 1,000 V AC.

screwdriver sets. The correct torque protects you from warranty claims.

screwdriver sets. The correct torque protects you from warranty claims. Increases your efficiency: The correct torque avoids damaging material and no follow-up work is necessary. Fully compatible with the Wiha slimBit system. Offers you full protection: Each tool individually

41479		1
+10%	1 x 0,8 Nm / 1 x 2,0 Nm /	1 x 2,5 Nm / 1 x 2,8 Nm /
1070	1 x 4,0 Nm	
Manufactured	acc. to IEC 60900.	

with slimVario® holder and SL/PZ slimBits, 4-pcs. in blister pack

		29701 200 S4
Order-No.		
41477		1
	1 x 2,0 Nm ±10%	
۲	1 x SL/PZ1 / 1 x SL/PZ2	
	1 x SoftFinish® electric screwdriver handle	
Manufactured	acc. to IEC 60900.	

with slimVario® holder and SL/PZ slimBits, 4-pcs. in blister pack

in bilste	pack	29701 280 S4
Order-No		
41478		1
	1 x 2,8 Nm ±10%	
۲	1 x SL/PZ1 / 1 x SL/PZ2	
	1 x SoftFinish® electric screwdriver handle	

Manufactured acc. to IEC 60900.



Lowers your costs: Torque tool extension for LiftUp and slimVario® screwdriver sets. The correct torque protects you from warranty claims. Increases your efficiency: The correct torque avoids damaging material and no follow-up work is necessary. Fully compatible with the Wiha slimBit system. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

for slimBits and slimVario® holder in blister

Order-No.	Nm	+/- %	₽	÷	
41341	0,8	10 %	59	5,5	1
41342	2,0	10 %	59	5,5	1
41343	2,0	10 %	59	5,5	1
41344	2,8	10 %	59	5,5	1
41345	4,0	10 %	59	5,5	1
Manufactured ad	cc. to IE	C 60900.			

2970









Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. **Makes handling easier:** Compact slimBit box with easy access and an optimal view of profiles. Convenient safe storage of 12 slimBits – easily taken directly from the belt. **Makes handling easier:** Compact slimBit box with easy access and an optimal view of profiles. Convenient safe storage of 12 slimBits – easily taken directly from the belt. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.



TORX®	, TORX PLUS®, 12-pcs. in SlimBit box	2831
Order-N	No.	
43161		6
۲	6IP• / 7IP• / 8IP• / 9IP• / 10IP• / 15	
۲	T6• / T7• / T8• / T9• / T10• / T15	
	slimBit box	
• no slim v	version ured acc. to IEC 60900.	

Slotted, Phillips, Pozidriv, PlusMinus/Pozidriv, TORX[®] 12-pcs. in SlimBit box

	2831
Order-No	
43162	6
\ominus	3,5 / 5,5
\oplus	PH1 / PH2
*	PZ1 / PZ2
۲	SL/PZ1 / SL/PZ2
۲	T10• / T15 / T20 / T25
	slimBit box

• no slim version

Manufactured acc. to IEC 60900.

INFOBOX: slimBit box



v Č

slimBit box

- Compact slimBit box with easy access and an optimal view of profiles.
- Suitable for storing Wiha slimBits. Ideal for mobile use.
- Wiha slimBits ensure unrestricted and fully insulated access to low-lying screws.
- Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.







Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. Makes handling easier: Compact slimBit box with easy access and an optimal view of profiles. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.



Order-No		
43152		6
\ominus	2,0• / 2,5• / 3,5 / 4,0 / 5,5 /	6,5
	slimBit box	

TORX [®] , 6-pcs. in SlimBit box 28				
Order-N	0.			
43153		6		
۲	T8• / T9• / T10• / T15 / T20	/ T25		
	slimBit box			
• no slim v	ersion red acc. to IEC 60900.			
	6-pcs. in SlimBit box	2831		
Order-N	0.			
43154		6		

۲						T10•	T15
	slim	Bit	t box				
no slim version							

Manufactured acc. to IEC 60900.

TORX PLUS®, 6-pcs. in SlimBit box 2831

Order-No.		(m)
43155		6
۲	6IP• / 7IP• / 8IP• /	
	slimBit box	
 no slim versic Manufactured a 	n Icc. to IEC 60900.	

Hex, 6-pcs. in SlimBit box

Order-No.		(m)
43156		6
۲	2• / 2,5 / 3 / 4 / 5 / 6	
	slimBit box	
• no slim versio	n	

Manufactured acc. to IEC 60900.

Slotted	Slotted, Pozidriv 6-pcs. in SlimBit box 283			
Order-N	lo.			
43157		6		
\ominus	2,5• / 3,5 / 5,5 / 6,5			
*	PZ1 / PZ2			
	slimBit box			
• no slim v	version			

Manufactured acc. to IEC 60900.

Slotted, F	PlusMinus/Pozidriv 6-pcs	. in SlimBit box 2831
Order-No.		
43158		6
\ominus	2,5• / 3,5 / 5,5 / 6,5	
۲	SL/PZ1 / SL/PZ2	
	slimBit box	
 no slim versi Manufactured 		

Manufactured acc. to IEC 60900.

Slotted, Phillips 6-pcs. in SlimBit box 2831			831
Order-No.	-		
43159		6	
\ominus	2,5• / 3,5 / 5,5 / 6,	5	
Ð	PH1 / PH2		
	slimBit box		
 no slim version 			

Manufactured acc. to IEC 60900.

Slotted, Phillips, Pozidriv 6-pcs. in SlimBit box 283		
Order-No.		
43160		6
\ominus	2,0• / 2,5•	
Ð	PHO• / PH1	
*	PZ0• / PZ1	
	slimBit box	
• no slim ver	sion d acc. to IEC 60900.	

Mixed 6-pcs. in slimBit box

Order-No.		
44366	1	
\ominus	2,5•	
Ð	PH1	
*	PZ1	
۲	SL/PZ1	
۲	T9• / T10•	
	slimBit-Box	

Manufactured acc. to IEC 60900.



2831



slimBit box





2831-B992



Increases your safety: Wiha Power slimBits ensure good, protected access to deep-set screws. **Makes handling easier:** Compact slimBit box with easy access and an optimal view of profiles. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Makes handling easier: Compact slimBit box with easy access and an optimal view of profiles. Convenient safe storage of 12 slimBits – easily taken directly from the belt.

empty, 2-pcs. with belt clip

Order-No.	
43164	6
slimBit box Empty	



Mixed 6-p	ocs. in slimBit box	2831
Order-No.		
44106		1
\ominus	5,5	
\oplus	PH2	
۲	SL/PZ2	
۲	T15 / T20 / T25	
	slimBit-Box	

Manufactured acc. to IEC 60900.

Slotted, he	ex, 6-pcs. in slimBit box	2831
Order-No.		
44107	1	
\ominus	6,5	
۲	2,5 / 3 / 4 / 5 / 6	
	slimBit-Box	

Manufactured acc. to IEC 60900.

slimBit box



 $\ensuremath{\textbf{Makes}}$ handling easier: Compact slimBit box with easy access and an optimal view of profiles.

Empty

Order-No.	
43163	6



slimBit electric bit



283115

283116

5

5

5

5

5

5

5

5

5



Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. Saves space: Extensive interchangeable bit system saves you space. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

TORX®

Order-No.

43140

43141

43142

35506

41160

35507

35508

'**€**mm

75

75

75

75

75

75

75

75

75

۲

T5∙

T6•

Τ7∙

T8∙

T9∙

T10•

T15

•‡

6,0

6,0

6,0

6,0

6,0

6,0

6,0

6,0

6,0

max. Nm

0,4

0,4

0,4

1,3

1,3

3,8

5,0

5,5

5,5

⊖Slotted						283110
Order-No.	θ	i • mm	⊖ŧ	@ ‡	max. Nm	
43114	1,5•	75	0,4	6,0	0,4	5
43115	, -	75	- /	6,0	0,4	5
34578	2,5•		0,4	6,0	0,4	5
34579	3,0•	75	0,5	6,0	0,6	5
41159	- / -	75	- , -	6,0	1,4	5
34580	4,0	75	0,8	6,0	2,5	5
34581	5,5	75		6,0	3,8	5
34582	6,5	75	1,2	6,0	5,5	5
no slim versio					*******	

Manufactured acc. to IEC 60900.

Phillips

Phillips					283111
Order-No.	Ð	¦ ∗ → I mm	١	max. Nm	
43116	PH0•	75	6,0	0,4	5
34583	PH1	75	6,0	3,8	5
34584	PH2	75	6,0	5,5	5

Pozidriv	/				283112
Order-No.	*	i • mm	١	max. Nm	
43117	PZ0•	75	6,0	0,5	5
34585	PZ1	75	6,0	3,8	5
34586	PZ2	75	6,0	5,5	5
Manufactured	acc. to IF	C 60900			

max. Nm

3,8

5,5

34586	PZ2	75	6,0
Manufactured	acc. to IFC	6090	0.

Ð

SL/PH1

SL/PH2

'mm'

75

75

0

6,0

6,0

PlusMinus/Phillips

Manufactured acc. to IEC 60900.

Order-No.

34587

34588

Order-No.	۲	™mm	١	max. Nm	
43143	5IP•	75	6	0,5	5
43144	6IP•	75	6	0,8	5
43145	7IP●	75	6	1,3	5
43146	8IP•	75	6	2,0	5
43147	9IP•	75	6	3,0	5
43148	10IP•	75	6	4,5	5
43149	15IP	75	6	5,5	5
43150	20IP	75	6	5,5	5
43151	25IP	75	6	5,5	5
 no slim versi 					

Manufactured acc. to IEC 60900.

Square						283117
Order-No.			¦•—→I mm	©‡	max. Nm	H
35510	#1	2,3	75	6,0	5,5	5
35511	#2	2,8	75	6,0	5,5	5
Manufactured a						

PlusMini	us/Pozidriv	283114			
Order-No.	۲	i• mm i	۱	max. Nm	
34589	SL/PZ1	75	6,0	3,8	5
34590	SL/PZ2	75	6,0	5,5	5

Manufactured acc. to IEC 60900.

283113

5

5

Order-No.	۲	i ≪mm i	۵	max. Nm	
37222	1,5•	75	6,0	0,9	5
37223	2•	75	6,0	1,8	5
37224	2,5	75	6,0	3,8	5
37147	3	75	6,0	5,5	5
37225	4	75	6,0	5,5	5
37226	5	75	6,0	5,5	5
37227	6	75		5,5	5



Manufactured acc. to IEC 60900.

TORX PLUS®

46	wiha 🐵
	Tools that work for you



Insulated nut driver insert

O1/4^ª hexagon head







Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. Protects your material:

Fully insulated tool reduces the risk of short circuits.



Increases your efficiency: Fully compatible with the Wiha slimBit system. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Ofor slim					28799
Order-No.	0	•1	™mm	ţ.	
35870	6	3,8	170	13	10

Manufactured acc. to IEC 60900.



7209NS Order-No. Ο ₩mm 5,5

Increases your efficiency: Adapter allows users to fasten with a nut driver and TorqueVario®-S electric. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Ofor 1/4"	nut dr	iver			28799
Order-No.	۲	•1	l ∗ mm [−] l	ţ	
43128	1/4"	3,8	178	12	10

Manufactured acc. to IEC 60900.

Manufactured according to EN/IEC 60900.



Torque screwdriver with T-handle TorqueVario®-S T electric

Interchangeable electric blade



Meets your requirements: A variably settable torque covers a large application area. Lowers your costs: The correct torque protects you from warranty claims. Makes handling easier: Effortless and comfortable transmission of high torques thanks to T-handle with ComfortGrip. Increases your efficiency: The correct torque avoids damaging material and no follow-up work is necessary. Offers you full protection: Torque blades tested at 10,000 V AC and approved for 1,000 V AC.

	Variable torque limit settings 2933						
Order-No.	Nm	+/- %	0	.	-0 ‡		
43177	5-14	6	6	56	120	1	

Manufactured acc. to IEC 60900. DIN EN ISO 6789.



Increases your safety: Wiha slim interchangeable blades ensure unlimited and fully-insulated access to low-lying screws. Increases your efficiency: Extensive interchangeable blade system saves you space. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

TORX[®] for torque screwdriver with T-handle electric

					283795
Order-No.	۲	mm	→	max. Nm	Ê
38931	T15	136	35	5,5	10
38932	T20	136	35	10	10
38933	T25	136	35	15	10
38934	T27	136	35	15	10
38935	T30	136	35	20	10
38936	T40	136	35	20	10
Manufactured					

Hex for torque screwdriver with T-handle lectric

e	I	е	С	τ	

					283793
Order-No.	۲	" ← →" mm		max. Nm	₩
38918	3,0	136	35	5,5	10
38919	4,0	136	35	15	10
38920	5,0	136	35	20	10
38921	6,0	136	35	20	10
Manufactured		C 60900)		

000700

INFOBOX:

Torque T-handle TorqueVario[®]-S T electric





Torque T-handle TorqueVario®-S T electric

- For controlled fastening in a large range of applications.
- Torque value is continuously adjustable thanks to the adjusting tool.
- More fastening power thanks to T-handle design.
- Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.
- Certified individual item testing directly after on-site production.
- Broad selection of interchangeable blades



2899

Adjusting tool

Interchangeable electric blade



Increases your efficiency: Extensive interchangeable blade system saves you space. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

O Hex nut driver for torque screwdriver with T-handle electric

				283794
Order-No.	0	mm	max. Nm	=
38925	.,-	136	5	10
38926	8,0	136	10	10
38927	9,0	136	14	10
38928	10,0	136	17	10
38929	13,0	136	20	10
38930	17,0	136	20	10
Manufactured				





Order-No.	╤╸	¦ ∢ ≻∣ mm	⊨
28691	90	146	1

wiha 🤄

11



All bits in the handle, always and everywhere.



Why make things complicated, when they can be compact? The practical Wiha LiftUp electric magazine bit holder accommodates up to six common insulated slimBits - and is therefore the ideal portable companion for every electrician. The bit magazine is unlocked at the touch of a button on the two rockers, and the slimBits can easily be removed and re-inserted. A reliably locked magazine prevents anything from being lost when on the move. The rotating cap is used to make working easier: Additional axial force can be exerted by pressing strongly with the hand against the cap, while rotating around the longitudinal axis with the other hand. Uncompromising safety is ensured in production and testing according to IEC 60900, VDE/GS certifi cation and individual part testing at 10,000 V AC.

The Wiha magazine bit holder LiftUp electric is available in two content variants (SL/PH or SL/PH/PlusMinus PZ)

- Increases your efficiency
 Wiha LiftUp electric, saves 75 % volume and 50 % less weight for 100 % efficiency.
- Protect your health No risk of injury, all blades stowed safely inside the handle.
- Offers you full protection Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.
- Increases your safety

Wiha slimBits grant unhindered, fully insulated access to deep lying screws.







Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. **Protect your health:** No risk of injury, all blades stowed safely inside the handle. **Increases your efficiency:** Wiha LiftUp electric saves 75% volume and 50% less weight for 100 % efficiency. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.



sSlotte	d, Phillips with 6 slimBits in blister pack SB2831
Order-N	
38612	1
Θ	1 x 2,5 / 1 x 3,0 / 1 x 4,0 / 1 x 5,5
Ð	1 x PH1 / 1 x PH2
Manufact	ired acc. to IEC 60900.

Slotted	I, Pozidriv, PlusMinus/Pozidriv with 6 slimBits in blister pack	SB2831
Order-N	lo.	
41235	1	
\ominus	1 x 2,5 / 1 x 3,5 / 1 x 5,5	
*	1 x PZ1 / 1 x PZ2	
*	1 x SL/PZ2	
Manufactu	ured acc. to IEC 60900.	

TORX [®] with 6 slimBits in blister pack	SB2831
Order-No.	
41158	1
1 x T8 / 1 x T9 / 1 x T10 / 1 x T15 / 1 x T20 / 1 x T25	

Manufactured acc. to IEC 60900.









Simplifies your work: All tools securely arranged in a robust, orderly bag. Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. Increases your efficiency: Extensive interchangeable blade system saves you space. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Mixed, 18-pcs. in folding bag

		2001
Order-No.		
41231		1
0	Schraubendreher mit Bithalter SoftFinish® electric slimVario Stubby for slimBits, VDE and GS tested	
0	Schraubendreher mit Bithalter SoftFinish® electric slimVario for slimBits, VDE and GS tested	
Θ	1 x 2,5• / 1 x 3,5 / 1 x 5,5	
Ð	1 x PH1 / 1 x PH2	
*	1 x PZ1 / 1 x PZ2	
٠	1 x SL/PZ1 / 1 x SL/PZ2	
۲	1 x T9• / 1 x T10• / 1 x T15 / 1 x T20	
\bigcirc	1 x 3 / 1 x 4 / 1 x 5	

Manufactured acc. to IEC 60900.









Simplifies your work: All tools securely arranged in a robust, orderly bag. Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. Increases your efficiency: Extensive interchangeable blade system saves you space. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Slotted, Phillips, Pozidriv, 9-pcs. in folding bag

Order-N	0.	
41232		1
0	Screwdriver with bit holder SoftFinish® electric slimVario Stubby for slimBits, VDE and GS tested	
0	Screwdriver with bit holder SoftFinish® electric slimVario for slimBits, VDE and GS tested	
Θ	1 x 2,5• / 1 x 3,5 / 1 x 5,5	
Ð	1 x PH1 / 1 x PH2	
*	1 x PZ1 / 1 x PZ2	

Manufactured acc. to IEC 60900.

Slotted,	, Pozidriv, PlusMinus/Pozidriv, 9-pcs. in folding bag	2831
Order-No	o. 🗎	
41233	1	
0	Screwdriver with bit holder SoftFinish® electric slimVario Stubby for slimBits, VDE and GS tested	
0	Screwdriver with bit holder SoftFinish® electric slimVario for slimBits, VDE and GS tested	
\ominus	1 x 2,5• / 1 x 3,5 / 1 x 5,5	
*	1 x PZ1 / 1 x PZ2	
*	1 x SL/PZ1 / 1 x SL/PZ2	
• no slim ve	ersion	

no slim version
 Manufactured acc. to IEC 60900.









Simplifies your work: All tools securely arranged in a robust, orderly bag. Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. Protects your material: Fully insulated nut driver reduces the risk of short circuits.

mixed, 13-pcs. in folding bag

mixed, 13-pcs. in folding bag		7209N
Order-N	0.	
43467		1
0	1 x SoftFinish® electric screwdriver handle, VDE and GS tested	
0	1 x Extension slimVario® electric for slimBits, VDE and GS tested	
	1 x slimVario® electric adapter for 1/4" nut driver	
\ominus	1 x 3,5 / 1 x 5,5	
0	1 x 5 / 1 x 5,5 / 1 x 6 / 1 x 7 / 1 x 8 / 1 x 10 / 1 x 11 / 1 x 13	
Monufacti	red acc. to JEC 60000	

Manufactured acc. to IEC 60900.









Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. **Protect your health:** With the patented SoftFinish[®] handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

4-pcs.	4-pcs. with slimBits		
Order-N	lo. 🗎		
43449	5		
0	1 x Screwdriver with bit holder SoftFinish® slimVario® electric for slimBits, VDE and GS tested		
\ominus	1 x 5,5		
۲	1 x SL/PZ1 / 1 x SL/PZ2		
Manufact	ured acc. to IEC 60900.		

Screwdriver with bit holder set electric slimVario®	VARIO FAMILY
se wiha	vihas
34.772 2 / 2001) with a second seco	
First 120111 withor rest 15 km	
EAGISITANY WITH 2001	A 1000 V IEC 60900

Simplifies your work: Compact handle – maximum power. Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. Protected work in constricted spaces. Increases your efficiency: Fully compatible with the Wiha slimBit system. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Order-N	No.	
41230		1
0	Screwdriver with bit holder SoftFinish® electric slimVario Stubby for slimBits, VDE and GS tested	
\ominus	3,5 x 75	
Ð	PH2 x 75	
*	SL/PZ2 x 75	









Fastening / jamming


Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. Increases your efficiency: Fully compatible with the Wiha slimBit system. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. Increases your efficiency: Careful workmanship and controlled power transmission thanks to the slim handle with soft grip. Particularly suitable for use with slimBit profiles.

4-pcs. with slimBits

4-pcs. with slimBits	
Order-No	
43167	5
0	1 x Fine screwdriver PicoFinish® slimVario® electric for slimBits, VDE and GS tested
\ominus	1 x 2,0•
Ð	1 x PH0•
*	1 x PZ0•
• no slim v	sion

Manufactured acc. to IEC 60900.







Wiha SoftFinish® electric slimFix

- Unlimited access.
- Blades up to 33 % narrower due to integrated insulation.
- Tool for spring clips (wedge-profiled output geometry).







Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. **Makes handling easier:** Compact slimBit box with easy access and an optimal view of profiles. Convenient safe storage of 12 slimBits – easily taken directly from the belt. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.



TORX®, TORX PLUS®, 12-pcs. in SlimBit box 283		
Order-N	0.	
43161		6
۲	6IP• / 7IP• / 8IP• / 9IP• / 10IP• / 15	
۲	T6• / T7• / T8• / T9• / T10• / T15	
	slimBit box	
• no slim v	rersion Ired acc. to IEC 60900.	

Slotted, Phillips, Pozidriv, PlusMinus/Pozidriv, TORX® 12-pcs. in SlimBit box

		2831	
Order-No.		£	
43162		6	
\ominus	3,5 / 5,5		
\oplus	PH1 / PH2		
*	PZ1 / PZ2		
۲	SL/PZ1 / SL/PZ2		
۲	T10• / T15 / T20 / T25		
	slimBit box		

no slim version

Manufactured acc. to IEC 60900.

INFOBOX: slimBit box



slimBit box

- Compact slimBit box with easy access and an optimal view of profiles.
- Suitable for storing Wiha slimBits. Ideal for mobile use.
- Wiha slimBits ensure unrestricted and fully insulated access to low-lying screws.
- Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.







Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. Makes handling easier: Compact slimBit box with easy access and an optimal view of profiles. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.



Slotted, 6-pcs. in SlimBit box		2831
Order-N		
43152		6
\ominus	2,0• / 2,5• / 3,5 / 4,0 / 5,5	/ 6,5
	slimBit box	
• no slim v	ersion red acc. to IEC 60900.	
TORX®,	6-pcs. in SlimBit box	2831

Order-No			
43153		6	
۲	T8• / T9• / T10• / T15 / T20 / T25		
	slimBit box		
• no slim ve	ersion red acc. to IEC 60900.		
TORX®, 6-pcs. in SlimBit box		2831	

Order-N	0.	
43154		6
۲	T6• / T7• / T8• / T9• /	T10• / T15
	slimBit box	
• no slim v	ersion red acc. to IEC 60900.	

TORX PLUS®, 6-pcs. in SlimBit box 2831 Order-No. 43155 6 ۲ 6IP• / 7IP• / 8IP• / 9IP• / 10IP• / 15IP slimBit box • no slim version Manufactured acc. to IEC 60900.

Hex, 6-pcs. in SlimBit box

2831 Order-No. 43156 6 2• / 2,5 / 3 / 4 / 5 / 6 ۲ slimBit box

• no slim version Manufactured acc. to IEC 60900.

Slotted, Pozidriv 6-pcs. in SlimBit box

Order-No.		
43157		6
\ominus	2,5• / 3,5 / 5,5 / 6,5	
*	PZ1 / PZ2	
	slimBit box	
 no slim version Manufactured ad 	1	

,	PlusMinus/Pozidriv 6-pcs. in SlimBit box	2831
Order-No.	í	
43158		6
\ominus	2,5• / 3,5 / 5,5 / 6,5	
۲	SL/PZ1 / SL/PZ2	
	slimBit box	
 no slim vers Manufactured 	ion 1 acc. to IEC 60900.	

Slotted,	Phillips 6-pcs. in SlimBit box	2831
Order-No.	•••••	
43159		6
\ominus	2,5• / 3,5 / 5,5 / 6,5	
\oplus	PH1 / PH2	
	slimBit box	
 no slim ver 	sion d acc. to IEC 60900.	

Slotted, Phillips, Pozidriv 6-pcs. in SlimBit box 2831 Order-No. 43160 6 \ominus 2,0• / 2,5• Ð PH0• / PH1 PZ0• / PZ1 slimBit box • no slim version

Manufactured acc. to IEC 60900.

Mixed 6-pcs. in slimBit box

Order-No.	
44366	1
\ominus	2,5•
Ð	PH1
*	PZ1
*	SL/PZ1
۲	T9• / T10•
	slimBit-Box
• no slim versior	1

Manufactured acc. to IEC 60900.

2831

2831

VARIO FAMII

slimBit box





Increases your safety: Wiha Power slimBits ensure good, protected access to deep-set screws. Makes handling easier: Compact slimBit box with easy access and an optimal view of profiles. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Makes handling easier: Compact slimBit box with easy access and an optimal view of profiles. Convenient safe storage of 12 slimBits easily taken directly from the belt.

empty, 2-pcs. with belt clip

Order-No.	
43164	6
slimBit box Empty	

2831-B992



. . .

Mixed 6-pcs. in slimBit box					
Order-No.	-				
44106		1			
\ominus	5,5				
\oplus	PH2				
۲	SL/PZ2				
۲	T15 / T20 / T25				
	slimBit-Box				

Manufactu

Slotted, he	Slotted, hex, 6-pcs. in slimBit box 2831					
Order-No.						
44107	1					
\ominus	6,5					
۲	2,5 / 3 / 4 / 5 / 6					
	slimBit-Box					
Manufactured						

Manufactured acc. to IEC 60900.

slimBit box



Makes handling easier: Compact slimBit box with easy access and an optimal view of profiles.

Empty

Order-No.	
43163	6

. . .

10.		
	1	
	5,5	
	PH2	
	SL/PZ2	
	T15 / T20 / T25	
	slimBit-Box	
ured ac	c. to IEC 60900.	

slimBit electric bit





Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws. Saves space: Extensive interchangeable bit system saves you space. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

TORX®

\ominus Slotted						283110
Order-No.	θ	i ∢ ► mm	O ‡	١.	max. Nm	
43114	1,5•	75	0,4	6,0	0,4	5
43115	2,0•	75		6,0	0,4	5
34578	2,5•	75	0,4	6,0	0,4	5
34579	,	75	,	6,0	0,6	5
41159	3,5		0,6	6,0	1,4	5
34580	4,0	75	0,8	6,0	2,5	5
34581	5,5		1,0	6,0	3,8	5
34582	6,5	75	• ,—	6,0	5,5	5
 no slim version 	on			******		

Manufactured acc. to IEC 60900.

Phillips

Phillips					283111
Order-No.	Ð	¦ ∢ ≯∣ mm	۵	max. Nm	É
43116	PH0•	75	6,0	0,4	5
34583	PH1	75	6,0	3,8	5
34584	PH2	75	6,0	5,5	5

🕀 Pozidriv	V				283112	
Order-No.	*	¦ ∗ ⊧ mm	۵	max. Nm	H	
43117	PZ0•	75	6,0	0,5	5	
34585	PZ1	75	6,0	3,8	5	
34586	PZ2	75	6,0	5,5	5	
Manufactured acc. to IEC 60900.						

			••••••		
36	PZ2	75	6,0	5,5	
factured	acc. to IEC	60900	•		

PlusMinu	us/Phillips				283113
Order-No.	Ð	™mm	١٠)	max. Nm	
34587	SL/PH1	75	6,0	3,8	5
34588	SL/PH2	75	6,0	5,5	5
Manufactured a					

PlusMinus/Pozidriv

PlusMinu					283114
Order-No.	۲	™mm	٤)	max. Nm	£
34589	SL/PZ1	75	6,0	3,8	5
34590	SL/PZ2	75	6,0	5,5	5
Manufactured ac					

TORX®					283115
Order-No.	۲	i • mm ⁱ	١	max. Nm	
43140	T5•		6,0	0,4	5
43141	T6∙	75	6,0	0,4	5
43142	T7●	75	6,0	0,4	5
35506	T8∙	75	6,0	1,3	5
41160	T9∙	75	6,0	1,3	5
35507	T10•	75	6,0	3,8	5
35508	T15	75	6,0	5,0	5
35509	T20	75	6,0	5,5	5
36071	T25	75	6,0	5,5	5
• no slim versi	on				

Manufactured acc. to IEC 60900.

TORX PLUS®

TORX F	PLUS®				283116
Order-No.	۲	i ∙ → I mm	١	max. Nm	
43143	5IP•	75	6	0,5	5
43144	6IP•	75	6	0,8	5
43145	7IP•	75	6	1,3	5
43146		75		/ -	5
43147		75		3,0	5
43148	10IP•	75	6	4,5	5
43149	15IP	75	6	5,5	5
	20IP	75	6	5,5	5
43151	25IP		6	5,5	5
• no slim versi					

Manufactured acc. to IEC 60900.

Hex					
					28311
Order-No.	۲	™mm	۵	max. Nm	
37222	1,5•	75	6,0	0,9	5
37223	2•	75	6,0	1,8	5
37224	2,5	75	6,0	3,8	5
37147	3	75	6,0	5,5	5
37225	4	75	6,0	5,5	5
37226	5	75	6,0	5,5	5
37227	6	75	6,0	5,5	5
 no slim versionali 	on	••••••••••			

Manufactured acc. to IEC 60900.

Square						283117
Order-No.			¦ ∗ → I mm	۵	max. Nm	
35510	#1	2,3	75	6,0	5,5	5
35511	#2	2,8	75	6,0	5,5	5



Extension slimVario[®] electric

INFOBOX:



slimVario[®] electric adapter

for 1/4" nut driver

0

¦**←**→ mm

Order-No.



2831-08

Improved access: Deep-set screws can be reached easily. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.


Increases your efficiency: Adapter allows nut driver to be fastened with speedE[®] and slimVario[®] handles. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Þ


۵**–**

for slimBits	6			2831-07
Order-No.	0	i ∗ mm	ţ	
43292	6	69,5	13,3	6

43139 6 6 59 1/4" 12.4 1/4" **VDE** interchangeable bit system



Can be used with these slimBits



PZ0 / PZ1 / PZ2 SL/PZ1/SL/PZ2 T5 / T6 / T7 / T8 / T9 /

1,5 / 2,0 / 2,5 / 3,0 / 3,5 /

4,0 / 5,5 / 6,5

PH0 / PH1 / PH2

T10 / T15 / T20 / T25 IP5 / IP6 / IP7 / IP8 / IP9 / IP10 / IP15 / IP20 / IP25

1,5/2/2,5/3/4/5/6


Robertson 1/2

VDE interchangeable bit system

- Compact VDE bit sets: holder + slimBit (length 75 mm))
- Wiha slimBits ensure good, protected access to deep-set screws.
- slimBits tested at 10,000 V AC and approved for 1,000 V AC.
- Space saved thanks to extensive interchangeable bit system and nut driver inserts.

VDE torque system

• Controlled tightening of electrical screw connections



Fastening / jamming

Easier and protected access to deep-set screws.





Wiha slimTECHNOLOGY enables blades to be up to 33 % slimmer due to the integrated insulation in the blade. Lowlying screw and spring elements in the critical working area can therefore be reached easily. The high-quality blade insulation guarantees safe work in on live parts up to 1,000 V AC/1,500 V DC. Additional safety is assured as each individual screwdriver is tested in a water bath at 10,000 V AC in accordance with IEC 60900. Roll-off protection, the patented, SoftFinish® handle design

that protection, the patented, soft must manue design that protects the hands and muscles from strain, and the unique handle-length concept for optimal balance between power and control all ensure healthier and more efficient work.

The system for every electrician. Available as a screwdriver or as an interchangeable bit system

• Increases your efficiency

Unique Wiha handle-length concept for optimum balance of torque and control.

• Protect your health With the patented SoftFinish[®] handle design,

ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs.


• Offers you full protection Each tool individually tested at 10,000 V AC and

approved for 1,000 V AC.

 Increases your safety
 Wiha slim blades grant unhindered, fully insulated access to low lying screws.









3201

Increases your safety: Wiha slim blades ensure unlimited, protected access to deep-set screws. **Protect your health:** With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. **Increases your efficiency:** Unique Wiha handle-length concept for optimum balance of torque and control. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

assorted 12-pcs.

Order-No	
41003	1
\ominus	3,5 x 100 / 4,0 x 100 / 5,5 x 125 / 6,5 x 150
\oplus	PH1 x 80 / PH2 x 100
*	PZ1 x 80 / PZ2 x 100
۲	SL/PZ2 x 100
۲	T15 x 100 / T20 x 100 / T25 x 125

INFOBOX: Handle size concept



Wiha SoftFinish® handle sizes

- Every Wiha handle optimally balances guidance, speed and torque for the respective fastening task.
- Quick-turning Motor skills are consistently taken into consideration.
- Maximum power transmission: comfortable and loss-free transmission of physical strength, even during intensive fastening.
- The power-turning and quick-turning zones vary significantly

over the four handle sizes in various forms.

• The Wiha SoftFinish screwdrivers enable work that is kind on the hands and muscles and is therefore recommended by doctors and therapists from the AGR.







Increases your safety: Wiha slim blades ensure unlimited, protected access to deep-set screws. Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. Increases your efficiency: Unique Wiha handle-length concept for optimum balance of torque and control. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Slotted, Phillips 6-pcs.

.	
Order-N	lo.
35389	1
\ominus	3,5 x 100 / 4,0 x 100 / 5,5 x 125 / 6,5 x 150
-	
\oplus	PH1 x 80 / PH2 x 100
Manufactu	Jred acc. to IEC 60900.

Slotted, Pozidriv 6-pcs.

Slotted	d, Pozidriv 6-pcs. 3201
Order-N	No.
36455	1
\ominus	3,5 x 100 / 4,0 x 100 / 5,5 x 125 / 6,5 x 150
*	PZ1 x 80 / PZ2 x 100
Manufact	ured acc. to IEC 60900.

Slotted, Phillips, PlusMinus/Pozidriv 6-pcs.

38362	1 4.0 x 100 / 5.5 x 125
-	4 0 × 100 / 5 5 × 125
⊕ PH1 x 80 /	
ℜ SL/PZ2 x 10	0

TORX[®] 6-pcs.

Order-No	
36558	1
۲	T8 x 60• / T9 x 60•
۲	T10 x 100 / T15 x 100 / T20 x 100 / T25 x 125

3201

3201

3251



3251 TR

Increases your safety: Wiha slim blades ensure unlimited, protected access to deep-set screws. **Protect your health:** With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. **Increases your efficiency:** Unique Wiha handle-length concept for optimum balance of torque and control. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

3201

3211

3241

						0201
Order-No.	\ominus	☴	\ominus ;	i• mm	-+	
35446	3,5	100	0,6	204	23	10
35390	4,0	100	0,8	211	30	10
35501	4,5	125	1,0	236	30	10
35391	5,5	125	1,0	243	36	10
35392	6,5	150	1,2	268	36	10
		tured acc				

PlusMinus/Pozidriv

Plusiiint						3281
Order-No.	۲		mm			
36329	SL/PZ1	80	191	30	10	
36330	SL/PZ2		218	36	10	
Manufactured ar	c to IEC 6090	n				•••••

Vanufactured acc. to IEC 60900.

TORX[®] Tamper Resistant (with hole)

Order-No.	۲	—	i•>I mm	
41141	T10H	100	204	23
41142	T15H	100	211	30
41143	T20H	100	211	30
41144	T25H	125	243	36
41145	T27H	125	243	36
41146	T30H	125	243	36
41147	T40H	150	268	36

Manufactured acc. to IEC 60900.

TORX®					3251
Order-No.	۲	☴■	¦ • mm	*	Ĥ
36536	T10	100	204	23	10
36537	T15	100	211	30	10
36538	T20	100	211	30	10
36539	T25	125	243	36	10
36540	T27	125	243	36	10
36541	T30	125	243	36	10
36542	T40	150	268	36	10

DIN ISO 8764-PH. Manufactured acc. to IEC 60900.

Square						3581
Order-No.		۲	☴╸	™mm		Ê
35504	#1	2,3	100	211	30	10
35505	#2	2,8	125	243	36	10
Manufactured ad					••••••	

Phillips

Order-No.	Ð	—	l ∢ → I mm		
35393	PH1	80	191	30	10
35394	PH2		218	36	10
DIN ISO 8764-	PH. Manı	factured	acc. to I	EC 60900.	

Pozidriv

Order-No.	*	╤╸	l ∢ mm ^l		LODI	
35395	PZ1	80	191	30		10
35396	PZ2	100	218	36		10
DIN ISO 8764-	PZ. Manı	factured	acc. to I	EC 6090	0.	

PlusMinu	-				3271
Order-No.	\oplus	╤■	l ≁ →I mm		
35502	SL/PH1	80	191	30	10
35503	SL/PH2		218	36	10
	cc. to IEC 60900		******		





320N

320N

Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. Increases your efficiency: Unique Wiha handle-length concept for optimum balance of torque and control. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Slotted, Phillips 7-pcs.

Slotted,	, Phillips 7-pcs. 320N
Order-No	p. 🖬
00834	1
Θ	2,5 x 75 / 4,0 x 100 / 5,5 x 125 / 6,5 x 150
⊕ Manufactur	PH1 x 80 / PH2 x 100 red acc. to IEC 60900.

Slotted, Phillips 6-pcs.

Order-No		
00833		10
θ	3,0 x 100 / 4,0 x 100 / 5,5 x 125 / 6,5 x 150	
Ð	PH1 x 80 / PH2 x 100	

Slotted, Pozidriv 6-pcs.

Order-No	
25477	1
\ominus	2,5 x 75 / 3,5 x 100 / 4,5 x 125 / 5,5 x 125
*	PZ1 x 80 / PZ2 x 100
Manufactu	red acc. to IEC 60900.



Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. Increases your efficiency: Unique Wiha handle-length concept for optimum balance of torque and control. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

\ominus of σ and σ						320N
Order-No.	θ	=	⊖ ;	l ≁ mm ^I	-+	
00819	2,0	60	0,4	164	23	10
00820	2,5	75	0,4	179	23	10
00821	3,0	100	0,5	204	23	10
00822	3,5	100	0,6	204	23	10
00823	4,0	100	0,8	211	30	10
00824	4,5∙	125	1,0	236	30	10
00825	4,5•	175	1,0	286	30	5
31863	4,5	200	1,0	311	30	5
00826	5,5	125	1,0	243	36	10
00827	5,5•	175	1,0	293	36	5
00828	6,0•	150	1,2	268	36	10
00829	6,5	150	1,2	268	36	10
00830	8,0	175	1,2	299	41	10
00831	8,0	175	1,6	299	41	10
00832	10,0•	200	1,6	324	41	5
Additional dimension. Non-DIN size. Manufactured acc. to IEC 60900.						

PlusMinus/Phillips

PlusMinus	s/Phillips				327
Order-No.	Ð	╤╸	mm	<u> </u>	
30716	SL/PH1	80	191	30	10
30715	SL/PH2	100	218	36	10
Manufactured acc		λ.		••••••	

PlusMinus/Pozidriv 328 ۲ Order-No. mm ____ 30700 SL/PZ1 10 80 191 30 30701 SL/PZ2 100 218 10 36 Manufactured acc. to IEC 60900.

TORX®					325
Order-No.	۲	☴■	mm	+ +	£
03760	T5	60	164	23	10
03761	Т6	60	164	23	10
03762	Τ7	60	164	23	10
00881	T8	60	164	23	10
00882	Т9	60	164	23	10

Manufactured acc. to IEC 60900.

321N

324

Hex					323N
Order-No.	۲	☴■	™mm		
30361	2,5	75	179	23	10
30362	3,0	75	179	23	10
30363	4,0	75	186	30	10
30364	5,0	75	186	30	10
30365	6,0	100	218	36	10
30366	8,0	100	218	36	10
Manufactured a	acc to IE	C 60900			

ired acc. to IEC 60900

Square						358N
Order-No.				™mm		
32396	#1	2,3	100	211	30	10
32397	#2	2,8	150	268	36	10
Manufactured a						

Order-No.

Phillips

Order-No.	Ð		™mm		
00846	PH0	60	164	23	10
00847	PH1	80	191	30	10
00848	PH2	100	218	36	10
00849	PH3	150	268	41	10
00850	PH4	200	318	41	5
Manufactured acc. to IEC 60900.					

🕀 Pozidriv

					-
Order-No.	*	╤╸	™mm		
00877	PZ0	60	164	23	10
00878	PZ1	80	191	30	10
00879	PZ2	100	218	36	10
00880	PZ3	150	324	41	5
Manufactured a					



Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. **Increases your efficiency:** Unique Wiha handle-length concept for optimum balance of torque and control. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Hexagor	nut driver 5-pcs.	322 K5
Order-No		
29466		1
0	5,5 x 125 / 7 x 125 / 8 x 1	25 / 10 x 125 / 13 x 125
Manufactur	ed acc. to IEC 60900.	

Screwdriver SoftFinish [®] elec	tric
--	------

balance of torque and control. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. Increases your efficiency: Unique Wiha handle-length concept for optimum

OHex nut driver

OHex nut	drive	r				322
Order-No.	0	—	l ₄ mm ^l	-+	ţ	
00853	4	125	236	30	10,2	10
00855	5	125	236	30	11,2	10
00856	5,5	125	236	30	11,2	10
00857	6	125	236	30	12,2	10
00858	7	125	243	36	14,5	10
00859	8	125	243	36	15,2	10
00860	9	125	243	36	16,0	10
00861	10	125	243	36	17,2	10
00862	11	125	243	41	19,2	10
00863	12	125	243	41	20,2	10
00864	13	125	243	41	22,2	10
00865	14	125	243	41	23,2	10
00866	15	125	243	41	25,2	10
00867	16	125	243	41	25,2	10
00868	17	125	243	41	27,2	10
Manage for a bound of	I		·			

Manufactured acc. to IEC 60900.

INFOBOX: Combination profiles



PlusMinus.

- The special PlusMinus/Pozidriv profile is ideal for PlusMinus terminal screws.
- The combination profile reduces slipping out and guarantees a higher torque transmission.

Fine screwdriver set PicoFinish® electric

Fine screwdriver PicoFinish electric





Simplifies your work: With a practical plastic holder to hang up or stand on a surface. **Makes handling easier:** Extra-long rotating cap ensures optimum feed. **Increases your efficiency:** Screwdriver handle size concept for optimal balance between precision and control. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. **Increases your efficiency:** Careful workmanship and controlled power transmission thanks to the slim handle with soft grip.

Makes handling easier: Extra-long rotating cap ensures optimum
feed. Increases your efficiency: Screwdriver handle size concept for
optimal balance between precision and control. Offers you full
protection: Each tool individually tested at 10,000 V AC and approved
for 1,000 V AC. Increases your efficiency: Careful workmanship and
controlled power transmission thanks to the slim handle with soft grip.

wiha

Slotted, Phillips, 6 pcs. with holder					
Order-No.					
42989		1			
\ominus	1,5 x 50 / 2,0 x 50 / 2,5 x 65 / 3 x 65				
\oplus	PH00 x 50 / PH0 x 65				

		⊖ Slotted 2270P							
Order-No.	⊖ ∓	—	•1	™mm —	∔ (
42374 1	1,5	50	2,0	152	18	10			
42375 2	2,0	50	2,0	152	18	10			
42376 2	2,5	65	2,5	167	18	10			
42377	3	65	3	167	18	10			
42471 3	3,5	65	3,5	167		10			

Phillips 2271P									
Order-No.	\oplus	—	•:	' ≁ mm'					
42379	PH00	50	2	152	18	10			
42378	PH0	65	3	167	18	10			
42380	PH1	65	4	167	18	10			

INFOBOX: PicoFinish electric



Wiha PicoFinish electric: The VDE-GS tested precision screwdriver.

• The smooth-running turn-cap enables fast turning.

• Imprint with the screw symbol and sizes eases recognition.



L-key with T-handle electric





336N



AILC 6

334N

Simplifies your work: More power when fastening thanks to the leverage from the T-handle design Increases your efficiency: Handle size concept for an optimum balance between torque and control Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

complities your work where perior when actioning marke to the
leverage from the T-handle design Increases your efficiency: Handle
size concept for an optimum balance between torque and control
Offers you full protection: Each tool individually tested at
10,000 V AC and approved for 1,000 V AC.

Simplifies your work: More power when fastening thanks to the

Hex

<u> </u>				, ,	
4	150	176	80	26	10
5	150	182	100	32	10
6	150	182	100	32	10
8	150	182	100	32	10
	4 5 6 8	4 150 5 150 6 150 8 150	4 150 176 5 150 182 6 150 182 8 150 182	4 150 176 80 5 150 182 100 6 150 182 100 8 150 182 100	4 150 176 80 26 5 150 182 100 32 6 150 182 100 32 8 150 182 100 32

Manufactured acc. to IEC 60900.

OHex Order-No.

Order-No.	-					
27932	8	200	202		32	10
27933	10	230	262	100	32	10
27934	13	230	262	100	32	10
27935	17	230	268	120	38	10

Manufactured acc. to IEC 60900.



Single, insulated open-end spanner

the risk of short circuits.



for 1,000 V AC. Protects your material: Fully insulated tool reduces

Improved access: Through the 15° position of jaws, light work is made of fastening even in restricted spaces. Offers you full protection: Each tool individually tested at 10,000 V AC and approved individually tested at 10,000 V AC app



Meets your requirements: Continuously adjustable spanner width for a large application field. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

OAdjustable between 0-30 mm

OAdjustab	m 5590NA					
Order-No.	0	₩mm				
43061	0 - 30	250	1			
Manufactured ac	Manufactured according to EN/IEC 60900.					

Insulated nut driver insert





Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. **Protects your material:** Fully insulated tool reduces the risk of short circuits.

O1/2" hex	agon	head	7208NS
Order-No.	0	₩mm	
43077	10	55	1
43078	11	55	1
43079	12	55	1
43080	13	55	1
43081	14	55	1
43082	17	55	1
43083	19	55	1
43084	22	55	1
43085	24	55	1
43086	27	55	1
43087	32	55	1
Manufactured a	according	to EN/IE	60900.

0			55901
Order-No.	0	₩mm	
43026	6	90	1
43027	7	90	1
43028	8	100	1
43029	9	100	1
43030	10	110	1
43031	11	110	1
43032	12	130	1
43033	13	135	1
43034	14	145	1
43035	15	150	1
43036	16	160	1
43037	17	160	1
43038	18	175	1
43039	19	175	1
43040	22	195	1
43041	24	225	1
43042	27	250	1
43043	30	290	1
43044	32	310	1
Manufactured a	according	g to EN/IE0	C 60900.

Insulated nut driver insert





₹1000 HEC 60

Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. **Protects your material:** Fully insulated tool reduces the risk of short circuits.





Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. **Protects your material:** Fully insulated tool reduces the risk of short circuits.

O3/8" hexagon head					
Order-No.	0	₩mm			
43065	8	45	1		
43066	10	45	1		
43067	11	45	1		
43068	12	45	1		
43069	13	45	1		
43070	14	45	1		
43071	16	45	1		
43072	17	45	1		
43073	18	45	1		
43074	19	47	1		
43075	21	47	1		
43076	22	47	1		
Manufactured a	according	g to EN/IEC	60900.		

O1/4" he	kagon	head	7209NS
Order-No.	0	₩mm	
43088	4	42	1
43089	5	42	1
43090	5,5	42	1
43091	6	42	1
43092	7	42	1
43093	8	42	1
43094	9	42	1
43095	10	42	1
43096	11	42	1
43097	12	42	1
43098	13	42	1
43099	14	42	1
Manufactured a	according	g to EN/IEC	60900.



Insulated nut driver insert

Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Offers you full protection: Each tool individually	y tested at
10,000 V AC and approved for 1,000 V AC.	

●1/2" inte		-	/ 200NH5	
Order-No.	۲	₩mm		
43100	4	120	1	
43101	5	120	1	
43102	6	120	1	
43103	8	120	1	
43104	10	120	1	
Manufactured according to EN/IEC 60900.				

● 3/8" internal hexagon ₩mm Order-No.









Ratchet wrench insulated for nut drivers



Improved access: Deep-set screws can be reached easily. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.


O1/2[■] square adapter for nut driver inserts, insulated

			7208NEX	
Order-No.	ţ	₩mm		
43055	1/2"	125	1	
43056	1/2"	250	1	
Manufactured			2 60900	

ing to EN/IEC 60

○3/8" square adapter for nut driver inserts, insulated

			12011121
Order-No.	 ‡	↑mm	(m)
43057	3/8"	125	1
43058	3/8"	250	1
Manufactured a	according	to EN/IE	C 60900.



7207NRW

Protect your health: Reduction of the risk of injury by increasing the hand working space. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC. Increases your flexibility: Adjustable right or left rotation through switching lever.

Switchable

Order-No.	1	₩mm	₩
43052	3/8"	200	1
43053	1/2"	250	1
Manufactured a			C 60900

7207NEX



Improved access: Deep-set screws can be reached easily. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

			24618T
Order-No.	ţ	₩mm	⊨
43063	1/2"	200	10
43062	3/8"	200	10
Manufactured	according	to EN/IEC 60	900.





Makes handling easier: Can be used as a slim pin or as a powerful T-handle thanks to the double joint. **Increases your efficiency:** 8 key profiles combined in a compact and light tool.

with triangular heads, square heads and double bit 2468						
Order-No.	٥	¢	0			
44001	7-9	3-5	5-8			

Switch cabinet key cross shape



Increases your efficiency: All keys and profiles integrated into one compact, lightweight tool.

with triangular heads, square heads and double bit 24667							
Order-No.	0	0	Ŷ	\ominus	Ð		
36114	5-8	9	3-5	7.0	PH2	1	

INFOBOX: Solid steel cap and hexagon head





- The solid steel cap at the end of the screwdriver handle enables targeted hammering, e.g. to loosen jammed screws.
- The direct connection of the solid steel cap to the blade means that the impact energy is transmitted without any loss.
- Blade includes a hexagon bolster for using a set of spanners for additional torque.



Screwdriver SoftFinish®

Simplifies your work: Striking cap integrated into the handle allows you to strike and lift with the screwdriver. **Makes handling easier:** Easy loosening of tight screws thanks to hex bolster for spanners. **Protect your health:** With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. **Increases your efficiency:** Screwdriver handle size concept for optimal balance between precision and control.

⊖ Slotted with one-piece hexagonal blade and solid steel cap

							530
Order-No.	\ominus	\leftrightarrow		e t	\bigcirc	i ∢ + mm	£
03223		75			-	186	10
03224	4,5•	90	0,8	4,0	-	201	10
03225	5,5	100	1,0	5,0	8	213	10
03226	6,5	125	1,2	6,0		238	10
03228		150	1,2	8,0			5
03230	10,0	175	1,6	8,0	13	296	5
03231	12,0		, -	10,0	16	321	5
03232				10,0	16	371	5
 Additional di 	moneion I	Non-DIN	cizo				

Additional dimension. Non-DIN size.

Phillips with one-piece hexagonal blade and solid steel cap

							531
Order-No.	\oplus	╤╸	•1	\bigcirc	¦• m m		
03237	PH1	80	5,0	8	186	30	10
03238	PH2	100	6,0	10	213	36	10
03239	PH3	150	8,0	13	268	41	10

Pozidriv with one-piece hexagonal blade and solid steel cap

							532
Order-No.	-	☴■	•1	\bigcirc	¦ ∢ →→ mm		
03245	PZ1	80	5,0	8	186	30	10
03246	PZ2	100	6,0	10	213	36	10
03247	PZ3	150	8,0	13	268	41	10







Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. Increases your efficiency: Unique Wiha handle-length concept for optimum balance of torque and control.





Protect your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. Increases your efficiency: Unique Wiha handle-length concept for optimum balance of torque and control.

⊖Slotted with round blade for low-lying screws

								302
Order-No.	\ominus	→ ■	⊖¦	•1	™mm	— ‡		
00684	2,0•	65	0,4	2,0	169	23	10	
00685	2,5	75	0,4	2,5	179	23	10	
00686	3,0•	80	0,5	3,0	184	23	10	
00687	3,0	100	0,5	3,0	204	23	10	
00689	3,0•	150	0,5	3,0	254	23	10	
00690	3,0•	200	0,5	3,0	304	23	10	
32383	3,0	300	0,5	3,0	404	23	5	
00691	3,5	100	0,6	3,5	204	23	10	
26931	3,5•	200	0,6	3,5	304	23	10	
00692	4,0	100	0,8	4,0	211	30	10	
00694	4,0•	150	0,8	4,0	261	30	10	
00695	4,0•	200	0,8	4,0	311	30	10	
00696	4,0•	300	0,8	4,0	411	30	10	
27753	4,5•	80	0,8	4,5	191	30	10	
00697	4,5•	125	0,8	4,5	236	30	10	
00698	5,5	125	1,0	5,5	236	30	10	
00700	5,5	150	1,0	5,5	261	30	10	
00701	5,5∙	200	1,0	5,5	311	30	10	
00702	5,5•	300	1,0	5,5	411	30	5	
32384	6,0•	300	1,0	6,0	418	36	5	
 Additional dir 	mension.	Non-DIN	size.					

Order-No.	\ominus	→	⊖¦	•t	™mm		
27754	6,0	100	1,0	5,5	218	36	10
27755	6,0	150	1,0	5,5	268	36	10
00704	6,5	100	1,2	6,0	218	36	10
00703	6,5	150	1,2	6,0	268	36	10
00706	6,5•	200	1,2	6,0	318	36	10
00708	8,0	150	1,2	7,0	274	41	10
00707	8,0	175	1,2	7,0	299	41	10
00709	8,0	175	1,6	7,0	299	41	5
32399	8,0	300	1,2	7,0	424	41	5
00711	10,0	200	1,6	8,0	324	41	10
32400	10,0	300	1,6	8,0	424	41	5
00712	12,0	250	2,0	8,0	374	41	10
00713	14,0•	250	2,5	11,0	374	41	10
 A statistic scale all' 		Law DINI	- 1				

Additional dimension. Non-DIN size.
DIN ISO 2380.

⊖Slotted with round blade

3022

Screwdriver with LiftUp 25 magnetic bit magazine

Screwdriver with bit magazine magnetic





Simplifies your work: Larger handle – maximum power. Protect your health: No risk of injury, *all bits stowed safely inside the handle.	Ord
Increases your flexibility: Standard bits are also suitable for machine	337
operation.	Θ

SB 380302



assorted with 12 bits, 1/4" in blister pack

Order-No	.
38606	5
\ominus	1 x 5,5
\oplus	1 x PH2
*	1 x PZ1 / 1 x PZ2 / 1 x PZ3
۲	1 x T15 / 1 x T20 / 1 x T25 / 1 x T30
۲	1 x 3,0 / 1 x 4,0 / 1 x 5,0

Phillips slotted with 6 bits, Stubby, 1/4" in blister pack SB 3801 Order-No. Image: Constraint of the state of the stat

TORX[®] with 6 bits, Stubby, 1/4" in blister pack


Order-No.	
33744	5
۲	1 x T10 / 1 x T15 / 1 x T20 / 1 x T25 / 1 x T30 / 1 x T40

SB 3801

Slotted, Pozidriv with 6 bits, Stubby, 1/4" in blister pack SB 3801

Order-No.	(m)
33746	5
\ominus	1 x 4,5 / 1 x 6,5 / 1 x 8,0
	1 x PZ1 / 1 x PZ2 / 1 x PZ3







Three.For all your jobs.





Which machine? Which application? Which bit? The revolutionary Wiha bit concept puts an end to any confusion and presents three bit types which can cover all areas of use.

Only the screw shape is crucial for selecting the bit. The Y bit is ideal for fastening Y-shaped screws with an angle no greater than 90° between the thread and screw head. The T bit is used for T-shaped screws at a 90° angle. If you need to fasten both screw types, then the TY bit is the right choice since this universal bit is suitable for all type of fastenings.

• Increases your efficiency


The specialist with 120x greater lifespan* thanks to optimised bits. * Compared to Wiha standard bits

• Lowers your costs

Bit quick and easy to find thanks to marking – even in dark environments when a UV light is used.

Saves time

No long searches thanks to fluorescent bit, infrequent bit replacement thanks to long lifespan.







Lowers your costs: Bit quick and easy to find thanks to red marking – even in dark environments by using an UV light. Saves time: No long searches thanks to fluorescent bit, infrequent bit replacement thanks to long lifespan. Automatic opening at the push of a button and simple bit change directly in the holder. Increases your efficiency: The all-rounder with 120x greater lifespan* thanks to patented bit technology, suitable for all screws. (*compared to Wiha standard bit)



Pozidriv 1/4" 7-pcs.	SB 7946-TY202
Order-No.	
42099	6
♣ 1 x PZ1 / 5 x PZ2 / 1 x PZ3	

Hexagon 1/4" 7-pcs.		SB 7946-TY303
Order-No.		
42114		6
۲	2 x SW3 / 2 x SW4 / 2 x SW5 / 1 x SW6	

TORX [®] 1/4" 7-pcs.		SB 7946-TY505
Order-No.	<u>í</u>)
42115	e	3
۲	1 x T10 / 1 x T15 / 2 x T20 / 1 x T25 / 1 x T3	30 / 1 x T40

Phillips, Pozidriv, TORX®, 7-pcs., 1/4"		SB 7946-TY903
Order-No.	É	
42116	6	
\oplus	1 x PH2	
*	1 x PZ1 / 1 x PZ2 / 1 x PZ3	
٢	1 x T15 / 1 x T20 / 1 x T25	

Phillips, Pozidriv, TORX®, 7-pcs., 1/4"		SB 7946-TY904
Order-N		
42117		6
Ð	1 x PH2	
*	1 x PZ1 / 1 x PZ2	
۲	1 x T10 / 1 x T15 / 1 x T20 / 1 x T2	5
~		-

Pozidriv, TORX [®] 7-pcs. 1/4" in box		SB 7946-TY905
Order-No		
42118		6
*	1 x PZ2 / 1 x PZ3	
۲	1 x T15 / 1 x T20 / 1 x T25 / 1 x T30 / 1	







Lowers your costs: Bit quick and easy to find thanks to red marking - even in dark environments by using an UV light. Saves time: No long searches thanks to fluorescent bit, infrequent bit replacement thanks to long lifespan. Automatic opening at the push of a button and simple bit change directly in the holder. Increases your efficiency: The all-rounder with 120x greater lifespan* thanks to patented bit technology, suitable for all screws. (*compared to Wiha standard bit)

SB 7945-TY202



Pozidriv 1/4" 8-pcs.

Order-No.	
42098	6
*	1 x PZ1 / 5 x PZ2 / 1 x PZ3
0	1 x Bit holder magnetic extra strong magnet, 1/4"

Hexagon 8-pcs. 1/4"		SB 7945-TY303
Order-No.)
42135	e	3
۲	2 x SW3 / 2 x SW4 / 2 x SW5 / 1 x SW6	
0	1 x Bit holder magnetic extra strong magnet, 1/4"	

TORX® 1/4" 8-pcs.

SB 7945-TY505

Order-No.	
42136	6
۲	1 x T10 / 1 x T15 / 2 x T20 / 1 x T25 / 1 x T30 / 1 x T40
0	1 x Bit holder magnetic extra strong magnet, 1/4"

Phillips, Pozidriv, TORX®, 8-pcs., 1/4" SB 7945-TY903 Order-No. 42137 6 Ð 1 x PH2 ***** 1 x PZ1 / 1 x PZ2 / 1 x PZ3 ۲ 1 x T15 / 1 x T20 / 1 x T25 0 1 x Bit holder magnetic extra strong magnet, 1/4"

Phillips	s, Pozidriv, TORX®, 8-pcs., 1/4"	SB 7945-TY904
Order-N	lo.	
42138		6
\oplus	1 x PH2	
\	1 x PZ1 / 1 x PZ2	
۲	1 x T10 / 1 x T15 / 1 x T20 / 1 x T25	
0	1 x Bit holder magnetic extra strong magne	et, 1/4"

Pozidriv, TORX[®] 1/4" 8-pcs.

Pozidr	iv, TORX® 1/4" 8-pcs.	SB 7945-TY905
Order-N	No. (
42139		6
*	1 x PZ2 / 1 x PZ3	
۲	1 x T15 / 1 x T20 / 1 x T25 / 1 x T30 / 1 x	
0	1 x Bit holder magnetic extra strong magnet, 1/	

XLSelector T bit set, 50 mm

FlipSelector T bit set, 25 mm



Lowers your costs: Bit quick and easy to find thanks to blue marking - even in dark environments by using an UV light. Saves time: No long searches thanks to fluorescent bit, infrequent bit replacement thanks to long lifespan. Increases your efficiency: The specialist with 120x greater lifespan* thanks to optimised bit for T-shaped screws(*compared to Wiha standard bit)



Lowers your costs: Bit quick and easy to find thanks to blue marking - even in dark environments by using an UV light. Saves time: No long searches thanks to fluorescent bit, infrequent bit replacement thanks to long lifespan. Simple and rapid bit removal thanks to clear organisation and automatic opening at the push of a button. Increases your efficiency: The specialist with 120x greater lifespan* thanks to optimised bit for T-shaped screws(*compared to Wiha standard bit)

Phillips, TORX [®] , hex 13-pcs. 1/4"		SB 7948-T950
Order-N		
41831		6
Ð	1 x PH1 / 1 x PH2 / 1 x PH3	
۲	1 x T15 / 1 x T20 / 1 x T25 / 1 x T30 / 1 x T	T40
۲	1 x SW3 / 1 x SW4 / 1 x SW5 / 1 x SW6	
0	1 x Bit holder magnetic extra strong magnet, 1/4	

Hexagon 16-pcs. 1/4"

Order-No.	
41825	6
۲	3 x SW3 / 3 x SW4 / 3 x SW5 / 3 x SW6
0	1 x Bit holder magnetic extra strong magnet, 1/4"

SB 7947-T303

SB 7947-T906

Phillips, Pozidriv, TORX®, 13-pcs., 1/4"

Order-No.	
41824	6
\oplus	1 x PH1 / 3 x PH2 / 1 x PH3
*	1 x PZ2
۲	1 x T10 / 1 x T15 / 1 x T20 / 1 x T25 / 1 x T30 / 1 x T40
0	1 x Bit holder magnetic extra strong magnet, 1/4"

----as

assorted 1/4" 13-pcs.		SB 7947-T999
Order-No	. (
41826		6
Ð	1 x PH1 / 1 x PH2 / 1 x PH3	
*	1 x PZ2	
۲	1 x T15 / 1 x T20 / 1 x T25 / 1 x T30 / 1 x T	40
۲	1 x SW4 / 1 x SW5 / 1 x SW6	
0	1 x Bit holder magnetic extra strong magnet, 1/4	

XLSelector T bit set, 25 mm



Lowers your costs: Bit guick and easy to find thanks to blue marking - even in dark environments by using an UV light. Saves time: No long searches thanks to fluorescent bit, infrequent bit replacement thanks to long lifespan. Increases your efficiency: The specialist with 120x greater lifespan* thanks to optimised bit for T-shaped screws(*compared to Wiha standard bit)

Phillips, TORX [®] , hex 31-pcs. 1/4"		SB 7948-T999
Order-No.		
41830		6
Ð	2 x PH1 / 4 x PH2 / 2 x PH3	
۲	2 x T10 / 2 x T15 / 4 x T20 /	2 x T25 / 2 x T30 / 2 x T40
	2 x SW3 / 2 x SW4 / 2 x SW5	/ 2 x SW6
0	1 x Bit holder magnetic extra stro	ong magnet, 1/4"



XLSelector Y bit set, 50 mm



Lowers your costs: Bit quick and easy to find thanks to yellow marking - even in dark environments by using an UV light. Saves time: No long searches thanks to fluorescent bit, infrequent bit replacement thanks to long lifespan. Increases your efficiency: The specialist with 120x greater lifespan* thanks to optimised bit for Y-shaped screws(*compared to Wiha standard bit)

Phillips, Poziariv, TORA*, 13-pcs., 1/4*		SB 7948-Y950
Order-No.		
41834		6
Ð	2 x PH2	
*	1 x PZ1 / 2 x PZ2 / 1 x PZ3	
۲	1 x T10 / 1 x T15 / 1 x T20 / 1 x T25 /	
0	1 x Bit holder magnetic extra strong magne	

XLSelector Y bit set, 25 mm

Dhilling Desideiv TODV® 12 per 1/4



Lowers your costs: Bit quick and easy to find thanks to yellow marking - even in dark environments by using an UV light. Saves time: No long searches thanks to fluorescent bit, infrequent bit replacement thanks to long lifespan. Increases your efficiency: The specialist with 120x greater lifespan* thanks to optimised bit for Y-shaped screws(*compared to Wiha standard bit)

TORX® 3	1-pcs. 1/4" SB 7948-Y505
Order-No.	
41833	6
۲	3 x T10 / 6 x T15 / 6 x T20 / 6 x T25 / 6 x T30 / 3 x T40
0	1 x Bit holder magnetic extra strong magnet, 1/4"

Phillips, Pozidriv, TORX®, 31-pcs., 1/4"

Order-No.	
41832	6
Ð	1 x PH1 / 4 x PH2 / 1 x PH3
*	2 x PZ1 / 4 x PZ2 / 2 x PZ3
۲	2 x T10 / 3 x T15 / 3 x T20 / 3 x T25 / 3 x T30 / 2 x T40
0	1 x Bit holder magnetic extra strong magnet, 1/4"

FlipSelector Y bit set, 25 mm



Lowers your costs: Bit quick and easy to find thanks to yellow marking - even in dark environments by using an UV light. Saves time: No long searches thanks to fluorescent bit, infrequent bit replacement thanks to long lifespan. Simple and rapid bit removal thanks to clear organisation and automatic opening at the push of a button. Increases your efficiency: The specialist with 120x greater lifespan* thanks to optimised bit for Y-shaped screws(*compared to Wiha standard bit)

Pozidriv 1/4" 13-pcs.		SB 7947-Y202
Order-No.		
41829		6
*	2 x PZ1 / 8 x PZ2 / 2 x PZ3	
0	1 x Bit holder magnetic extra strong ma	

TORX[®] 1/4" 13-pcs. Order-No.

41828	6
۲	2 x T10 / 2 x T15 / 3 x T20 / 2 x T25 / 2 x T30 / 1 x T40
0	1 x Bit holder magnetic extra strong magnet, 1/4"

Phillips, Pozidriv, TORX®, 13-pcs., 1/4"

Phillips, Pozidriv, TORX®, 13-pcs., 1/4"		SB 7947-Y904	
Order-N			
41827		6	
Ð	2 x PH2		
*	1 x PZ1 / 2 x PZ2 / 1 x PZ3		
۲	1 x T10 / 1 x T15 / 1 x T20 / 1 x T25 /	1 x T30 / 1 x T40	
0	1 x Bit holder magnetic extra strong magnet		

SB 7948-Y904

SB 7947-Y505

(mai)

Bit set XLSelector Standard 25 mm

Bit set FlipSelector Standard 25 mm



Meets your requirements: Robust and precise bits for general fastening in trade and industry. **Saves time:** Simple and quick recognition of profile sizes thanks to contrasting laser marking. **Increases your efficiency:** All standard 25 mm bits organised in a compact, space-saving design.

assorted 1/4" 31-pcs. 7948-0	
Order-No.	
29417	5
\ominus	1 x 4,5 / 1 x 5,5 / 1 x 6,5
Ð	2 x PH1 / 4 x PH2 / 1 x PH3
*	2 x PZ1 / 5 x PZ2 / 1 x PZ3
۲	2 x T10 / 2 x T15 / 2 x T20 / 3 x T25 / 2 x T30 / 1 x T40
0	1 x Bit holder magnetic, 58 mm 1/4"
assorted 1/4" 31-pcs. 7049 007	

assorte	u 1/4" 31-pcs.	7948-927
Order-No	Э.	
29416		5
Ð	1 x 0 / 1 x 1 / 1 x 2 / 1 x 3 / 1 x 4	
\bullet	1 x 4 / 1 x 6 / 1 x 8 / 1 x 10	
۲	1 x TR2,0 / 1 x TR2,5 / 1 x TR3,0 / 1 x T 1 x TR6,0	R4,0 / 1 x TR5,0 /
Ð	1 x 6 / 1 x 8 / 1 x 10	
۲	1 x T8H / 1 x T9H / 1 x T10H / 1 x T15H T25H / 1 x T27H / 1 x T30H / 1 x T40H	/ 1 x T20H / 1 x
	1 x #1 / 1 x #2 / 1 x #3	
0	1 x CentroFix quick release holder, magnetic,	style E 6.3.



Mixed, 1/4", 13-pcs. with belt clip in blister pack

SB	7947-999

Order-No	. 💼
39083	5
\ominus	1 x 5,5
Ð	1 x PH2
*	1 x PZ1 / 1 x PZ2 / 1 x PZ3
۲	1 x T15 / 1 x T20 / 1 x T25 / 1 x T30
۲	1 x 3,0 / 1 x 4,0 / 1 x 5,0
0	1 x Bit holder magnetic, 58 mm 1/4"

Slotted, Phillips, Pozidriv, 13-pcs., 1/4" with belt clip, in blister pack

0110, 111 01		SB 7947-005
Order-No.		
39049		5
\ominus	1 x 5,5	
Ð	1 x PH1 / 3 x PH2 / 1 x PH3	
*	1 x PZ1 / 4 x PZ2 / 1 x PZ3	
0	1 x Bit holder magnetic, 58 mm 1/4"	

Phillips, Pozidriv, TORX®, 13-pcs., 1/4" with belt clip, in blister pack

chp, m bi	SB 7947-904
Order-No.	⊨
39060	5
Ð	2 x PH2
*	1 x PZ1 / 2 x PZ2 / 1 x PZ3
۲	1 x T10 / 1 x T15 / 1 x T20 / 1 x T25 / 1 x T30 / 1 x T40
0	1 x Bit holder magnetic, 58 mm 1/4"

Pozidriv, TORX[®] 1/4" 13-pcs.

7947-905

Order-No.	
39041	10
*	1 x PZ1 / 2 x PZ2 / 1 x PZ3
۲	1 x T10 / 1 x T15 / 2 x T20 / 2 x T25 / 1 x T30 / 1 x T40
0	1 x Bit holder magnetic, 58 mm 1/4"

TORX[®], 13-pcs., 1/4" with belt clip, in blister pack

Order-No	. 🔒
39056	5
۲	1 x T7 / 1 x T8 / 1 x T9 / 1 x T10 / 2 x T15 / 2 x T20 / 2 x T25 / 1 x T30 / 1 x T40
0	1 x Bit holder magnetic, 58 mm 1/4"

TORX[®] Tamper Resistant (with drill hole), 13-pcs., 1/4" with belt clip, in blister pack

	SB /947-505TR
Order-No.	
39057	5
۲	1 x T7H / 1 x T8H / 1 x T9H / 1 x T10H / 2 x T15H / 2 x T20H / 2 x T25H / 1 x T30H / 1 x T40H
0	1 x Bit holder magnetic, 58 mm 1/4"

Hex, 11-pcs., 1/4" with belt clip in blister pack

Order-No.	
39059	5
۲	1 x 1,5 / 1 x 2,0 / 1 x 2,5 / 2 x 3,0 / 2 x 4,0 / 1 x 5,0 / 1 x 6,0 / 1 x 8,0
0	1 x Bit holder magnetic, 58 mm 1/4"

SIT (for Assy® and Pias screws), 13-pcs., 1/4" 7947-995 Order-No. Image: Constraint of the screws of the

High-performance offset screwdriver with quick release holder 1/4"



Increases your safety: Variably settable stabiliser arm. **Increases your efficiency:** Unlimited access to hard-to-reach screws thanks to the 105°-angled tool head.

O1/4" in blister pack

-					24020
Order-No.	0	۲		max. Nm	
32310	1/4	1/4	165	57	1

Bit holder CentroFix mechanically lockable

SB 7947-505

SB 7947-902



Simplifies your work: Ideal for all applications due to the non-magnetic locking mechanism . **Increases your efficiency:** Extremely secure and tight zero-play hold of bits.

O ^{1/4} "				7148C
Order-No.	0	۲	™mm	Ê
32477	1/4	1/4	60	10

Bit holder CentroFix Super Slim mechanically lockable



Saves time: Automatic bit locking mechanism upon insertion. **Increases your efficiency:** Unlimited access to deep-set screws thanks to extreme slimline design.



24628

∩1/4", magnetic

O1/4", ma	-			7148 CS
Order-No.	0	۲	¦ ∗ —→I mm	É
39134	1/4	1/4	66	1

Bit holder magnetic, clamping with retaining ring



Simplifies your work: Unrestricted access to low-lying screws thanks to bit holder lengths of up to 250mm. **Increases your efficiency:** Unlimited access to deep-set screws thanks to extreme slimline design.

0	7143
Order-No. O 🖲 🛗	
01913 1/4 1/4 72 10	
36092 1/4 1/4 100 5	
34306 1/4 1/4 150 5	
36093 1/4 1/4 200 5	
36094 1/4 1/4 250 5	





Phillips 1/4"

Meets your requirements: Robust and precise bits for general fastening in trade and industry. Saves time: Simple and quick recognition of profile sizes thanks to contrasting laser marking. Increases your efficiency: Best rotation characteristics for stable fastening processes.

\ominus Slotted	1/4"			7040
Order-No.	\ominus	i ∗ → i mm	⊖ ;	
33961	2,5	70	0,4	5
01790	3,0	50	0,5	5
33962	3,0	70	0,5	5
01792	3,5	50	0,6	5
33963	3,5	70	0,6	5
01791	4,0	50	0,5	5
01794	4,0	50	0,8	5
33964	4,0	70	0,8	5
01793	4,5	50	0,6	5
01795	5,5	50	0,8	5
01796	5,5	50	1,0	5
33965	5,5	70	1,0	5
01798	6,5	50	1,2	5
33966	6,5	70	1,2	5
01799	8,0	50	1,2	5
01800	8,0	50	1,6	5

Order-No.	Ð	i • mm
31960	PH00	50
31961	PH00	70
31962	PH00	90
32105	PH0	50
35456	PH0	70
35457	PH0	90
33703	PH1	50
01803	PH1	70
04126	PH1	90
23213	PH1	110
23219	PH1	127
22509	PH1	150
33704	PH2	50
01805	PH2	70
04009	PH2	90
05800	PH2	110
06888	PH2	127
22510	PH2	150
33705	PH3	50
04010	PH3	70
04127	PH3	90
23215	PH3	110
23217	PH3	127
22511	PH3	150

7041 Z

PlusMinus/Phillips 1/4"

Ψ.	us/Phillips		7049PHM
Order-No.	\oplus	™mm	
32490	SL/PH1	50	5
32491	SL/PH1	70	5
32686	SL/PH1	90	5
32492	SL/PH2	50	5
32493	SL/PH2	70	5
32687	SL/PH2	90	5

/ 1/4"		7042 Z
*	l ≁ mm ⁱ	
PZ0	50	5
PZ0	70	5
PZ0	90	5
PZ1	50	5
PZ1	70	5
PZ1	90	5
PZ1	110	5
PZ1	127	5
PZ1	150	5
PZ2	50	5
PZ2	70	5
PZ2	90	5
PZ2	110	5
PZ2	127	5
PZ2	150	5
PZ3	50	5
PZ3	70	5
PZ3	90	5
PZ3	110	5
PZ3	127	5
PZ3	150	5
	 ✤ ₽Z0 PZ0 PZ1 PZ2 PZ2 PZ2 PZ2 PZ3 	 ➡ ➡

90 wiha 🐵

Pozidriv 1/4"

PlusMinus/Pozidriv 1/4"

Order-No.	۲	¦ ∢ mm	
32494	SL/PZ1	50	5
32495	SL/PZ1	70	5
32688	SL/PZ1	90	5
32496	SL/PZ2	50	5
32497	SL/PZ2	70	5
32689	SL/PZ2	90	5

TORX®	ball en	id 1/4"	
order-No.	۲	i • mm	
2409	Т9	50	5
2410	T10	50	5
2416	T10	70	5
2417	T15	50	5
2418	T15	70	5
2411	T20	50	5
2419	T20	70	5
2412	T25	50	5
2421	T25	70	5
2413	T27	50	5
2414	T30	50	5
2423	T30	70	5
2415	T40	50	5

Order-No. Immin Immin Immin 34452 T10 50 5 34453 T15 50 5 34454 T20 50 5 34455 T25 50 5 34456 T30 50 5 34457 T40 50 5	TORX®	Magic	Spring®	1/4" 704
34452 T10 50 5 34453 T15 50 5 34454 T20 50 5 34455 T25 50 5 34456 T30 50 5	Order-No.	۲	i• ── >I mm	
34453 T15 50 5 34454 T20 50 5 34455 T25 50 5 34456 T30 50 5	34452	T10	50	5
34454 T20 50 5 34455 T25 50 5 34456 T30 50 5	34453	T15	50	5
34455 T25 50 5 34456 T30 50 5	34454	T20	50	5
34456 T30 50 5	34455	T25	50	5
34457 T40 50 5	34456	T30	50	5
	34457	T40	50	5

70		1/4"	TORX® 1
	l ∢	۲	Order-No.
5	50	T1	39184
5	50	T2	39185
5	50	T3	39186
5	50	T4	39187
5	50	T5	32299
5	50	Т6	32302
5	70	Т6	33709
5	90	T6	33717
5	150	Т6	38370
5	50	Τ7	32303
5	70	Τ7	33710
5	90	Τ7	33718
5	150	Τ7	38371
5	50	T8	32304
5	70	T8	33711

3IP

4IP

4IP

5IP

5IP

6IP

6IP

7049PZM	Order-No.	۲	l ∢ ⊢ mm	
	33719	Т8	90	5
	36327	T8	150	5
	32305	Т9	50	5
	33712	Т9	70	5
	33720	Т9	90	5
	38372	Т9	150	5
	32306	T10	50	5
	33713	T10	70	5
7045BE	33721	T10	90	5
	33725	T10	110	5
	33726	T10	150	5
	32307	T15	50	5
	33714	T15	70	5
	33722	T15	90	5
	33727	T15	110	5
	33728	T15	150	5
	32308	T20	50	5
	33715	T20	70	5
	33723	T20	90	5
	33729	T20	110	5
	33730	T20	150	5
	32309	T25	50	5
	33716	T25	70	5
	33724	T25	90	5
7045R	33731	T25	110	5
	33732	T25	150	5
	33920	T27	50	5
	33921	T27	70	5
	33922	T27	90	5
	33923	T30	50	5
	33924	T30	70	5
•••••	33925	T30	90	5
	33926	T30	110	5
	33927	T30	150	5
7045 Z	33928	T40	50	5
	33929	T40	70	5
	33930	T40	90	5
	33931	T40	110	5
	33932	T40	150	5
	TORX P	LUS®	1/4"	7046 Z
<u>-</u>	Order-No.	۲	i • mm ⁱ	10402
	39195	1IP	50	5
	39196	2IP	50	5
	00100	11 ک		J

Order-No.	۲	¦ ₄ —→I mm	
26002	7IP	50	ξ
23195	8IP	50	ξ
31975	8IP	90	2
23197	9IP	50	ξ
23199	10IP	50	ξ
31977	10IP	90	ξ
23201	15IP	50	Ę
25553	15IP	90	ξ
23203	20IP	50	ξ
39200	20IP	90	Ę
23205	25IP	50	Ę
39201	25IP	90	Ę
23207	27IP	50	Ę
39202	27IP	90	ξ
23209	30IP	50	ξ
39203	30IP	90	Ę
23211	40IP	50	Ę
39204	40IP	90	Ę

MagicRing® hex 1/4"

145 3,0 50 5 147 4,0 50 5 149 5.0 50 5
147 4,0 50 5
148 0,0 00 0
151 6,0 50 5

7043R Z

7043 Z

Hexagon 1/4"

	******	************************************
Order-No.	۲	™
05301	1,5	50
05302	2,0	50
34554	2,0	70
39178	2,0	90
05303	2,5	50
34555	2,5	70
39179	2,5	90
04194	3,0	50
34556	3,0	70
39180	3,0	90
04195	4,0	50
34557	4,0	70
39181	4,0	90
04196	5,0	50
34558	5,0	70
39182	5,0	90
04197	6,0	50
34559	6,0	70
39183	6,0	90
04198	8,0	50
34560	8,0	70
	•••••••	••••••••

Square 1/4

7045 Z TR


Square	1/4"			7048 Z
Order-No.		۲	¦ ∢ →→ mm	
06637	#1	2,3	50	5
39206	#1	2,3	90	5
06638	#2	2,8	50	5
39207	#2	2,8	90	5
06639	#3	3,3	50	5
39208	#3	3,3	90	5

Hexagonal ball end 1/4" 7047R Z ¦**∢**mm Order-No. ۲ 25739 3,0 50 5 25740 4,0 50 5 25741 5,0 50 5 25742 6,0 50 5

🕀 Torq-Se	t® 1/4		7049 TS
Order-No.	Ð	mm	É
22596	4	50	5
22597	5	50	5
22598	6	50	5
22599	8	50	5
22600	10	50	5

$\textcircled{\mbox{stat}}$ TORX* Tamper Resistant (with hole) 1/4*

Order-No.	۲	™mm
21045	T7H	50
21047	T8H	50
20218	Т9Н	50
20219	T10H	50
39188	T10H	90
24867	T15H	50
39189	T15H	90
20220	T20H	50
39190	T20H	90
20221	T25H	50
39191	T25H	90
20222	T27H	50
39192	T27H	90
20223	T30H	50
39193	T30H	90
20224	T40H	50
39194	T40H	90





Perfect order when fast work is required.





Perfect order and easy handling - the ErgoStar L-key holder provides both: Rotating a single L-key in the holder means that all other keys rotate at the same angle! Keys sitting next to each other no longer need to be disentangled. Instead, all keys are ready for removal with one turn - as fast and easy as never before. The keys of the ErgoStar also help to make work significantly easier: The Wiha L-key set, made of fully hardened chrome vanadium steel, includes an innovation that will convince everyone. A spring steel ring holds hexagon screws reliably.

• Simplifies your work


The ball end facilitates access to screws and allows you to work at an angle of up to 25°.

Increases your efficiency Wiha MagicRing[®] retaining function holds all screws firmly in place – without any magnets.

• Makes handling easier Always the correct key when you need it.

• Saves time

Ensures order: removing and targeted insertion in the holder is child's play.





Simplifies your work: The ball end facilitates access to screws and allows you to work at an angle of up to 25°. Lowers your costs: Reduces the risk of forgetting and leaving keys inside a machine and causing damage. Makes handling easier: Always the correct key when you need it. Increases your efficiency: Coloured L-keys quick and easy to find - also in dark environments thanks to fluorescent paint visible in UV light. The required key width can be quickly found thanks to colour coding. Wiha MagicRing® holding feature holds all hex screws in place without a magnet.

369RF

hexag	onal ball Magicring® 9-pcs. in flourescen	t colour
Order-I	No.	
41979		5
	1,5 / 2 / 2,5	
	3 / 4 / 5 / 6 / 8 / 10	
MagicRir	a® from size 3 mm.	

Based on ISO 2936L.





colour

INFOBOX:

- Coloured bits and ErgoStar with coloured L-keys light up under a UV light.
- Ensuring misplaced tools are quickly and easily found again.
- The Wiha flashlight with a UV light makes the perfect complement to coloured fluorescent tools.







360R

Simplifies your work: The ball end facilitates access to screws and allows you to work at an angle of up to 25°. Lowers your costs: Highly durable thanks to high-quality, chrome-plated L-key surface to prevent corrosion. Makes handling easier: Always the correct key when you need it. Saves time: Ensures order: removing and targeted insertion in the holder is child's play. Increases your efficiency: Wiha MagicRing® holding feature holds all hex screws in place without a magnet.

Hexagonal ball end MagicRing [®] matt c	chrome-plated 9-pcs.
--	----------------------

Order-No		
37351		5
	1,5 / 2 / 2,5	
	3 / 4 / 5 / 6 / 8 / 10	
MagicRing®	from size 3 mm.	

Based on ISO 2936L





Wiha MagicRing®

- Spring steel ring reliably holds hex screws in place
- An innovation, which will benefit each user.

L-key set in Compact holder



Hexagonal ball end, 11-pcs., matt chrome-plated in blister pack

in blister	pack			SB 369 H11
Order-No.				
36454			5	
	1,5 / 2 / 2,5 / 3 / 4	/5/6/7/	8 / 9 / 10	
Including 7 m Based on IS	m and 9 mm special sizes. O 2936L.			



Simplifies your work: The ball end facilitates access to screws and allows you to work at an angle of up to 25°. **Makes handling easier:** Always the correct key when you need it. **Saves time:** Ensures order: removing and targeted insertion in the holder is child's play.

L-key set in Compact holder



Hexagonal ball end, 9-pcs., matt chrome-plated in blister pack

		SB 369 H9
Order-No.		
02292		5
	1,5 / 2 / 2,5 / 3 / 4 / 5 / 6 /	8 / 10
Deserved are 100		

Based on ISO 2936L.

TORX[®] ball end. 13-pcs.. black oxidised

L-key set in ErgoStar holder

		366BE
Order-No	o. (
36487		5
۲	T5 / T6 / T7 / T8	
۲	T9 / T10 / T15 / T20 / T25 / T27 / T30 /	/ T40 / T45
TOBX® ball	end from size T9	

INFOBOX: TORX[®] ball end





Wiha TORX® ball end

- With optimised TORX[®] ball end geometry
- Increased strength thanks to the special cold forming on a system developed by Wiha especially for this purpose.
- Allows fastening and unfastening at angles up to 25°.
- Simple insertion of the tool/bit and fastening/ unfastening, especially in hard-to-reach positions.
- Broad product range: As an L-key, as a bit and as a SoftFinish® screwdriver.

INFOBOX: Ball end hex



Wiha hexagonal ball end

• The ball end can be rotated by up to 25° in both clockwise and anti-clockwise direction.





Increases your efficiency: Thread-conserving removal of the screw without damage.

Hex, 16- _I	ocs. with spiral drill bit in box	405
Order-No.		
03988	10	
$\mathbf{\Theta}$	2,3 / 2,8 / 3,4 / 4,5 / 5,7 / 6,8 / 9,0 / 11,0	
	2,0 / 2,5 / 3,0 / 4 / 5 / 6 / 8 / 10	

Protect your health:

Special DynamicJoint[®] design reduces effort required for cutting.

Protect your health

Wiha pliers are kind to the muscles and ergonomic to work with, permanently reducing wrist strain.

Offers you full protection

Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.




Trimming / cutting A cut above the rest with Wiha.

A precise cut at the right time – no problem for Wiha diagonal cutters, heavy-duty diagonal cutters, cable cutters, cable shears and combination pliers. With the perfect combination of high-quality materials and ergonomic comfort, Wiha VDE-tools withstand the toughest demands. Production is in accordance to the state-of-the-art quality management guidelines. A special heat treatment and inductive hardening of the parts under high stress ensure a long lifespan. The precise interaction of the joints and the exacting quality workmanship of the blades and gripping surfaces ensure the highest level of functionality.

All Wiha products have been designed according to the latest findings in ergonomics. Ergonomic handles and well thought-out soft and hard zone distribution makes for workthat protects the hands from strain and is comfortable.

"With BiCut[®], I always have sufficient power when cutting - and without aching fingers." Timo Schweitzer





Double your power at the push of a button.






Precise and safe work – at double the power: no problem for the Wiha BiCut[®] Professional electric diagonal cutters. If there is not enough power when cutting, or if cutting is laborious, a simple push of a button is all that is required and the cutting power is doubled. Another push of the button, and the power is halved again – easy! This significantly reduces the risk of cramp or slippage when applying too much force. The extra-wide back for the handle, with perfectly distributed soft and hard zones, ensures the optimum ergonomics. The new Wiha BiCut[®] has already been awarded with the "reddot award 2014winner" for outstanding design quality.

- Increases your efficiency Two pliers in one - 200 % power at the touch of a button, available at any time.
- Protect your health Requires less force and reduces pressure on the wrists.
- Offers you full protection Each tool individually tested at 10,000 V AC and

Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.





BiCut[®] Professional electric high-performance diagonal cutters with DynamicJoint[®]

X






Z 18 0 06

Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. Protect your health: Requires less force and reduces pressure on the wrists. Increases your efficiency: Two pliers in one - 200 % power at the touch of a button, available at any time. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.



Switchable

-



• When working with cutting pliers - beware of wire ends flying off. Please wear safety glasses.

INFOBOX: Cutting capacity info

*	Example
1 - 5	copper,aluminium
6 - 10	Iron nails
11 - 15	Screws
16 - 21	Hardened spring steel








Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. Increases your safety: Wiha combination pliers enable safe, non-slip gripping in all work situations. Protect your health: Special DynamicJoint[®] design reduces effort required for cutting. Increases your efficiency: Wiha needle nose pliers with extra-long plier head for inserting low-lying components. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Combin	nation pliers, needle nose pliers, diagonal cutters 3-pcs.
Order-N	io. 🔒
26852	1
Trimmi	ng / cutting
X	Professional electric diagonal cutters with DynamicJoint [®] 160 x 6 1/2" (43335)
Supply	ing / holding
	Combination pliers Professional electric with Dynamic Joint® and OptiGrip with extra long cutting edge, VDE and GS tested / 180 mm, 7" (26708
•	Needle nose pliers Professional electric with cutting edge straight shape, VDE and GS tested / 200 mm, 8" (26727)

Manufactured acc. to IEC 60900.



Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. Protect your health: Special DynamicJoint® design reduces effort required for cutting. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Simplifies your work: Up to 40% more cutting force thanks to optimised leverage. Lowers your costs: Durable thanks to highquality, chrome-plated plier surface to prevent corrosion. Protect your health: Special DynamicJoint® design reduces effort required for cutting. Reduces strain from continuous work thanks to opening spring. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

					Z 12 1 06
Order-No.	₩mm	↓	≫	Ømm	
43326	140	5 1/2"	16	1,6	5
43335	160	6 1/2"	17	2	5
43340	180	7"	18	2,3	5

with switchable opening spring

with switc		•	• ·	-	Z 16 3 06	
Order-No.	₩mm	↓	≫	Ømm	Ĥ	
40921	160	6,5	17	2	5	
41274	180	7	18	2,3	5	
41279	200	8	19	2,5	5	
DIN ISO 5749, Manufactured acc, to IEC 60900,						

INFOBOX: **DynamicJoint®**





Wiha DynamicJoint[®] – A new dimension in strength and durability

- Innovative: Optimised joint construction.
- Effective: Minimal power loss means less force needed for cutting.
- Permanent: Optimal performance even after thousands of cuts.







Z 50 1 06

Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. **Protect your health:** Reduces strain from continuous work thanks to opening spring. **Increases your** efficiency: Clean work thanks to cable cutting without crushing. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

with switchable opening spring

	₩mm		mm²		
43660	180	7	50	5	
43662	210	8 1⁄4	60	5	
Manufactured acc. to IEC 60900.					

INFOBOX:

Heavy-duty diagonal cutters & Cable cutters





with switchable opening spring

- Up to 40% more cutting force thanks to optimised leverage.
- Opening spring with on/off function for fatigue-free work.
- Opening spring can be activated with just one hand.



Combination pliers Professional electric with $\mbox{DynamicJoint}^{\otimes}$ and $\mbox{OptiGrip}$

High-leverage combination pliers Professional electric with DynamicJoint[®] and OptiGrip



Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. Protect your health: Special DynamicJoint[®] design reduces effort required for cutting. Increases your efficiency: A secure, non-slip grip in all standard work situations. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.



Simplifies your work: Up to 40% more cutting force thanks to optimised leverage. Lowers your costs: Durable thanks to highquality, chrome-plated plier surface to prevent corrosion. Protect your health: Special DynamicJoint® design reduces effort required for cutting. Increases your efficiency: A secure, non-slip grip in all standard work situations. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

with extra long cutting edge

Order-No.	₩mm	₩	≫	Ømm		
26705	160	6 ½	15	1,6	5	
26708	180	7	16	1,8	5	
26711	200	8	17	2	5	
DIN ISO 5746. Manufactured acc. to IEC 60900.						

with extra long cutting edge Z 02 0						
Order-No.	₩mm	↓	≫	Ømm	Ê	
26714	200	8	18	2,3	5	
26717	225	9	19	2,5	5	
DIN ISO 5746. Manufactured acc. to IEC 60900.						

INFOBOX: **OptiGrip**



7 01 0 06



Wiha OptiGrip – optimal grip due to newly designed gripping surfaces

- A firm hold: The "triple-point support" protects the workpiece from twisting or slipping.
- Highly effective: Optimum grip even with large jaw opening – and at the same time significantly less force needed.
- A wide selection: Now in standard Wiha combination pliers and high leverage combination pliers.





Meets your requirements: For almost flush cutting of soft and semi-hard wires. Protect your health: Reduced risk of injury thanks to smooth burr-free finished results, for example with cable ties.

Ømm

0,8

Meets your requirements: For the smooth and flush cutting of plastics. Protect your health: Reduced risk of injury thanks to smooth burr-free finished results, for example with cable ties.

with opening spring without bevelled edge Z 15 0 01							
Order-No.	₩mm	₩	>				
37402	125	5	2	5			
37403	160	6 ½	3	5			
DIN ISO 5743.		•••••••	••••••				

Shear for electricians

with opening spring

mm

125

Order-No.

DIN ISO 5749.

36189

т

5

>

7



Simplifies your work: Large blade notch and micro-toothed cutting edge prevent the cable from slipping out of the shears. Increases your safety: Protective cover with retaining clip for safe carrying. Makes handling easier: The combination between a sturdy blade and an ergonomic handle with extra large handle holes enable users to make a flawless cut into cables up to 50 mm². Increases your efficiency: Shear for electricians with stripping, skinning, crimping & cutting-tolength functions in a single tool.

with crimp function in blister pack Z 71 7 06 Order-No. mm mm² 41923 5 160 50

Hacksaw electric

7 44 3 01

5

wihe



Lowers your costs: Durable and sturdy thanks to bimetallic saw blade. Makes handling easier: The ergonomic handle is suitable for both right- and left-handed users* Using the plastic screw, the saw blade can be changed quickly and easily. Increases your efficiency: The fine-toothed saw blade allows a clean cut, for example on plastic pipes and metal cable ducts. Offers you full protection: Each tool individually tested at 10,000 V AC and usable for 1,000 V AC.

insulated with three saw blades 150 mm

Order-No.		↔		47
		mm	[SB]	
43125	150	280	х	1

W



2/6176

antibula lanotanatori

Increases your efficiency

Wiha gripping pliers enable safe, non-slip gripping in all work situations.

Protect your health:

DynamicJoint[®]: Special DynamicJoint[®] design reduces effort required for cutting.

Offers you full protection

Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.



Supplying / holding Supplying – completely relaxed.

In the supplying and holding working procedures, Wiha pliers prove to be clever helpers for relaxed and efficient work. For instance, the OptiGrip of the combination and high-leverage combination pliers ensure optimal and secure holding using an innovative gripping surface: The unique 'triple-point support' protects the work piece from twisting or slipping. The circlip pliers from the Classic Series with their MagicTips[®] precision tips made of high-performance steel offer considerable additional safety and stability. Their special latching function is especially useful against in preventing the circlips jumping off.


"You only have to lose a circlip,and then you realize the benefits of Wiha pliers!" Frank Scheck







Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. Increases your efficiency: Extralong plier head for inserting low-lying components. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.





Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. Protect your health: Special DynamicJoint® design reduces effort required for cutting. Increases your efficiency: A secure, non-slip grip in all standard work situations. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

with cuttin		Z 05 0 06				
Order-No.	₩mm	↔	≫	Ømm		
26720	160	6 ½	16	1,2	5	
26727	200	8	17	1,6	5	
DIN ISO 5745. Manufactured acc. to IEC 60900.						

with extra long cutting edge

Order-No.	₩mm	₩	≫	Ømm	£
26705	160	6 ½	15	1,6	5
26708	180	7	16	1,8	5
26711	200	8	17	2	5

7 01 0 06

DIN ISO 5746. Manufactured acc. to IEC 60900.

Needle nose pliers Professional electric



Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. Increases your efficiency: Extralong plier head for inserting low-lying components. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

with cutting edge curved shape, approx. 40°

Order-No.	₩mm	₩	≫	Ømm			
26728	160	6 ½	16	1,2	5		
26729	200	8	17	1,6	5		
DIN ISO 5745. Manufactured acc. to IEC 60900.							

Z 05 1 06

Water pump pliers Professional electric



Meets your requirements: Permanently stable through box joint with double guidance. Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. Increases your efficiency: Fast and simple adjustment of pliers with push button. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

with push	buttor	Z 22 0 06			
Order-No.	₩mm	₩	0;	0:	
37450	250	10	2	50	5

Order-No.	mm		0,	Ο,				
37450	250	10	2	50	5			
DIN ISO 8976. Manufactured acc. to IEC 60900.								



Long flat-nose pliers Professional electric



Simplifies your work: Up to 40% more cutting force thanks to optimised leverage. Lowers your costs: Durable thanks to highquality, chrome-plated plier surface to prevent corrosion. Protect your health: Special DynamicJoint® design reduces effort required for cutting. Increases your efficiency: A secure, non-slip grip in all standard work situations. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.



Increases your efficiency: Extra-long plier head for inserting low-lying components. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

with extra long cutting edge

z 02 0 C							
Order-No.	₩mm	↓	≫	Ømm			
26714	200	8	18	2,3	5		
26717	225	9	19	2,5	5		
DIN ISO 5746. Manufactured acc. to IEC 60900.							

			Z 07 0 06			
Order-No.	₩mm	₩	É			
26732	160	6 ½	5			
DIN ISO 5745. Manufactured acc. to IEC 60900.						

Water pump pliers Professional electric

Meets your requirements: Permanently stable through box joint with double guidance. **Lowers your costs:** Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Long round-nose pliers Professional electric



Increases your efficiency: Extra-long plier head for inserting low-lying components. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

box type					Z 21 0 06
Order-No.	₩mm		0;	0:	
33520	250	10	2	50	5
DIN ISO 8976	Manufa	ctured ac	c. to IEC	60900.	

			Z 09 0 06			
Order-No.	₩mm	₩				
26735	160	6 ½	5			
DIN ISO 5745. Manufactured acc. to IEC 60900.						





Simplifies your work: Self-locking at AF 17 and above. Also suitable for left-handed users as operated without side push button. Lowers your costs: Minimises wear and prevents damage to sensitive surfaces thanks to smooth, parallel jaws and backlash-free handling. Saves space: Replaces a set of metric and imperial open-ended spanners. Protect your health: Compaction and bending tasks take minimum effort thanks to manual force increased tenfold. Saves time: Safe, rapid setting directly on the work piece with no need to press any buttons. Ratchet function allows users to fasten screws instantly with a simple glide. Improved access: Slender design thanks to button-free setting enables it to be used in confined working environments, minimising the risk of damage.

				Z 25 0 01
	→ +	→	0;	
40923 25	50 1	10	46	6

INFOBOX: Plier wrench






- Required width setting directly on the work piece with no need to press any buttons.
- Ratchet principle allows users to fasten screws rapidly with a simple glide.
- Thanks to its slim design and button-free setting, it is ideal for use in tight spaces.
- Smooth, parallel-acting jaws prevent damage on sensitive surfaces.







For those situations where a good grip is essential.





They make our circlip pliers for the Classic series head and shoulders above the rest: MagicTips[®], the precision tips made of high-performance steel. Additionally hardened, they offer a high level of resistance to wear and therefore ensure a long shelf-life. The special latching feature is as unique as it is useful, and prevents jumping of the circlips and therefore any reworking in the motor or working space caused by lost circlips. And thanks to the non-slip pliers handle, precise work is also guaranteed in unfavourable situations. Hard as nails, durable, safe, accurate: These qualities make Wiha MagicTips[®] circlip pliers useful and indispensable helpers during day-to-day work.

- Lowers your costs Prevents damage caused by lost circlips in the work area.
- Saves time Safe and sturdy grip on circlips.









Lowers your costs: Prevents damage caused by lost circlips in the work area. Saves time: Safe and sturdy grip on circlips.

Circlip pliers 4-pcs.

Circlip	Z 99 0 007 01
Order-I	No.
34708	1
Suppl	ying / holding
C	Circlip pliers Classic with MagicTips® For inner rings (drill holes) J 1, 140 mm (34689) / J 2, 180 mm (34690)
C	Circlip pliers Classic with MagicTips [®] For outer rings (shafts) A 1, 140 mm (34699) / A 2, 185 mm (34700)
 with sa 	fety latching function

• DIN ISO 5254 & 5256





INFOBOX: **MagicTips**[®]

Wiha MagicTips[®] – Top of their class.

- Maximum grip: The special latching function preventing jumping away of the safety rings makes the Wiha circlip pliers truly unique.
- Hard as steel: Additional hardening of tips means high wear resistance and therefore excellent durability.
- Precise: Precision tips of high performance steel for maximum grip and high stability.



Classic circlip pliers with MagicTips[®], straight (°)

Lowers your costs: Prevents damage caused by lost circlips in the work area. Saves time: Safe and sturdy grip on circlips.

Classic circlip pliers with MagicTips®, angled



Lowers your costs: Prevents damage caused by lost circlips in the work area. Saves time: Safe and sturdy grip on circlips.

For inner rings (drill holes)

Order-No.	Тур	₩mm	₩	C	
34688	JO	140	5 ½	8-13	5
34689	J 1	140	5 ½	12-25	5
34690	J 2•	180	7	19-60	5
34691	J 3•	220	9	40-100	5
34692	J 4•	305	12	85-140	5
 with safety lat 					

DIN ISO 5256.

Classic circlip pliers with MagicTips®, straight



Lowers your costs: Prevents damage caused by lost circlips in the work area. Saves time: Safe and sturdy grip on circlips.

₩ $^{\circ}$ Order-No. Тур **™**m

For inner rings (drill holes)

34693	J 01		5 ½	8-13	5
34694	J 11	140	5 ½	12-25	5
34695	J 21•	180	7	19-60	5
34696	J 31•	220	9	40-100	5
34697	J 41•	305	12	85-140	5
 with safety la 			•••••••	•••••••••••••••••••••••••••••••••••••••	

DIN ISO 5256.

Z 33 4 01

Classic circlip pliers with MagicTips®, angled



Lowers your costs: Prevents damage caused by lost circlips in the work area. Saves time: Safe and sturdy grip on circlips.

For outer rings (shafts)

For outer rings (shafts) Z 34 4									
Order-No.	Тур	₩mm	€ II	ů					
34698	A 0	140	5 1⁄2	7-10	5				
34699	A 1	140	5 1⁄2	10-25	5				
34700	A 2•	185	7	19-60	5				
34701	A 3•	240	9	40-100	5				
34702	A 4●	300	12	85-140	5				
 with safety la 									

DIN ISO 5254.

For outer rings (shafts)

Order-No.	Тур	₩mm	₩	C	₩
34703	A 01	140	5 ½	7-10	5
34704	A 11	140	5 1⁄2	10-25	5
34705	A 21•	185	7	19-60	5
34706	A 31•	240	9	40-100	5
34707	A 41•	300	12	85-140	5
 with safety la 		ction			

DIN ISO 5254.

Z 33 5 01

▤



Z 34 5 01

Protect your health

Wiha pliers are kind to the muscles and ergonomic to work with, permanently reducing wrist strain.

Lowers your costs

Thanks to the integration and combination of several operations in one tool, this removes the need for several tools.

Offers you full protection

Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.




Stripping/ insulating / crimping For tidy cable ends.

Wiha crimping tools guarantee clean, precise crimping of components. Wiha offers a range of crimp tools for a great variety of applications, including wire-end sleeve, male blade connectors as well as cable eyes and contacts. A special highlight are the automatic crimping pliers with hex crimping for processing wire-end sleeves with and without insulating collars. Due to the large crimping range from 0.08 – 16 mm² only one tool is required for working on wire-end sleeves with larger and smaller diameters. At the same high quality level as the the automatic crimping pliers, the crimp tools for cable eyes, contacts and male blade connectors also guarantee absolute crimping process safety coupled with comfortable work thanks to their impact-reducing plastic handles. The "electrical engineering accessories" product range offers the ideal solutions to complement the crimp tools, including superior quality innovatively packaged wire-end sleeves and connectors.

"Due to the large crimping range of the automatic crimping pliers I always have the right tool for practically all wire-end sleeves at my disposal. Even with wire-end sleeves with small diameters, the crimping process is problem-free thanks to the feed aid."

Ralf Flaig





Three functions – one tool.





Less tools means less weight, better handling and more efficient work. The Wiha Professional electric TriCut installation pliers combine three tools in one, ideal for the three operations cutting-to-length, stripping and skinning. And it does all this while saving you energy: Due to an ergonomically shaped, specifically angled plier head forged from high-quality steel. The low-wear, inlaid joint with heavy-duty riveting makes the pliers particularly robust and durable, and production and testing according to IEC 60900, VDE/ GS certification and individual piece testing at 10,000 V AC ensures uncompromising safety.



• Simplifies your work

The angled shape of the head allows work to be performed in hard-to-reach spaces such as installation boxes.

• Increases your efficiency Three tools in one. Saves 60% volume and 50% less weight for 100% efficiency.

• Lowers your costs

Now you only need one tool for three tasks: cutting to length, stripping and skinning.

• Offers you full protection Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.







Simplifies your work: The angled head allows you to work in hard-to-reach places such as installation sockets. Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. Saves money: Now you only need one tool for three tasks: cutting to length, stripping and skinning. Increases your efficiency: Three tools in one. Saves 60% volume and 50% less weight for 100% efficiency. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Stripping diagonal cutters Professional electric with DynamicJoint®







Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. Saves money: Two tools in one for cutting to length and skinning. Protect your health: Special DynamicJoint[®] design reduces effort required for cutting. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

					Z 14 0 06
Order-No.	₩mm	₩	≫	Ømm	
26745	160	6 ½	13	1,6	5
DIN ISO 5749.					

INFOBOX: Cutting capacity info

*	Example
1 - 5	copper,aluminium
6 - 10	Iron nails
11 - 15	Screws
16 - 21	Hardened spring steel



Stripping pliers Professional electric

s to high-quality, chrome-plated

Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion. **Protect your health:** Reduces strain from continuous work thanks to opening spring. **Increases your efficiency:** Skinning of several cross-sections due to wide variety of settings. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

					Z 55 0 06
Order-No.	₩mm	↓ II	Ø	mm²	
26847	160	6 ½	5	10	5
DIN ISO 5743.	Manufa	ctured ac	c. to IEC	C 60900.	

Stripping tool



Simplifies your work: Perfect handling thanks to ergonomic handle shape. Saves time: Automatic setting from round to length cutting. Increases your efficiency: Skinning of all standard cross-sections through continuous setting. Saves time: Colour code 1 (FR)

with self-rotating trailing blade 24622							
Order-No.	₩mm	₩	Ømm				
35969	165	6½	4,0-28	1			



Simplifies your work: Enables stripping in hard-to-reach places such as installation sockets.

for round cable, in blister pack	

Order-No.	₩mm	↔	mm²	SB	(11)
36052	125	5	8-13	х	1

Cable stripping knife



Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

straight cutting edge for round cables in blister pack	24680
	24680

Order-No.	₩mm	₩	SB	₩
38798	200	8	Х	1
Manufactured	acc. to IE	C 6090).	



Lowers your costs: No damage to wire insulation through sliding shoe on tip.

hooked blade with sliding shoe for round cable, in blister pack

-				24678		
Order-No.	⁺mm		SB)			
36053	200	8	х	1		
Manufactured acc. to IEC 60900.						

Stripping tool

24677



Simplifies your work: Enables incremental cable stripping and skinning in hard-to-reach places such as installation sockets.

for coaxial cable, in blister pack 24676						
Order-No.	₩mm	↔	mm²	SB		
36051	110	4¼	4,8-7,5	х	1	



Stripping tool automatic

Spare blade and gripping jaw set



Lowers your costs: Long-lasting and robust thanks to metal blade insert. Protect your health: Damper enclosed for large cable crosssections to reduce recoil and protect wrists. Saves time: Blades quickly exchanged by immediately available replacement blades in the handle. Increases your efficiency: Automatic stripping pliers for a wide range of cables between 0.03 and 16 mm².

Spare part: Spare blade and gripping jaw set for automatic stripping pliers 42062

up to 16 mm ² in blister pack Z 57 0 06						
Order-No.	₩mm	↔	mm²	AWG	SB	
42062	200	8	0,03 - 16	32-5	x	1

for automatic stripping tool	Z 57 0 001 06K
Order-No.	
42162	1



Stripping tool, automatic up to 16mm²



f



- These pliers can handle a wide range of cables, thus combining two pairs of pliers in one.
- The supplied damper can be used to lessen recoil caused by larger cable gauges, such as those greater than 6 mm², thus helping to protect wrists.
- Precise cutting to length thanks to adjustable longitudinal stop.
- Integrated hand protection along the cutting edge guards against injury.



Stripping tool automatic

Crimp tool



Simplifies your work: Unrestricted access to hard-to-reach work areas thanks to extremely slim handle shape. Saves money: Two tools in one for cutting to length and skinning. Increases your efficiency: Damage-free stripping thanks to automatic adjustment to cable diameter.



wihn

Increases your safety: Safe working through automatic pressing adjustment.

up to 6 mm² in blister pack

						24010
Order-No.	₩mm	↔	mm²	AWG	SB	
36050	190	7 ½	0,2-6,0	24-10	х	1

for wire-er	nd slee	ves	Z 62 0 06			
Order-No.	₩mm	mm²	AWG			
33844	220	0,14-16	26-5	1		
For processing of wire-end sleeves with and without isolating collar according to DIN 46228, EN 50027.						



Lowers your costs: An integrated lever enables users to interrupt the crimping process at any time to protect the pliers. Increases your safety: Safe work through feed aid prevents crimping the plastic cover of wire-end sleeves. Makes handling easier: Thanks to hexagonal crimping, small wire-end sleeves no longer get caught. Increases your efficiency: Automatic adjustment of wire-end sleeve size with suitable crimping force for a large coverage area of 0.08-16mm².

for wire-end sleeves hex crimping Z 62 0 0						
Order-No.	₩mm	mm²	AWG			
41246	210	0,08-16	28-5	1		
For processing twin sleeves and wire-end sleeves with or without insulating collar as per DIN 46228 & EN 50027						

Crimp tool

for wire-end sleeves

24675



Increases your safety: Safe working through automatic pressing adjustment.

for insulated terminals and connectors Z 62 0 06				
Order-No.	mm	mm ²	AWG	É
33841	220		20-10	1

For processing of red, blue and yellow isolated terminals, pin-end terminals, contact pins, contact pin sleeves, circular pins, circular pin sleeves, batch connectors and parallel connectors according to DIN 46234.



Crimp tool



Increases your safety: Safe working through automatic pressing adjustment.

Crimping pliers Professional electric



Meets your requirements: Safe pressing in marked trapezoidal/ semi-circular profiles. Lowers your costs: Durable thanks to highquality, chrome-plated plier surface to prevent corrosion. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

for non-insulated cable eye with closed sleeve

Order-No.	₩mm	mm²	AWG			
33843	220	0,1-16	26-6	1		
For processing of non-isolated contact pins and contact pin sleeves according to DIN 46247 for standardised, solderless electrical connections.						

Z 60 0 06 Order-No. mm ίΠ, mm² 35861 145 5 3⁄4 0,25-2,5 5 DIN ISO 5743. Manufactured acc. to IEC 60900.



Increases your safety: Safe working through automatic pressing adjustment.

Crimping pliers Professional electric

Z 62 0 06



Meets your requirements: Safe pressing in marked trapezoidal/ semi-circular profiles. Lowers your costs: Durable thanks to highquality, chrome-plated plier surface to prevent corrosion. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

for non-insulated male blade connectors

Tor non-insulated male blade connectors Z 62 0						
Order-No.	₩mm	mm²	AWG			
33842	220	0,25-6	24-10	1		

For processing of non-isolated contact pins and contact pin sleeves according to DIN 46247 for standardised, solderless electrical connections.

				Z 60 0 06
Order-No.	⁺mm	↓ II	mm²	
35862	180	7	0,25-16	5
			c. to IEC 60900.	










For a safe connection.





crimping

There are many pitfalls in conventional wiring installation. All-too-familiar problems include wires skinned incorrectly, twisted crimps in the pliers or poorly pressed sleeves. The comprehensive set by Wiha provides you with the right professional tools, including a wide selection of the most commonly used connectors and wire end sleeves, clearly arranged in an assortment case for portable use or for vehicles.Wiha's automatic stripping pliers promise to deliver "Skinning made easy". Users can skin cables ranging between 0.03 and 16 mm² with just one set of pliers. The automatic crimping pliers with hex crimping can handle wire-end sleeves between 0.08 and 16 mm² and twin wire end sleeves up to 10 mm². The automatic crimp tool for insulated cable eyes and contacts is designed for a crimping range between 0.5 and 6 mm² and thus covers most applications in the small and medium cable gauge range. Wiha's standard-compliant wire end sleeves and connectors offer heat resistance up to 105 °C.

- Increases your process safety
 Consistently high processing quality for permanent safe contact.
- Makes handling easier Quick, easy cable insertion thanks to funnel sleeve.
- Increases your safety
 Cable breakages prevented thanks to protected individual wires. High thermal resistance up to 105 °C.
- Increases your efficiency

Automatic stripping and crimping tool for a wide range of coverage from 0.08 - 16 mm². Comprehensive assortment of wire end ferrules and cable connectors in a clear and mobile assortment box.

Increases your work quality
 Gas-tight connections thanks to perfect
 combination of professional tools and high quality
 connectors.







Increases your efficiency: Comprehensive assortment of wire end ferrules and cable connectors in a clear and mobile assortment box. **Increases your work quality:** Gas-tight connections thanks to perfect combination of professional tools and high quality connectors.

with cable connectors 2,600 pcs. colour code DIN in assortment box

Order-N	0.	
43984		1
•	Automatic crimp tool for wire-end sleeves hex crimping / 210 mm, 0,08-16 mm ² (41246)	
	Stripping tool, automatic up to 16mm² / 200 mm, 8" (42062)	
•	Crimping tools for isolated cable eyes and contacts. / 220 mm, 0,5-6 mm ² (33841)	
	Wire end ferrules with plastic collar	
	400 x 0,50 / 400 x 0,75 / 400 x 1,00 / 300 x 1,50 / 200 x 2,50 / 100 x 4,00 / 50 x 6,00 / 50 x 10,0 / 50 x 16,0	
	Crimp-type cable socket, ring-shaped, insulated	
	50 x 0,50 - 1,00; M4 / 50 x 0,50 - 1,00; M5 / 50 x 1,50 - 2,50; M5 / 50 x 1,50 - 2,50; M6 / 50 x 4,00 - 6,00; M6 /	0 x 4,00 - 6,00; M8
	Butt connectors, insulated 50 x 0,50 - 1,00 / 50 x 1,50 - 2,50 / 50 x 4,00 - 6,00	
	Female blade connectors, insulated 50 x 0,50 - 1,00; 6,3 x 0,8 / 50 x 1,50 - 2,50; 6,3 x 0,8	
	Male blade connectors, insulated 50 x 0,50 - 1,00; 6,3 x 0,8 / 50 x 1,50 - 2,50; 6,3 x 0,8	

With connection elements, 2,600 units, colour code 1 (FR), in assortment box

Order-No.	
43982	1
•	Automatic crimp tool for wire-end sleeves hex crimping / 210 mm, 0,08-16 mm ² (41246)
	Stripping tool, automatic up to 16mm ² / 200 mm, 8" (42062)
•	Crimping tools for isolated cable eyes and contacts. / 220 mm, 0,5-6 mm ² (33841)
	Wire end ferrules with plastic collar
	400 x 0,50 / 400 x 0,75 / 400 x 1,00 / 300 x 1,50 / 200 x 2,50 / 100 x 4,00 / 50 x 6,00 / 50 x 10,0 / 50 x 16,0
	Crimp-type cable socket, ring-shaped, insulated
	50 x 0,50 - 1,00; M4 / 50 x 0,50 - 1,00; M5 / 50 x 1,50 - 2,50; M5 / 50 x 1,50 - 2,50; M6 / 50 x 4,00 - 6,00; M6 / 50 x 4,00 - 6,00; M8
	Butt connectors, insulated 50 x 0,50 - 1,00 / 50 x 1,50 - 2,50 / 50 x 4,00 - 6,00
	Female blade connectors, insulated 50 x 0,50 – 1,00; 6,3 x 0,8 / 50 x 1,50 – 2,50; 6,3 x 0,8
	Male blade connectors, insulated 50 x 0,50 - 1,00; 6,3 x 0,8 / 50 x 1,50 - 2,50; 6,3 x 0,8

93001011



With connection elements, 2,600 units, colour code 2 (DE), in assortment box

Order-No.	
43983	1
•	Automatic crimp tool for wire-end sleeves hex crimping / 210 mm, 0,08-16 mm ² (41246)
	Stripping tool, automatic up to 16mm ² / 200 mm, 8" (42062)
•	Crimping tools for isolated cable eyes and contacts. / 220 mm, 0,5-6 mm ² (33841)
	Wire end ferrules with plastic collar
	400 x 0,50 / 400 x 0,75 / 400 x 1,00 / 300 x 1,50 / 200 x 2,50 / 100 x 4,00 / 50 x 6,00 / 50 x 10,0 / 50 x 16,0
	Crimp-type cable socket, ring-shaped, insulated
	50 x 0,50 - 1,00; M4 / 50 x 0,50 - 1,00; M5 / 50 x 1,50 - 2,50; M5 / 50 x 1,50 - 2,50; M6 / 50 x 4,00 - 6,00; M6 / 50 x 4,00 - 6,00; M8
	Butt connectors, insulated 50 x 0,50 - 1,00 / 50 x 1,50 - 2,50 / 50 x 4,00 - 6,00
	Female blade connectors, insulated 50 x 0,50 – 1,00; 6,3 x 0,8 / 50 x 1,50 – 2,50; 6,3 x 0,8
	Male blade connectors, insulated 50 x 0,50 - 1,00; 6,3 x 0,8 / 50 x 1,50 - 2,50; 6,3 x 0,8

Insert boxes set





Spare part: Insert boxes for assortment box connector elements 43982, 439823 and 43984

16-pcs. for assortment box connector elements	930019930019
Order-No.	
43995	1





Simplifies your work: Easy removal and safe storage thanks to the pocket box with latching twist cap. Increases your efficiency: Automatic stripping and crimping tool for a wide range of coverage from 0.08 - 16 mm². Ideal for mobile use thanks to compact, stackable pocket box. Increases your work quality: Gas-tight connections thanks to perfect combination of professional tools and high quality connectors.

with wire end ferrules 500 pcs. colour code DIN in L-Boxx Mini

with wi	re end ferrules 500 pcs. colour code DIN in L-Boxx Mini	930010930010
Order-No	0.	
43987		1
•	Automatic crimp tool for wire-end sleeves hex crimping 210 mm, 0,08-16 mm ² (41246)	
	Stripping tool automatic up to 16 mm ² in blister pack 200 mm, 8" (42062)	
	Wire end sleeves with plastic collar set (43904) 50 x 0,50 / 100 x 0,75 / 100 x 1,00 / 100 x 1,50 / 50 x 2,50	
	Wire end sleeves with plastic collar set (43903) 50 x 4,00 / 20 x 6,00 / 20 x 10,0 / 10 x 16,0	

With wire end sleeves, 500 units, colour code 1 (FR), in L Boxx Mini		930010930010	
Order-No			
43985		1	
•	Automatic crimp tool for wire-end sleeves hex crimping 210 mm, 0,08-16 mm ² (41246)		
	Stripping tool automatic up to 16 mm ² in blister pack 200 mm, 8" (42062)		
	Twin wire end sleeves with plastic collar set (43900) 50 x 0,50 / 100 x 0,75 / 100 x 1,00 / 100 x 1,50 / 50 x 2,50		
	Twin wire end sleeves with plastic collar set (43899) 50 x 4,00 / 20 x 6,00 / 20 x 10,0 / 10 x 16,0		

With wire end sleeves, 500 units, colour code 2 (DE), in L Boxx Mini

Order-No.	
43986	1
•	Automatic crimp tool for wire-end sleeves hex crimping 210 mm, 0,08-16 mm ² (41246)
	Stripping tool automatic up to 16 mm ² in blister pack 200 mm, 8" (42062)
	Wire end sleeves with plastic collar set (43902) 50 x 0,50 / 100 x 0,75 / 100 x 1,0 0 / 100 x 1,50 / 50 x 2,50
	Wire end sleeves with plastic collar set (43901) 50 x 4,00 / 20 x 6,00 / 20 x 10,0 / 10 x 16,0

930010930010





Simplifies your work: Easy removal and safe storage thanks to the pocket box with latching twist cap. **Increases your safety:** Cable breakages prevented thanks to protected individual wires. High thermal resistance up to 105 °C. **Makes handling easier:** Organisation system for your workshop or storage area gives you simple and quick access. Quick, easy cable insertion thanks to funnel sleeve. **Increases your efficiency:** Extensive assortment of wire sleeves with mobile organiser box sets and a selection of the most popular sizes in polyester bags. Ideal for mobile use thanks to compact, stackable pocket box. **Increases your process safety:** Consistently high processing quality for permanent safe contact.

Colour code DIN, 0.5 - 10 mm² in polyester bag and 0.5 - 16 mm² in organiser box

der-No	0.	
007		1
	Wire end sleeves with plastic collar set 8 units 50 x 0,50 / 100 x 0,75 / 100 x 1,00 / 100 x 1,50 / 50 x 2,50	
	Wire end sleeves with plastic collar set 8 units 50 x 4,00 $/$ 20 x 6,00 $/$ 20 x 10,0 $/$ 10 x 16,0	
	Wire end ferrules with plastic collar	
	80 units 100 x 0,50 / 80 units 100 x 0,75 / 60 units 100 x 1,00 / 60 units 100 x 1,50 / 30 units 100 x 2,50 / 30 uni	ts 100 x 4,00 /
	30 units 100 x 2,50 / 20 units 100 x 6,00 / 20 units 50 x 100	

Colour code 1 (FR), 0.5 - 10 mm² in polyester bag and 0.5 - 16 mm² in organiser box

Order-N	o. 🔒
44005	1
	Wire end sleeves with plastic collar set 8 units 50 x 0,50 / 100 x 0,75 / 100 x 1,00 / 100 x 1,50 / 50 x 2,50
	Wire end sleeves with plastic collar set 8 units 50 x 4,00 / 20 x 6,00 / 20 x 10,0 / 10 x 16,0
	Wire end ferrules with plastic collar
	80 units 100 x 0,50 / 80 units 100 x 0,75 / 60 units 100 x 1,00 / 60 units 100 x 1,50 / 30 units 100 x 2,50 / 30 units 100 x 4,00 /
	30 units 100 x 2,50 / 20 units 100 x 6,00 / 20 units 50 x 100

Colour code 2 (DE), 0.5 - 10 mm² in polyester bag and 0.5 - 16 mm² in organiser box

Order-No	Э.	
44006		1
	Wire end sleeves with plastic collar set 8 units 50 x 0,50 / 100 x 0,75 / 100 x 1,00 / 100 x 1,50 / 50 x 2,50	
	Wire end sleeves with plastic collar set 8 units 50 x 4,00 $/$ 20 x 6,00 $/$ 20 x 10,0 $/$ 10 x 16,0	
	Wire end ferrules with plastic collar	
	80 units 100 x 0,50 / 80 units 100 x 0,75 / 60 units 100 x 1,00 / 60 units 100 x 1,50 / 30 units 100 x 2,50 / 30 u	nits 100 x 4,00 /
	30 units 100 x 2,50 / 20 units 100 x 6,00 / 20 units 50 x 100	

C000C

C000A



Wire end sleeves with plastic collar set

Wire end sleeves with plastic collar set





Simplifies your work: Easy removal and safe storage thanks to the pocket box with latching twist cap. **Increases your safety:** Cable breakages prevented thanks to protected individual wires. High thermal resistance up to 105 °C. **Makes handling easier:** Quick, easy cable insertion thanks to funnel sleeve. **Increases your efficiency:** Ideal for mobile use thanks to compact, stackable pocket box. **Increases your process safety:** Consistently high processing quality for permanent safe contact.

Simplifies your work: Easy removal and safe storage thanks to the pocket box with latching twist cap. **Increases your safety:** Cable breakages prevented thanks to protected individual wires. High thermal resistance up to 105 °C. **Makes handling easier:** Quick, easy cable insertion thanks to funnel sleeve. **Increases your efficiency:** Ideal for mobile use thanks to compact, stackable pocket box. **Increases your process safety:** Consistently high processing quality for permanent safe contact.

0.5–2.5 mm², 400 units, DIN colour code, in dispenser			
Order-No). 🖬		
43904	8		
50	0 x 0,50 / 100 x 0,75 / 100 x 1,00 / 100 x 1,50 /	50 x 2,50	

4–16 mm ² , 100 units, DIN colour code, in dispenser COOOC						
Order-No.						
43903	8					
50 x 4,00 / 20 x 6,00 / 20 x 10,0 / 1	,					

0.5–2.5 mm², 400 units, colour code 1 (FR), in dispenser	C000A

Oldel-NO.	
43900	8
50 x 0,50 / 100 x 0,75 / 100 x 1,00 /	/ 100 x 1,50 / 50 x 2,50

0.5–2.5 mm², 400 units, colour code 2 (DE), in dispenser

Order-No.	
43902	8
50 x 0,50 / 100 x 0,75 / 100 x 1,00	

4–16 mm ² , 100 units, colour code 1 (FR) in dispenser	C000A

	0000,1
Order-No.	
43899	8
50 x 4,00 / 20 x 6,00 / 20 x 10,0 / 1	

C000B 4-16 mm², 100 units, colour code 2 (DE) in dispenser C000B

Order-No.	
43901	8
50 x 4,00 / 20 x 6,00 / 20 x 10,0 /	





Simplifies your work: Easy removal and safe storage thanks to the pocket box with latching twist cap. **Increases your safety:** Cable breakages prevented thanks to protected individual wires. High thermal resistance up to 105 °C. **Makes handling easier:** Quick, easy cable insertion thanks to funnel sleeve. **Increases your efficiency:** Ideal for mobile use thanks to compact, stackable pocket box. **Increases your process safety:** Consistently high processing quality for permanent safe contact.


2x 2 x 0.75 - 2 x 2.5 mm ² , 200 units, DIN colour code, in					
dispenser	001C				
Order-No.					

Order-INO.		
43907		8
	2 x 0,75 / 50 x 2 x 1,00 / 50 x	

2 x 0.75 - 2 x 2.5 mm ² , 200 units, colour code 1 (FR), in dispenser						
Order-No.						
43905	8					
50 x	2 x 0,75 / 50 x 2 x 1,00 / 50 x 2 x 1,50 / 50 x 2 x 2,50					

2 x 0.75 - 2 x 2.5 mm ² , 200 units, colour code 2 (DE), in dispenser						
Order-No.						
43906 8						
50 x 2 x 0,75 / 50 x 2 x 1,00 / 50 x 2 x 1,50 / 50 x 2	x 2,50					





Increases your safety: Cable breakages prevented thanks to protected individual wires. High thermal resistance up to 105 °C. Makes handling easier: Quick, easy cable insertion thanks to funnel sleeve. Increases your process safety: Consistently high processing quality for permanent safe contact.

											COOOA
Order-No.	√C	mm²	AWG	D1	D2	L1	L2	S1	S2	I I	
43908	brown●	0,14	26	0,7	1,6	12	6	0,15	0,25	100	40
43909	purple•	0,25	24	0,75	1,8	12	6	0,15	0,25	100	40
43910	light pink•	0,34	22	0,8	2	12	6	0,15	0,25	100	40
43911	white	0,50	20	1	2,6	14	8	0,15	0,25	100	40
43912	blue	0,75	18	1,2	2,8	14	8	0,15	0,25	100	40
43913	red	1,00	18	1,4	3	14	8	0,15	0,25	100	60
43914	black	1,50	16	1,7	3,5	14	8	0,15	0,25	100	60
43915	grey	2,50	14	2,2	4,2	14	8	0,15	0,25	100	50
43916	orange	4,00	12	2,8	4,8	17	10	0,2	0,3	100	30
43917	green	6,00	10	3,5	6,3	20	12	0,2	0,3	100	20
43918	brown	10,00	8	4,5	7,6	22	12	0,2	0,4	50	20
43919	ivory	16,00	6	5,8	8,8	24	12	0,2	0,4	50	20
* Additional	dimonsion	Non D				•••••••					

* Additional dimension. Non-DIN size.

Wire end ferrules with plastic collar, Colour code 2 (DE)

											C000B
Order-No.	√C	mm²	AWG	D1	D2	L1	L2	S1	S2	<u></u> ↓	
43920	grey∙	0,14	26	0,7	1,6	12	6	0,15	0,25	100	40
43921	light blue•	0,25	24	0,75	1,8	12	6	0,15	0,25	100	40
43922	turquoise•	0,34	22	0,8	2	12	6	0,15	0,25	100	40
43923	orange	0,50	20	1	2,6	14	8	0,15	0,25	100	40
43924	white	0,75	18	1,2	2,8	14	8	0,15	0,25	100	40
43925	yellow	1,00	18	1,4	3	14	8	0,15	0,25	100	60
43926	red	1,50	16	1,7	3,5	14	8	0,15	0,25	100	60
43927	blue	2,50	14	2,2	4,2	14	8	0,15	0,25	100	50
43928	grey	4,00	12	2,8	4,8	17	10	0,2	0,3	100	30
43929	black	6,00	10	3,5	6,3	20	12	0,2	0,3	100	20
43930	ivory	10,00	8	4,5	7,6	22	12	0,2	0,4	50	20
43931	green	16,00	6	5,8	8,8	24	12	0,2	0,4	50	20
* Additional	dimension. N	Non-DIN	l size.							•••••••••••	



Wire end ferrules with plastic collar, Twin wire end ferrules with plastic collar


Order-No.	√C	mm ²	AWG	D1	D2	L1	L2	S1	S2	<u>∖</u> †	€
43911	white	0,50	20	1	2,6	14	8	0,15			40
43996	grey	0,75	18	1,2	2,8	14	8	0,15	- , -		40
43913	red	1,00	18	1,4	3	14	8	0,15	0,25	100	60
43914	black	1,50	16	1,7	3,5	14	8	0,15	0,25	100	60
43927	blue	2,50	14	2,2	4,2	14	8	0,15	0,25	100	50
43928	grey	4,00	12	2,8	4,8	17	10	0,2	0,3	100	30
43932	gelb	6,00	10	3,5	6,3	20	12	0,2	0,3	100	20
43933	red	10,00	8	4,5	7,6	22	12	0,2	0,4	50	20
43934	blue	16,00	6	5,8	8,8	24	12	0,2	0,4	50	20

INFOBOX: Wire end ferrules with plastic collar



				Col	our code 1	1 (FR)	Co	olour code a	2 (DE)	Co	lour code	DIN
mm²	mm	Ъ				Order-No.	√C		Order-No.			Order-No
0,14	6	100	40		brown●	43908		grey∙	43920			
0,25	6	100	40		purple●	43909	-	light blue•	43921			
0,34	6	100	40		light pink•	43910		turquoise•	43922	••••••		
0,50	8	100	40		white	43911		orange	43923		white	43911
0,75	8	100	40		blue	43912		white	43924		grey	43996
1,00	8	100	60		red	43913		yellow	43925		red	43913
1,50	8	100	60		black	43914		red	43926		black	43914
2,50	8	100	50	=	grey	43915	-	blue	43927		blue	43927
4,00	10	100	30		orange	43916	- 3	grey	43928	-	grey	43928
6,00	12	100	20		green	43917	=	black	43929		yellow	43932
10,00	12	50	20		brown	43918	E	ivory	43930		red	43933
16,00	12	50	20		ivory	43919		green	43931		blue	43934

C000C



Increases your safety: Cable breakages prevented thanks to protected individual wires. High thermal resistance up to 105 °C. **Makes handling easier:** Quick, easy cable insertion thanks to funnel sleeve. **Increases your process safety:** Consistently high processing quality for permanent safe contact.

												C001A
Order-No.	₹C	mm²	AWG	D1	D2	D3	L1	L2	S1	S2	<u>∖</u> †	
43935	white	2 x 0,50	2 x 20	1,4	2,5	4,7	15	8	0,15		100	30
43936	blue	2 x 0,75	2 x 18	1,7	2,8	5	15	8	0,15	0,25	100	20
43937	red	2 x 1,00	2 x 18	1,95	3,4	5,4	15	8	0,15	0,3	100	20
43938	black	2 x 1,50	2 x 16	2,2	3,6	6,6	16	8	0,15	0,3	100	30
43939	grey	2 x 2,50	2 x 14	2,8	4,2	7,8	18,5	10	0,2	0,3	100	20
43940	orange	2 x 4,00	2 x 12	3,7	4,9	8,8	23	12	0,2	0,4	50	20
43941	green	2 x 6,00	2 x 10	4,8	6,9	10	26	14	0,2	0,4	50	15
43942	brown	2 x 10,00	2 x 8	6,4	7,2	13	26	14	0,2	0,4	25	20
		- ,	-	- /		-	-		- /	- /	-	-

Twin wire end ferrules with plastic collar, Colour code 2 (DE)

												C001B
Order-No.	√C	mm²	AWG	D1	D2	D3	L1	L2	S1	S2	<u></u>]↓	
43943	orange	2 x 0,50	2 x 20	1,4	2,5	4,7	15	8	0,15	0,25	100	30
43944	white	2 x 0,75	2 x 18	1,7	2,8	5	15	8	0,15	0,25	100	20
43945	yellow	2 x 1,00	2 x 18	1,95	3,4	5,4	15	8	0,15	0,3	100	20
43946	red	2 x 1,50	2 x 16	2,2	3,6	6,6	16	8	0,15	0,3	100	30
43947	blue	2 x 2,50	2 x 14	2,8	4,2	7,8	18,5	10	0,2	0,3	100	20
43948	grey	2 x 4,00	2 x 12	3,7	4,9	8,8	23	12	0,2	0,4	50	20
43949	black	2 x 6,00	2 x 10	4,8	6,9	10	26	14	0,2	0,4	50	15
43950	ivory	2 x 10,00	2 x 8	6,4	7,2	13	26	14	0,2	0,4	25	20

Twin wire end ferrules with plastic collar, Colour code DIN

												0010
Order-No.	~ C	mm²	AWG	D1	D2	D3	L1	L2	S1	S2	Ļ	
43935	white	2 x 0,50	2 x 20	1,4	2,5	4,7	15	8		0,25	100	30
43951	grey	2 x 0,75	2 x 18	1,7	2,8	5	15	8	0,15	0,25	100	20
43937	red	2 x 1,00	2 x 18	1,95	3,4	5,4	15	8	0,15	0,3	100	20
43938	black	2 x 1,50	2 x 16	2,2	3,6	6,6	16	8	0,15	0,3	100	30
43947	blue	2 x 2,50	2 x 14	2,8	4,2	7,8	18,5	10	0,2	0,3	100	20
43948	grey	2 x 4,00	2 x 12	3,7	4,9	8,8	23	12	0,2	0,4	50	20
43952	yellow	2 x 6,00	2 x 10	4,8	6,9	10	26	14	0,2	0,4	50	15
43953	red	2 x 10,00	2 x 8	6,4	7,2	13	26	14	0,2	0,4	25	20
••••••				••••	•••••••			••••••		******	•••••••••••••••••	

INFOBOX:

mm²

2 x 0,50

2 x 0,75

2 x 1,00

2 x 1,50

2 x 2,50

2 x 4,00

2 x 6,00

2 x 10,00

mm

8

8

8

8

10

12

14

14

50

50


25

20

15

20

Twin wire end ferrules with plastic collar



grey

black

ivory

43948

43949

43950

43940

43941

43942

orange

green

brown

Stripping/ insulating / crimping

Made in



43948

43952


43953

grey

yellow

red

C001C





Increases your safety: High thermal resistance up to 105 °C. Makes handling easier: Quick, easy cable insertion thanks to funnel sleeve. Increases your process safety: Consistently high processing quality for permanent safe contact.

										C020
Order-No.	<c< th=""><th>mm²</th><th>AWG</th><th>•1</th><th>D1</th><th>L1</th><th>В</th><th>D2</th><th>↓</th><th></th></c<>	mm²	AWG	•1	D1	L1	В	D2	↓	
43954	red	0,5-1,0	22-16	M4	4,1	18	8	4,3	100	15
43956	red	0,5-1,0	22-16		4,1	19	10	5,3	100	15
43958	red	0,5-1,0	22-16		4,1		11	6,5	100	15
43955	blue	1,5-2,5	16-14	M4	4,5	18	8	4,3	100	15
43957	blue	1,5-2,5	16-14	M5	4,5	20	10	5,3	100	15
43959	blue	1,5-2,5	16-14	M6	4,5	22	11	6,5	100	15
43960	yellow	4,0-6,0	12-10	M6	6,5	23	11	6,5	50	15
43961	yellow	4,0-6,0	12-10	M8	6,5	26	14	8,4	50	15
							••••••			

Terminals fork type insulated, per DIN



Increases your safety: High thermal resistance up to 105 °C. **Makes handling easier:** Quick, easy cable insertion thanks to funnel sleeve. **Increases your process safety:** Consistently high processing quality for permanent safe contact.

							_			C040
Order-No.	√C	mm²	AWG	•	D1	L1	В	D2	Ŀ	
43962	red	0,5-1,0	22-16	M4	4,1	18	8	4,3	100	15
43963	blue	1,5-2,5	16-14		4,5		8	4,3	100	15
43964	yellow		12-10		6,5	22	10	5,3	50	15





Increases your safety: High thermal resistance up to 105 °C. Makes handling easier: Quick, easy cable insertion thanks to funnel sleeve. Saves time: No further insulation required after pressing. Increases your process safety: Consistently high processing quality for permanent safe contact.

Order-No.		mm²	AWG	D1	L1	D2	Ъ	
43965	red	0,5-1,0	22-16	4,1	26	1,6	100	15
43966	blue	1,5-2,5	16-14	4,5	26	2,3	100	15
43967	yellow	4,0-6,0	12-10	6,5	28	3,6	50	15

Female blade connectors, insulated

Stripping/ insulating / crimping

	Societar Jeso Martinica Societar Jeso Martinica Societar Jeso Martinica Societar Jeso Martinica Societaria Societaria (La Martinica Societaria) e activitativa e activitati
D1	mm² pcs./St./ gitterature gitt
≤/	

Increases your safety: High thermal resistance up to 105 °C. **Makes handling easier:** Quick, easy cable insertion thanks to funnel sleeve. **Increases your process safety:** Consistently high processing quality for permanent safe contact.

									C141
Order-No.	√C	mm²	AWG	<u>]</u> ţ	D1	L1		ŀ	
43968	red	0,5-1,0	22-16	6,3 x 0,8	3,5	21	7,8	100	15
43969	blue	1,5-2,5	16-14	6,3 x 0,8	4,3	21	7,8	100	15
43970	yellow	4,0-6,0	12-10	6,3 x 0,8	6,2	23,8	7,8	50	15





Increases your safety: High thermal resistance up to 105 °C. Makes handling easier: Quick, easy cable insertion thanks to funnel sleeve. Saves time: No further insulation required after pressing. Increases your process safety: Consistently high processing quality for permanent safe contact.

									C146
Order-No.		mm²	AWG]ţ	D1	L1		¥	
43971	red	0,5-1,0	22-16		3,5	21,5	6,8	100	15
43972	blue	1,5-2,5	16-14		4,3		6,8	100	15
43973	yellow	4,0-6,0	12-10	6,3 x 0,8	5,8	25	6,8	50	15


Male blade connectors, insulated



Increases your safety: High thermal resistance up to 105 °C. **Makes handling easier:** Quick, easy cable insertion thanks to funnel sleeve. **Increases your process safety:** Consistently high processing quality for permanent safe contact.

Order-No.	√C	mm²	AWG	<u>]</u> ‡		L1	Ŀ
43974	red	0,5-1,0	22-16	6,3 x 0,8	3,5	21,5	100
43975	blue	1,5-2,5	16-14	6,3 x 0,8	4,3	21,3	100
43976	yellow	4,0-6,0	12-10	6,3 x 0,8	6,2	24	50







Simplifies your work

Torch with integrated laser makes it easier to fix positions more precisely and project measurements for ceiling installations, for example. Perfect light positioning thanks to lamp head swivelling in an L shape.

71mm

Simplifies your work

Comfortable measurement in different work positions thanks to the ingeniously positioned scales, even when viewed from above.



Surveying/marking/measuring/checking This is what we call precision work made to measure.

Wiha measurement and testing devices prove to be dependable helpers during electrical installation work. The multi-functional torch impresses in three ways thanks to its integrated laser, UV light and LED light with two lighting levels. With variable distance marks, the Wiha electrician's spirit level can reach across up to four flush boxes. Thanks to its ingeniously positioned scale, it allows users to make measurements effortlessly from different work positions. Users are guaranteed to see bubbles perfectly, even from a sharp angle. The Wiha electrician's folding ruler provides a scale for up to three flush boxes and edge distance marking at 150 mm. It can also be used to route cables into hard-to-reach installation locations. With its florescent coating, the folding ruler is also quick and easy to find in the dark with a UV light.

"The Wiha spirit level is a big hit! I can see the bubbles perfectly even when taking measurements above my head. I can also mark out measurements without needing to take a break." Ralf Kästle









Even the most experienced professional tradesmen find it difficult to work efficiently in poorly lit work environments. The Wiha multi-functional torch sheds light on things in three ways: It features an integrated laser, UV light and LED light with two lighting levels. It is thus a compact, universal work tool which replaces several instruments in a single device. The integrated laser offers a great advantage, providing detailed positioning and easy transmission of measurements for tasks such as ceiling installations. This torch is even more practical for portable use thanks to the retaining clip, magnetic positioning and swivelling lamp head used to point the light in the required direction. Compact, light and multi-functional, the Wiha torch ensures optimum illumination for perfect vision and positioning.

• Simplifies your work

Retaining clip and magnetic positioner on the lid allows you to keep hands free for other tasks.

• Simplifies your work

Integrated laser makes it easier to fix position more precisely and project measurements for ceiling installations, for example. Perfect light positioning thanks to lamp head swivelling in an L shape.

• Increases your efficiency

Very strong LED lamp – two light intensities to adjust to light conditions as required. Includes laser and UV light.

• Increases your safety

Power-on time of 2 seconds prevents the laser being activated by accident.








Simplifies your work: Retaining clip and magnetic positioner on the lid allows you to keep hands free for other tasks. Integrated laser makes it easier to fix position more precisely and project measurements for ceiling installations, for example. Perfect light positioning thanks to lamp head swivelling in an L shape. **Increases your safety:** Power-on time of 2 seconds prevents the laser being activated by accident. **Increases your efficiency:** Very strong LED lamp – two light intensities to adjust to light conditions as required. Includes laser and UV light.

in blister pack, including 3 AAA batteries

						24010
Best. Nr.	LED	*	UV		SB	
41286	100 / 310 lm	Class 2	390 - 400 nm	3 x AAA batteries	х	5







2909

2/670

Increases your safety: Checking your torque tool regularly guarantees safe, precise work with the correct torque. **Saves time:** LED traffic light system displays results in a way which is quick and easy to understand. **Increases your efficiency:** Fast, easy checking of your torque tool thanks to mobile, compact shape.

with adapter blades and batteries in box

Best. Nr.	Nm	+/- %	SB	
42086	2,8	2	х	1





Saves time: Rapid voltage test thanks to contactless measuring. Increases your efficiency: Compatible for use in all sockets worldwide thanks to measurement tip suited to international usage. Integrated high-luminescence LED flashlight. Increases your flexibility: Voltage tester covers a wide voltage range between 12 and 1,000 V AC. wiha e wiha e

Saves time: Rapid voltage test thanks to contactless measuring. **Increases your efficiency:** Compatible for use in all sockets worldwide thanks to measurement tip suited to international usage.

Includes t	wo AA	A batte	25513
Order-No.	-+	₩mm	
43797	28,5	150	10

Includes two AAA batteries

Order-No.	-+	₩mm	
43798	28,5	150	10

Voltage tester SoftFinish® single-pole, 110-250 volts



2 C E

255-11

25514

Increases your efficiency: Stable and as robust as a fully-fledged screwdriver. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

⊖Slotted transparent, with push-on clip

Order-No.	\ominus	—	\ominus ;	l ≁ mm	-+	SB D			
35378	3,0	60	0,5	140	19	х	5		
Tooted according to DIN 57690.6. CE. CE compliant									

Tested according to DIN 57680-6, GS, CE compliant.

INFOBOX: Single pole voltage tester, 12 - 1,000 V AC





- Rapid voltage test thanks to contactless measuring.
- Internationally adjustable measuring tip for all outlets, globally applicable.
- Green illuminated LED indicates readiness.
- Complies with safety standards EN 61010-1 / IEC 61326 and measuring category CAT IV 1,000 VAC.
- Extensive voltage range from 12 1,000 V AC.
- The strength of the alternating electrical field is signalled by an acoustic and five-level LED scale.
- Integrated high-luminescence LED flashlight.





- Rapid voltage test thanks to contactless measuring.
- Internationally adjustable measuring tip for all outlets, globally applicable.
- Green illuminated LED indicates readiness.
- Complies with safety standards EN 61010-1 / IEC 61326 and measuring category CAT IV 1,000 VAC.
- Voltage range from 90 1,000 V AC.
- The voltage is visually indicated by an illuminated LED.



Electrician's spirit level





Simplifies your work: Comfortable measurement in different work positions thanks to the ingeniously positioned scales, even when viewed from above. Saves space: Perfectly portable; fits into Wiha cases. Saves time: Variable distance marks for up to 4 flush boxes. Increases your efficiency: Both bubbles can be seen easily even from an acute angle.

40 cm		246
Order-No.	₩mm	₩
42074	400	10

Electrician's Longlife® folding ruler, 2 m



Simplifies your work: Integrated with cable retractor for cables between 3-7mm. Lowers your costs: Ruler quick and easy to find – even in dark environments with a UV light. Increases your efficiency: Ruler with integrated distance marks for up to 3 flush boxes. Offers you full protection: Tool tested at 10,000 V AC and suitable for 1.000 V AC.

metric, 10 segments

Order-No.	‡ <mark></mark>	√C	
42068	15	orange	10

4102008

Folding ruler LongLife Plus Composite 2 m



metric, 10	-		410 2005
Order-No.	‡ Inntre	√C	É
37067	15	red/ black	10





Increases your efficiency

Electrician's hammer offers perfect balance thanks to optimum weight distribution for effective handling.

06 mm PH2:100

Saves time

Dowel racket allows you to make dowel holes with the strike of a hammer anywhere at any time, even near power sockets.

Increases your work quality

The flat surface on the hammer handle ensures cables and dowels are fitted into position without causing any damage.



Striking Optimum power transmission.

Specially tailored for use by electricians: Wiha impact tools. With optimally uniform weight distribution, the Wiha electric hammer strikes a perfect balance and is also eminently suitable for use in confined working environments. Its flat claws allow you to remove nails and nail clamps easily. The flat surface on the hammer handle ensures cables and dowels are fitted into position without causing any damage to the cable duct or plasterboard. Wiha's scaled impact screwdriver blade ensures that the portable dowel racket makes a perfectly dimensioned dowel hole to the required depth anywhere at any time and without making a mess, unlike power tools. The galvanic separation between the blade and solid steel cap ensures that the user is always protected, even if they accidentally hit a live wire.

"Fits nicely into the hand and can be used in a variety of ways. It's now a permanent fixture in my toolbox!" Andreas Ebener







Thanks to its optimum balance, the electrician's hammer is perfectly sized in the hand while also providing a secure hold when hammering thanks to the ergonomically shaped hammer handle. With its U-shaped impact surface, the Wiha electrician's hammer delivers the optimum solution to working in corners and confined spaces. You can quickly and easily remove nails and nail clamps from walls with the flat claws on the hammer head. The flat surface on the hammer handle means cables and dowels are positioned effectively without causing any damage to the wall.

• Simplifies your work

Flat claws allow you to remove nails and nail clamps easily.

- Increases your efficiency Perfect balance thanks to optimum weight distribution for effective handling.
- Improved access Perfectly suited for use in confined working environments thanks to the combination of a square and round head shape.
- Increases your work quality The flat surface on the hammer handle ensures cables and dowels are fitted into position without causing any damage.



SoftFinish® dowel racket set with dowels

Electrician's hammer





Simplifies your work: Dirt- and dust-free work compared to when machines are used. Increases your safety: Galvanic separation in the handle prevents a discharge between the striking cap and the blade. Protect your health: Dowel hole can be made anywhere using a hammer at any time, even near power sockets. Saves time: Hammer dowel holes anywhere at any time without worrying how near you are to wall sockets. Increases your efficiency: Scaled impact screwdriver blade provides more detailed depth measurement. Perfectly dimensioned dowel hole thanks to blade adjusted to required size.





846

Simplifies your work: Flat claws allow you to remove nails and nail clamps easily. Increases your efficiency: Perfect balance thanks to optimum weight distribution for effective handling. Improved access: Perfectly suited for use in confined working environments thanks to the combination of a square and round head shape. Increases your work quality: The flat surface on the hammer handle ensures cables and dowels are fitted into position without causing any damage.

with 6 mm round blade in blister pack, 5-pcs.	SB 534S5
Order-No.	
41289	1
1 x Dowel racket	
2 x 30 mm Dowel	
2 x 40 mm Dowel	

with 300 g hammer head, in blister pack

Order-No.	
42071 23,9 283 4	

INFOBOX:

SoftFinish® dowel racket set with dowels







- Makes it easier to insert dowels and saves valuable working time.
- Ensures dirt- and dust-free work compared to machines.
- Galvanic separation between the blade and solid steel cap protects against electric shock.
- Perfect for portable use since you can make dowel holes anywhere at any time at the strike of a hammer.

INFOBOX: Electrician's hammer



- With its optimally uniform weight distribution, this hammer ensures perfect balance, delivering impact and fatique-free work.
- Its flat claws make it easier to remove fastening components such as nail clamps, even from difficult-toaccess spots.
- Optimum access into corners and confined spaces thanks to U-shaped striking surface.
- The flat hammer handle lower surface acts as a softfaced hammer, ensuring components such as cables and dowels are fixed into position without causing damage.



Subject to technical changes.

All illustrations and graphics, specified dimensions and valuesand references to standards, e.g. DIN/EN, are non-binding. Any liability claims based on this will therefore be rejec ted.

No liability claims will be accepted for printing errors and mistakes which have occurred during the production of the catalogue.

All property rights to the catalogue held by Wiha Werkzeuge GmbH are reserved. The printing or copying of the texts and illustrations contained in this catalogue or its design is prohibited.

Our General Terms and Conditions (Terms of Sale, Deliveryand Payment) apply.

TORX®, TORX PLUS® = Registered Trademarks of ACUMENT GlobalTechnologies B.V.

ACR/AOT, Tri-Wing®, Torq-Set®= Registered Trademarks of Phillips Screw Company

Pozidriv= Registered Trademark of European Industrial Services Ltd.

Protective measures

The following equipment is required for all work on or around live components and should be appropriate for the specific task

- insulating personal protective equipment
- insulating safety mechanisms
 insulated tools

Before starting work, you must disconnect all active, live components of electrical machines and equipment and ensure that they remain disconnected while you carry out the work

This is achieved by complying with the five safety rules: - disconnect

- secure against reconnection
- ensure power is switched off
- earth and short-circuit
- cover or block off adjacent live components

159

Wiha order number register

Order-No.	Page	Order-No.	Page	Order-No.	Page	Order-No.	Page
00		00833	69	01805	90	05	
00684	79	00834	69	01808	90	05301	92
00685	79	00846	70	01809	90	05302	92
00686	79	00847	70	01811	90	05303	92
00687	79	00848	70	01812	90	05799	90
00689	79	00849	70	01913	89	05800	90
00690	79	00850	70	02		06	
00691	79	00853	71	02292	98	06637	92
00692	79	00855	71	03		06638	92
00694	79	00856	71	03223	78	06639	92
00695	79	00857	71	03224	78	06888	90
00696	79	00858	71	03225	78	06889	90
00697	79	00859	71	03226	78	20	
00698	79	00860	71	03228	78	20218	92
00700	79	00861	71	03230	78	20219	92
00701	79	00862	71	03231	78	20220	92
00702	79	00863	71	03232	78	20221	92
00703	79	00864	71	03237	78	20222	92
00704	79	00865	71	03238	78	20223	92
00706	79	00866	71	03239	78	20224	92
00707	79	00867	71	03245	78	21	
00708	79	00868	71	03246	78	21045	92
00709	79	00877	70	03247	78	21047	92
00711	79	00878	70	03760	70	22	
00712	79	00879	70	03761	70	22509	90
00713	79	00880	70	03762	70	22510	90
00819	70	00881	70	03988	99	22511	90
00820	70	00882	70	04		22512	90
00821	70	01		04009	90	22596	92
00822	70	01790	90	04010	90	22597	92
00823	70	01791	90	04059	90	22598	92
00824	70	01792	90	04126	90	22599	92
00825	70	01793	90	04127	90	22600	92
00826	70	01794	90	04176	90	23	
00827	70	01795	90	04194	92	23145	92
00828	70	01796	90	04195	92	23147	92
00829	70	01798	90	04196	92	23149	92
00830	70	01799	90	04197	92	23151	92
00831	70	01800	90	04198	92	23195	92
00832	70	01803	90			23197	92



Order-No.	Page	Order-No.	Page	Order-No.	Page	Order-No.	Page
23199	92	26729	112	31		32421	91
23201	92	26732	113	31863	70	32423	91
23203	92	26735	113	31957	90	32477	89
23205	92	26745	124	31958	90	32486	91
23207	92	26755	20	31959	90	32490	90
23209	92	26847	125	31960	90	32491	90
23211	92	26852	105	31961	90	32492	90
23213	90	26864	39	31962	90	32493	90
23215	90	26931	79	31973	91	32494	91
23217	90	27		31975	92	32495	91
23219	90	27753	79	31977	92	32496	91
23221	90	27754	79	32		32497	91
23223	90	27755	79	32105	90	32686	90
23225	90	27928	73	32299	91	32687	90
23226	90	27929	73	32302	91	32688	91
23227	90	27930	73	32303	91	32689	91
23228	90	27931	73	32304	91	33	
24		27932	73	32305	91	33520	113
24867	92	27933	73	32306	91	33703	90
25		27934	73	32307	91	33704	90
25477	69	27935	73	32308	91	33705	90
25553	92	28		32309	91	33706	90
25739	92	28481	91	32310	89	33707	90
25740	92	28691	49	32383	79	33708	90
25741	92	29		32384	79	33709	91
25742	92	29416	88	32396	70	33710	91
26		29417	88	32397	70	33711	91
26000	91	29466	71	32399	79	33712	91
26002	92	30		32400	79	33713	91
26625	39	30361	70	32409	91	33714	91
26626	39	30362	70	32410	91	33715	91
26627	39	30363	70	32411	91	33716	91
26705	108, 112	30364	70	32412	91	33717	91
26708	108, 112	30365	70	32413	91	33718	91
26711	108, 112	30366	70	32414	91	33719	91
26714	108, 113	30700	70	32415	91	33720	91
26717	108, 113	30701	70	32416	91	33721	91
26720	112	30715	70	32417	91	33722	91
26727	112	30716	70	32418	91	33723	91
26728	112			32419	91	33724	91



Order-No.	Page	Order-No.	Page	Order-No.	Page	Order-No.	Page
33725	91	34457	91	35		36454	98
33726	91	34554	92	35389	67	36455	67
33727	91	34555	92	35390	68	36487	98
33728	91	34556	92	35391	68	36536	68
33729	91	34557	92	35392	68	36537	68
33730	91	34558	92	35393	68	36538	68
33731	91	34559	92	35394	68	36539	68
33732	91	34560	92	35395	68	36540	68
33738	80	34578	46, 61	35396	68	36541	68
33744	80	34579	46, 61	35446	68	36542	68
33746	80	34580	46, 61	35456	90	36558	67
33841	127	34581	46, 61	35457	90	36791	36
33842	128	34582	46, 61	35501	68	37	
33843	128	34583	46, 61	35502	68	37067	152
33844	127	34584	46, 61	35503	68	37147	46, 61
33920	91	34585	46, 61	35504	68	37222	46, 61
33921	91	34586	46, 61	35505	68	37223	46, 61
33922	91	34587	46, 61	35506	46, 61	37224	46, 61
33923	91	34588	46, 61	35507	46, 61	37225	46, 61
33924	91	34589	46, 61	35508	46, 61	37226	46, 61
33925	91	34590	46, 61	35509	46, 61	37227	46, 61
33926	91	34688	119	35510	46, 61	37351	97
33927	91	34689	119	35511	46, 61	37402	109
33928	91	34690	119	35861	128	37403	109
33929	91	34691	119	35862	128	37450	112
33930	91	34692	119	35870	47	38	
33931	91	34693	119	35969	125	38020	21
33932	91	34694	119	36		38074	38
33961	90	34695	119	36050	127	38191	104
33962	90	34696	119	36051	125	38362	67
33963	90	34697	119	36052	125	38370	91
33964	90	34698	119	36053	125	38371	91
33965	90	34699	119	36071	46, 61	38372	91
33966	90	34700	119	36092	89	38552	124
33969	20	34701	119	36093	89	38606	80
34		34702	119	36094	89	38612	52
34306	89	34703	119	36114	78	38798	125
34452	91	34704	119	36189	109	38918	48
34453	91	34705	119	36327	91	38919	48
34454	91	34706	119	36329	68	38920	48
34455	91	34707	119	36330	68	38921	48
34456	91	34708	118	36389	21	38925	49



Order-No.	Page	Order-No.	Page	Order-No.	Page	Order-No.	Page
38926	49	39199	91	41344	42	42375	72
38927	49	39200	92	41345	42	42376	72
38928	49	39201	92	41476	42	42377	72
38929	49	39202	92	41477	42	42378	72
38930	49	39203	92	41478	42	42379	72
38931	48	39204	92	41479	42	42380	72
38932	48	39206	92	41824	86	42471	72
38933	48	39207	92	41825	86	42766	31
38934	48	39208	92	41826	86	42989	72
38935	48	40		41827	87	43	
38936	48	40282	22	41828	87	43022	25
39		40523	17	41829	87	43023	24
39041	88	40674	37	41830	86	43024	24
39045	89	40921	106	41831	86	43026	74
39049	88	40923	114	41832	87	43027	74
39056	89	40948	22	41833	87	43028	74
39057	89	41		41834	87	43029	74
39059	89	41003	66	41914	31	43030	74
39060	88	41141	68	41915	31	43031	74
39083	88	41142	68	41923	109	43032	74
39134	89	41143	68	41979	96	43033	74
39178	92	41144	68	42		43034	74
39179	92	41145	68	42062	126	43035	74
39180	92	41146	68	42068	152	43036	74
39181	92	41147	68	42069	15	43037	74
39182	92	41158	52	42071	158	43038	74
39183	92	41159	46, 61	42074	152	43039	74
39184	91	41160	46, 61	42086	41, 150	43040	74
39185	91	41223	23	42098	85	43041	74
39186	91	41230	56	42099	84	43042	74
39187	91	41231	53	42114	84	43043	74
39188	92	41232	54	42115	84	43044	74
39189	92	41233	54	42116	84	43052	77
39190	92	41235	52	42117	84	43053	77
39191	92	41246	127	42118	84	43055	77
39192	92	41274	106	42135	85	43056	77
39193	92	41279	106	42136	85	43057	77
39194	92	41286	150	42137	85	43058	77
39195	91	41289	158	42138	85	43061	74
39196	91	41341	42	42139	85	43062	77
39197	91	41342	42	42162	126	43063	77
39198	91	41343	42	42374	72	43065	75
39198	91	41343	42	42374	72	43065	75




Order-No.	Page	Order-No.	Page	Order-No.	Page	Order-No.	Page
43066	75	43108	76	43467	55	43934	139
43067	75	43114	46, 61	43474	19	43935	140, 141
43068	75	43115	46, 61	43660	107	43936	140
43069	75	43116	46, 61	43662	107	43937	140, 141
43070	75	43117	46, 61	43797	151	43938	140, 141
43071	75	43125	109	43798	151	43939	140
43072	75	43128	47	43879	18	43940	140
43073	75	43139	62	43899	136	43941	140
43074	75	43140	46, 61	43900	136	43942	140
43075	75	43141	46, 61	43901	136	43943	140
43076	75	43142	46, 61	43902	136	43944	140
43077	74	43143	46, 61	43903	136	43945	140
43078	74	43144	46, 61	43904	136	43946	140
43079	74	43145	46, 61	43905	137	43947	140, 141
43080	74	43146	46, 61	43906	137	43948	140, 141
43081	74	43147	46, 61	43907	137	43949	140
43082	74	43148	46, 61	43908	138	43950	140
43083	74	43149	46, 61	43909	138	43951	141
43084	74	43150	46, 61	43910	138	43952	141
43085	74	43151	46, 61	43911	138, 139	43953	141
43086	74	43152	44, 59	43912	138	43954	142
43087	74	43153	44, 59	43913	138, 139	43955	142
43088	47, 75	43154	44, 59	43914	138, 139	43956	142
43089	47, 75	43155	44, 59	43915	138	43957	142
43090	47, 75	43156	44, 59	43916	138	43958	142
43091	47, 75	43157	44, 59	43917	138	43959	142
43092	47, 75	43158	44, 59	43918	138	43960	142
43093	47, 75	43159	44, 59	43919	138	43961	142
43094	47, 75	43160	32, 44, 59	43920	138	43962	142
43095	47, 75	43161	43, 58	43921	138	43963	142
43096	47, 75	43162	43, 58	43922	138	43964	142
43097	47, 75	43163	45, 60	43923	138	43965	143
43098	47, 75	43164	45, 60	43924	138	43966	143
43099	47, 75	43167	57	43925	138	43967	143
43100	76	43177	48	43926	138	43968	143
43101	76	43292	62	43927	138, 139	43969	143
43102	76	43326	106	43928	138, 139	43970	143
43103	76	43335	106	43929	138	43971	144
43104	76	43340	106	43930	138	43972	144
43105	76	43449	56	43931	138	43973	144
43106	76	43465	19	43932	139	43974	144
43107	76	43466	38	43933	139	43975	144



Order-No.	Page
43976	144
43982	132
43983	133
43984	132
43985	134
43986	134
43987	134
43995	133
43996	139
44	
44001	78
44005	135
44006	135
44007	135
44106	32, 45, 60
44107	32, 45, 60
44318	30
44351	30
44363	31
44364	31
44366	32, 44, 59
44367	31


Notes







Notes







Overview of torque tools


Tools	Precision	Setting	Special feature	Nm range	Torque	range			
					0,1 Nm	1 Nm	10 Nm	20 Nm	< 50 Nm
easyTorque Adapter	± 10%	fixed	VDE certification Permanently preset in factory	5 Versions 0,8 – 4,0					
TorqueVario [®] -S VDE				0,5 – 2,0				*****	
wiha o	± 6%	variable	VDE certification, numeric scale	0,8 - 5,0 2,0 - 7,0					
Torque screwdriver with T-handle TorqueVario®-S T electric		variable	VDE certification, numeric scale	5 – 14					


The cutting capacities for our pliers.

Soft wire Plastic/ copp	per/ aluminium elect	trical cable/electri	cal cable/ silver	wire	Medium-har	r d wire s screws, wire-me	esh fencing		
≫մ 1	2	3	4	5	≫ 6	7	8	9	10
	Diagonal cutters	for plastic				Precision mechar	nic's diagonal cu	itters	



Interchangeable blades





Values may vary depending on leverage, material thickness and the specific product application.



Legend

|--|

DIIVE	*5
٥	Triangular nut
0	Hexagon head
0	Square nut
۲	Internal hexagon
0	Internal hexagon with drill hole (tamper-resistant)
0	Tamper Resistant hex
۲	Countersink
O	Combination drill bit
۲	Pentalobe PL
٨	Ү-Туре
Ð	Phillips PH (cross-recessed)
*	Pozidriv PZ (Phillips)
	Robertson
	Round tip
Ф	Slotted
٩	Slotted nut
۲	SIT
\odot	Spanner
•	Twist drill
Ð	Sliding sleeve
Ð	Torq-Set [®]
۲	TORX®
۲	TORX [®] with drill hole (tamper-resistant)
۲	TORX PLUS®
Ð	Tri-Wing [®]
۲	Multitooth
	Square reaming blade
*	Xeno SL/PZ

Drives

0	Square nut
	Square
●	G7 drive system
O	Threaded connector
۲	SDS-Plus®
۲	Hex

Scre	wdrivers [mm]
۵‡	Cut width
⊖¦	Tip width
•	Round blade dimension
• 1	Hex blade
\bigcirc	Hex bolster
‡ >	Scraper width
:=	Clip opening
1	Tip width
₫,	Head width, nut driver
╤╸	Blade length
‡ ~ —	Shaft lengths
₽	Handle length
+	Handle diameter
	Torque T-handle length
-01	Torque T-handle width
max. Nm	Max. torque value [Nm]
max. in Ibs	Max. torque value [in.lbs]
₩4%	Accuracy [%]
₽	Cable key depth

	Pilers	s [mm]
		Flat jaws
	•	Half round jaws
on	:	Round jaws
	K	Cutter without bevel
	K	Cutter with small bevel
	X	Cutter with bevel
	ł	Anvil cutter
	I	Center cutter
er	5	Scissors cutter
	۵	Front cutting edge in stripping pliers
	Ømm	Max. diameter
	mm²	Max. cross-section
th	0;	Max. gripper pipe diameter
h	0:	Max. gripper width across flats
m]	U	External retaining ring
.lbs]	C	Internal retaining ring
	-Ai-	Clamping range
		Opening width flat
	≫	Cutting force
	WW	with opening spring
	AWG	American Wire Gauge
		Saw blade length

L-keys [mm]

•1	Round blade dimension
	Hex blade
\bigcirc	Hex bolster
Ì	Shaft lengths
, →	Blade length
━,	Side driver length T-handle
 0‡	Handle width
 _	Diameter

Bits [mm]

	Threaded connector
\Rightarrow	Drill working length
	Screw size

Pliers [mm]

‡ 	Width of segments
√C	Colour
	Measurement capacity [mm]
\ ≞/	Measurement capacity in Inch

Measurement tools [mm]

Elektro

	Battery
LED	LED lumens
*	Laser light


Soft faced hammer [mm]

•	Face diameter
	Hammer face width
! +	Hammer head width

General symbols

⊌ g ⊎	Weight, g
•	Diameter
SB)	Blister packed
mm	Total length
← →	Total length Inch
	Packaging unit

Legend





Wiha Werkzeuge GmbH Obertalstraße 3–7

 78136
 Schonach/Germany

 Phone
 +49
 77
 22
 959
 0

 Fax
 +49
 77
 22
 959
 159
 Inland

 Fax
 +49
 77
 22
 959
 155
 Export

 info.de@wiha.com
 www.wiha.com
 www.wiha.com
 Here
 Here

Wiha Tools Ltd.

841 Birchwood Boulevard Warrington WA3 7QU Phone +44 15 27575 758 +44 15 27910 986 Fax +44 15 27910 023 info.uk@wiha.com www.wiha.com/en

Wiha France SARL

Z. A. de Terrefort 33520 Bruges/France Phone +33 55 6167 935 Fax +33 55 6167 936 servicecommercial@wiha.fr www.wiha.com/fr

Wiha Nordic A/S

Korskildelund 6 2670 Greve/Denmark Phone +45 70 238 045 info.nordic@wiha.com www.wiha.com

Wiha Iberia Willi Hahn S.A.

Av. del Rey Juan Carlos I, 98. 3° C 28916 Leganés/Madrid, Spain Phone +34 91 6938 511 Fax +34 91 6936 383 iberia@wiha.com www.wiha.com/es

Wiha Polska Sp. z o.o.

ul. Budowlanych 10 b 80-298 Gdańsk/Poland Phone +48 58 7623 830 Fax +48 58 7623 900 info.pl@wiha.com www.wiha.com/pl

Wiha in Russia

Phone +48 58 7623 830 Fax +48 58 7623 900 michal.moczynski@wiha.com www.wiha.com

Willi Hahn Corp.

1348, Dundas Circle Monticello, MN 55362/USA Phone +1 76 32956 591 Fax +1 76 32956 598 cservice@wihatools.com www.wihatools.com

Wiha Tools Canada Ltd.

394 Deerhurst Drive L6T 5H9, Brampton, ON Phone +1 86 64940 096 Fax +1 80 04947 456 info@wihatools.ca www.wihatools.ca

Wiha Tools (Shanghai) Co.Ltd.

Room No. 908 - 910, Building 10, Long 2777, East Jinxiu Road, Pudong New District Shanghai, China 201206 Phone +86 21 64401 119 Fax +86 21 64401 112 info.cn@wiha.com.cn www.wiha.com.cn

Wiha Finland Oy Mäkituvantie 9 FI-01510 Vantaa Finland Phone +358 44 231 9988 raija.heliin@wiha.com www.wiha.com

Wiha en Belgique

Phone +32 49 3505 450 info.belux@wiha.com www.wiha.com

Wiha in Nederland

Phone +31 64 6311 330 info.nl@wiha.com www.wiha.com/nl

Wiha in Italia

Thoelke Rappresentanze Srl Phone +39 03 32966 039 info.it@wiha.com www.wiha.com/it

Premium Tools Australia Pty Ltd.

PO Box 63 Bargo, NSW 2574 Phone +61 02 46841 460 Fax +61 02 80887 272 sales@wiha.com.au www.wiha.com.au

Premium Tools (NZ) Ltd.

Unit 5C 89 Ellice Road Wairau Valley Auckland, New Zealand Phone +64 09 4442 560 Fax +64 09 3550 411 sales@wiha.co.nz www.wiha.co.nz

Robert Rieffel AG

Widenholzstrasse 8 8304 Wallisellen/Switzerland Phone +41 44 8773 333 Fax +41 44 8773 322 info@rieffel.ch www.rieffel.ch

