Independent 75

Maximum independence with the multifunctional ERSA gas soldering sets





Mobile power - wherever you may need it! Efficient, with a wide range of high quality accessories, small, handy and a convenient packaging: this gas soldering set is very versatile! The ergonomic antistatic gas soldering iron with piezo ignition is the perfect tool for service and maintenance work - especially when there is no electric power supply available.

With its infinitely variable power rating from 15 up to 75 watts (compared with electrical soldering irons) max. soldering tip temperatures of 500°C can be achieved. The Independent 75 operates on commercially available butane lighter gas.

The Independent 75 "Basic Set" is supplied in a practical transport case, consisting of a gas soldering iron with pre-installed catalytic soldering tip, a spare tip and a sponge container with cleaning sponge.

In addition to the "Basic Set", the Independent 75 "Profi Set" includes another 2 soldering tips suitable for virtually every soldering application. A hot blade to shape and cut high-resistance foam, a hot gas nozzle, a deflector to shrink heat-shrinkable sleeves and to solder SMD components as well as a flame nozzle to micro weld complete the equipment and open up many different applications.





ERSA-product range

Soldering tools

- NEW DIMENSION
- PROFI-LINE
- IR-Rework
- CLEAN-AIR

Soldering systems

Wave soldering

- ETS-line
- EWS-line
- N-Wave-line
- Solution

Reflow soldering

- Hotflow 3
- Hotflow 5
- Hotflow 7
- Hotflow 9
- Hotflow 11
- ERS 250

Selective soldering

- EAS-line
- Multiflow
- Versaflow
- Versaflow Compact
- Versaflow High Speed
- · Place & Solder

Inspection systems

- ERSASCOPE
- ImageDoc Software

Other services

- Know-how seminars
- In-House trainings
- Test soldering
- Installation and maintenance assistance
- · Process support





NDEPENDENT 75

Independent 75

Maximum independence with the multifunctional ERSA gas soldering sets





Rating: 15 - 75 W

183°C in approx. 30 sec. Heating time: Sold. tip temp.: approx. 500°C max.

Weight: 73 q

Ignition: piezo ignition, operates on

butane gas

Order nos.:

0G07400141 Gas soldering set Indpendent 75 "Profi Set"



consisting of:

Gas soldering iron Independent 0G070KN

75 with chisel-shaped soldering

tip 0G072KN, 2.4 mm

0G072CN Chisel-shaped sold. tip, 1.0 mm 0G072AN Chisel-shaped sold. tip, 3.2 mm 0G072VN Chisel-shaped sold. tip, 4.8 mm

0G072BE Flame nozzle 0G072HE Hot gas nozzle 0G072MN Hot blade

0G072RE Deflector to shrink heat-

shrinkable sleeves

0A20 Holder

0006 Cleaning sponge 0G156 Sponge container

Order nos.: 0G07400041 Gas soldering set Indpendent 75 "Basic Set"



consisting of:

0G070KN Gas soldering iron Independent 75

with chisel-shaped soldering tip

0G072KN, 2.4 mm

0G072CN Chisel-shaped sold. tip, 1.0 mm


0A20 Holder

0006 Cleaning sponge 0G156 Sponge container

Accessories:

0G 806 K Gas cartridge, 65 ml





ERSA GmbH Otto-Schott-Straße 3-7 P.O.Box 1261 97862 Wertheim/Germany Tel: +49(0)9342/800-0 Fax: +49(0)9342/800-250 e-mail: info@ersa.de

0G072CN



http://www.ersa.de

5PE0701-IN75 • subject to changes • © by ERSA

original size