

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2177971031](#)
Status: **Active**
Overview: [Off-the-Shelf Cable Assemblies](#)
Description: KK 254-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.54mm Pitch, Single Row, 150.00mm Length, 3 Circuits, Natural

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family Cable Assemblies
Series [217797](#)
Assembly Configuration Dual Ended Connectors
Connector to Connector KK 254-to-Pigtail
Overview [Off-the-Shelf Cable Assemblies](#)
Product Name KK 254
Type Discrete Wire Assembly
UPC 195842123014

Physical

Cable Length 150.00mm
Circuits (Loaded) 3
Color - Resin Natural (White)
Gender Female-Pigtail
Lock to Mating Part Yes
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 2.617/g
Number of Rows 1
Pitch - Mating Interface 2.54mm
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.57mm max.
Wire Size AWG 22
Wire/Cable Type UL 11028

Material Info

Reference - Drawing Numbers

Sales Drawing 2177971031-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[217797](#) Series

Mates With

KK254 PCB Headers
 [42375](#) , [42377](#)
 , [42376](#) , [4030](#) , [6373](#) , [6410](#) , [1718](#) 56,
[171857](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION