



[Home](#)
[Company](#)
[Product Range](#)
[Product Solutions](#)
[Downloads](#)
[LED Information](#)


+ 44





PCV12150 – Non IP Rated Constant Voltage Power Supply







Our energy efficient and energy compliant PCV12150 is a 12VDC 12.5A LED Driver. Suitable for indoor lighting applications including a high efficiency of 87% and power consumption of 150W.

SKU: PCV12150

Category: [LED DRIVERS](#)

[Receive a Quote →](#)

Our energy efficient and energy compliant PCV12150 is a 12VDC 12.5A LED Driver. Presented with an LED indicator for power on and features including an over load, short circuit and thermal protection, they are made suitable for indoor lighting applications, complimenting their high efficiency of 87% and power consumption of 150W. Designed with smart features including captive terminal screws for ease and an LED indicator for power on.

Additional information

Weight	0.75 kg
Product Type	AC/DC, Constant Voltage, LED Driver
Functions	Latch Off
Outputs	Single
Dimensions	216 x 74 x 42mm
Input Voltage	100 ~ 240VAC
IP Rating	IP20
Output Current	0-12.5A
Output Voltage	12VDC
Power	150W
tape-length	216
Efficiency	87%
Connections	Cable on I/P or O/P
Weight	450g
Dimensions	240 x 30 x 28mm

Applications

- Residential LED lighting
- Display cases
- LED downlights
- LED Backlighting
- Mood lighting
- Light sculptures