

75W 12V 6.25A IP67 Rated Constant Voltage LED Lighting Power Supply – PCV1275E



PCV1275E is a 75W RoHS compliant single 12V 6.25A output Constant Voltage power supply, with IP67 rating, suitable for LED lighting applications indoors and outdoors.

SKU: PCV1275E

Category: [LED DRIVERS](#)

Tags: [CONSTANT VOLTAGE LED DRIVER](#) • [WATERPROOF DRIVER](#)



PCV1275E is a 75W RoHS compliant single 12V 6.25A output Constant Voltage LED Lighting Power Supply with IP67 rating, suitable for LED lighting applications indoors and outdoors. PCV1275E has 100-240V input voltage, is of Class II design and offers cooling via free air convection.

Additional information

Weight	0.75 kg
Product Type	AC/DC, Constant Voltage, LED Driver
Outputs	Single
Dimensions	186 x 64 x 39 mm
Input Voltage	100 – 240VAC
IP Rating	IP67
Output Current	0-6.25A
Output Voltage	12VDC
PFC	PFC
Power	75W
Efficiency	85%
Input Voltage	100-240Vac
Output Voltage	12V
Output Current	6.25A
Power	75W

Applications

- Residential LED lighting
- Display cases
- LED downlights
- LED Backlighting
- Mood lighting
- Light sculptures

Features

- Universal AC input
- IP65 Rated design
- High efficiency
- Over load, short circuit and thermal protection
- SELV equivalent
- Class II product
- cooling by free air convection