CONSTANT CURRENT LED DRIVER 20WATT



An and a second second

POWERPAX: LED-DR-700-20

Features:

- Input Voltage 180-264vac
- IP20 Rated
- Class II
- Compact Plastic Low Profile enclosure
- 1 Year Warranty

Description:

The Range of 20 Watt Constant Current LED Drivers are housed in a compact light weight high quality IP20 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications.

Specification	
Part Number	LED-DR-700-20
Output Voltage Range	14-29Vdc
Output Current Range	700mA
Rated Power	20 Watt
Dimensions	154 x 50 x 14.5 mm
Input Voltage Range	180-264VAC
Input Voltage Frequency	50Hz
Inrush Current	<70A
Input power	<24.5W
Efficiency	≥82%
Power Consumption Without Load	<0.5W
Over Load Protection	Ta, 0.94-1.06 times of input voltage, 1.2 times of rated power
Short Circuit Protection	Ta, 0.94-1.06 times of input voltage
Automatically Restart	Yes
Working Temperature	-20°C ~ +45°C
Relative Humidity	45% ~ 85%
MTBF	30000hr
EMC emission	EN55015
EMC Immunity	EN6100-3-2, EN61547
Safety Standards	IEC61347-1, IEC61347-2-13



General Note TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

© TT Electronics plc

TT Electronics IoT Solutions Ltd Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK t: +44 (0) 1429 852 500


CONSTANT CURRENT LED DRIVER 20WATT




POWERPAX: LED-DR-700-20







Wiring Diagram



General Note

© TT Electronics plc

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics IoT Solutions Ltd Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK t: +44 (0) 1429 852 500

ISS.3 17/07/2020 Page: 2

POWERPAX