EXTERNAL DESKTOP POWER SUPPLY 9VDC 14.4WATT



POWERPAX: SW3111B

Features:

- Universal Input
- IEC-320-C8 Input Connector
- 3 Year Warranty
- Efficiency Level VI
- Safety approved to: UL,CUL,FCC,GS,CE,RCM



Description:

Our Range of 14.4 watt AC/DC switch mode power supplies provide 14.4 watts of continuous output power in a high quality compact enclosure suitable for many general power applications.

Specification	
Part Code	SW3111B
Input Voltage Range	100 → 240 Vac
Input Frequency Range	50 → 60Hz
Input Connector	IEC 320-C8
Input Current Rated	1.2A max.
Leakage Current	0.25mA.
Efficiency	83.92% Min
Input Power (Output: No Load)	Max. 0.1W
Output Voltage Rating	+9V
Output Current Range	1.6A
Output Min Current	0.0A
Output Connection Type	2.1 x 5.5 x 12 mm centre positive – Straight
Line and Load Regulation	LINE +/-5% LOAD +/-5%
Over Voltage Protection	V out *180%(Max)
Over Load Protection	V out *180%(Max)
Short Circuit Protection	Output shut down auto recover
Ripple Voltage	150mVp-p
Hi-Pot	3000Vac,10m A, 1 minute.
Safety Approved	UL, CUL, TUV, CE, UK, RCM, CCC
EMI Standard	FCC part 15: Class B,EN55022:2010,Class B,GB9254-2008, GB17625.1-2012
Operating Temperature Range	0° → +40 °C
Storage Temperature	-20°C → 80°C
Operating Humidity	5% to 95%
Storage Humidity	5% to 95%
Dimensions	75 (L) x 50.6 (W) x 29.8 (H) mm
Product Weight	107g
Regulator Type	Switched Mode Power Supply

EXTERNAL DESKTOP POWER SUPPLY 9VDC 14.4WATT



POWERPAX: SW3111B

Diagrams

