

rhino

Art.-Nr. 115.04/P

- mobiler Koffer mit anwendungsfreundlichem Teleskopgriff
- zwei Inline-Rollen
- Kofferschalen aus flugtauglichem HDPE Material
- robuster Aluminiumrahmen mit Stoßkantenschutz
- zwei abschließbare Kippschlösser
- ein B&W PROFICODE-Zahlenschloss
- B&W CONVENIENCE Griff
- Scharnierabdeckung
- Sicherheitsdeckelhalter
- Dokumentenfach im A4-Format
- zwei herausnehmbare Werkzeugtafel im Deckel mit
- 23 Tool Pockets auf Vorder- und Rückseite
- herausnehmbare Abdeckplatte für Bodenschale mit
- 15 Tool Pockets
- Bodenschale variabel

Innenmaße: 510 x 390 x 230 mm

Gewicht: 7,9 kg

Volumen: 46 l

Max. Zuladung: 35 kg



rhino

art.-no. 115.04/P

- mobile case with user-friendly telescopic handle
- and two free running rollers
- case shells made of HDPE material (flight case)
- robust aluminium frame with protection for the sharp edges
- two lockable clip locks
- one B&W PROFICODE combination lock
- B&W CONVENIENCE handle
- comfortable lid holder
- hinge cover
- document partition in the lid (A4 format)
- two removable tool board in the lid with 23 tool pockets
- on the front and back
- removable cover board for the floor shell with
- 15 tool pockets
- variable floor shell

interior measurements:

510 x 390 x 230 mm

weight: 7,9 kg

volume: 46 l

max. loading capacity: 35 kg

