

Han 32A-Dust Protect. Cover-f. Easy-Lock



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 032 5405
Specification	Han 32A-Dust Protect. Cover-f. Easy-Lock
HARTING eCatalogue	https://b2b.harting.com/09200325405

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings Metal
Type	Low construction High construction

Version

Locking type	Double locking lever
Size	32 A
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Surface (hood/housing)	Powder-coated
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	31 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors