

Han 3A-HBMA/P-DL-black



Part number	09 20 003 0827
Specification	Han 3A-HBMA/P-DL-black
HARTING eCatalogue	https://b2b.harting.com/09200030827

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Angled

Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Polyamide (PA)
Colour (locking)	RAL 9005 (jet black)



Material properties

Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
CE	Yes

Commercial data

Packaging size	10
Net weight	16.08 g
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors