

Han 10EMC/B-HSE-M32 (HT)



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 810 0527
Specification	Han 10EMC/B-HSE-M32 (HT)
HARTING eCatalogue	https://b2b.harting.com/19628100527

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] EMC/B Han [®] High Temp
Type of hood/housing	Hood
Type	High construction

Version

Locking type	Double locking lever
Size	10 B
Version	Side entry
Cable entry	1x M32

Technical characteristics

Limiting temperature	-40 ... +125 °C -40 ... +200 °C With Han [®] High Temp components
Degree of protection acc. to IEC 60529	IP65 IP66
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted



Pushing Performance

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes

Commercial data

Packaging size	1
Net weight	148.84 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors