

Double Frame, Ni plated, metal cover



Part number	39 50 000 0210
Specification	Double Frame, Ni plated, metal cover
HARTING eCatalogue	https://b2b.harting.com/39500000210

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Sockets
Series of hoods/housings	Han-Port [®]
Element	Frames
	Double
Specification	Metal version, nickel plated (electrically conductive)
	Metal cover, nickel plated

Technical characteristics

Limiting temperature	-10 +60 °C
Storage temperature	-25 +60 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Smoothed surface
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Commercial data

Packaging size	1	
----------------	---	--

Product data sheet 39 50 000 0210 Double Frame, Ni plated, metal cover



Commercial data

Net weight	624.28 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27182810 Cover/infill panel/identification strip (electrical cabinet)