

RHINO™ LABELS

RHINO tapes are developed for harsh environments and provide resistance against abrasion, different temperatures, chemicals, solvents, water and UV. DYMO offers several specific materials depending on the application, all with a strong adhesive and carefully chosen ribbon for high print quality and resistance.



FULL BACKSLIT FOR EASY PEEL

| | FLEXIBLE NYLON | COLOURED VINYL | PERMANENT POLYESTER | CLEAR POLYESTER | HEAT SHRINK TUBE | SELF-LAM. VINYL | NON-ADHESIVE TAG (INSERT) |
|-----------------------------|----------------|----------------|---------------------|-----------------|------------------|-----------------|---------------------------|
| SURFACE APPLICATIONS | | | | | | | |
| Smooth | ✓ | ✓ | ✓ | ✓ | – | – | n/a |
| Flat | ✓ | ✓ | ✓ | ✓ | – | – | n/a |
| Textured | ✓ | ✓ | ✓ | ✓ | – | – | n/a |
| Powder coated | ✓ | ✓ | ✓ | ✓ | – | – | n/a |
| Curved | ✓ | ✓ | – | – | – | – | n/a |
| Wire & Cable | ✓ | ✓ | – | – | ✓ | ✓ | n/a |
| RESISTANCY | | | | | | | |
| Heat | ✓ | – | ✓ | ✓ | ✓ | ✓ | n/a |
| Water | – | ✓ | ✓ | ✓ | ✓ | ✓ | n/a |
| UV | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | n/a |
| Chemicals | – | ✓ | ✓ | ✓ | ✓ | ✓ | n/a |
| Oils | – | ✓ | ✓ | ✓ | ✓ | ✓ | n/a |
| INDOOR | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| OUTDOOR | – | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |

RHINO tapes include specific material depending on the application. They all feature super strong adhesives that stick and last in harsh environments, attached to flat, curved, textured and highly-textured surfaces.

FLEXIBLE NYLON TAPE is specifically designed for wire and cable marking.

PERMANENT POLYESTER TAPE can be used on a variety of flat, textured or highly textured surfaces and has an excellent solvent and chemical resistance.

CLEAR PERMANENT POLYESTER with the sharp printed black characters integrate very nicely the structure and background of the application.

COLOURED VINYL TAPE combines flexibility, a strong adhesive and a high chemical resistance which makes this tape suitable for many type of applications where colour is requested.

HEAT SHRINK TUBING is a non-adhesive yet permanent polyolefin solution to identify and protect your wire and cables at the same time. Flame retardant and 3:1 shrink ratio.

NON-ADHESIVE TAG: ideally to be used as an insert for label holders.

NEW! SELF-LAMINATING VINYL LABELS protect your printed area from exposure (to oil, solvents, water and abrasion) ideal for wire and cable marking.

RHINO™ LABELS

| S-CODE | RHINO PRODUCT | COLOUR | PCK |
|----------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|------------------------|-----------------|
| FLEXIBLE NYLON – Curved or flat surfaces. Wires & cables, patch panels, machinery, equipment, bins, etc (L=3,5m) | | | |
| S0718100 | 12 mm flexible nylon tape | white | 1/5 |
| S0718120 | 19 mm flexible nylon tape | white | 1/5 |
| S0773840 | 24 mm flexible nylon tape | white | 1/5 NEW! |
| S0718080 | 12 mm flexible nylon tape | yellow | 1/5 |
| S0718090 | 19 mm flexible nylon tape | yellow | 1/5 |
| S0773850 | 24 mm flexible nylon tape | yellow | 1/5 NEW! |
| PERMANENT POLYESTER – Flat surfaces. Equipment, bins, patch panels, etc (L=5,5m) | | | |
| S0718240 | 9 mm permanent polyester tape | white | 1/5 |
| S0718210 | 12 mm permanent polyester tape | white | 1/5 |
| S0718220 | 19 mm permanent polyester tape | white | 1/5 |
| S0773830 | 24 mm permanent polyester tape | white | 1/5 NEW! |
| S0718170 | 9 mm permanent polyester tape | metallized | 1/5 |
| S0718180 | 12 mm permanent polyester tape | metallized | 1/5 |
| S0718200 | 19 mm permanent polyester tape | metallized | 1/5 |
| S0718160 | 9 mm clear polyester tape | clear | 1/5 |
| VINYL – All surfaces. Ideal for outdoor and colour-coding applications. Warning messages, wires, patch panels, equipment, machinery, etc (L=5,5m) | | | |
| S0718440 | 9 mm coloured vinyl tape | yellow | 1/5 |
| S0718450 | 12 mm coloured vinyl tape | yellow | 1/5 |
| S0718470 | 19 mm coloured vinyl tape | yellow | 1/5 |
| S0718480 | 9 mm coloured vinyl tape | orange | 1/5 |
| S0718490 | 12 mm coloured vinyl tape | orange | 1/5 |
| S0718500 | 19 mm coloured vinyl tape | orange | 1/5 |
| S0718510 | 9 mm coloured vinyl tape | red | 1/5 |
| S0718520 | 12 mm coloured vinyl tape | red | 1/5 |
| S0718530 | 19 mm coloured vinyl tape | red | 1/5 |
| S0718550 | 9 mm coloured vinyl tape | green | 1/5 |
| S0718560 | 12 mm coloured vinyl tape | green | 1/5 |
| S0718570 | 19 mm coloured vinyl tape | green | 1/5 |
| S0718580 | 9 mm coloured vinyl tape | white | 1/5 |
| S0718600 | 12 mm coloured vinyl tape | white | 1/5 |
| S0718620 | 19 mm coloured vinyl tape | white | 1/5 |
| HEAT SHRINK TUBE – Wire and cable. (L=1,5m) Cable Diameter | | | |
| S0718260 | 6 mm heat shrink tube | Min 1,18 mm Max 2,33mm | white 1/5 |
| S0718280 | 9 mm heat shrink tube | Min 1,73 mm Max 3,73mm | white 1/5 |
| S0718300 | 12 mm heat shrink tube | Min 2,97 mm Max 5,13mm | white 1/5 |
| S0718330 | 19 mm heat shrink tube | Min 4,64 mm Max 8,70mm | white 1/5 |
| S0718270 | 6 mm heat shrink tube | Min 1,18 mm Max 2,33mm | yellow 1/5 |
| S0718290 | 9 mm heat shrink tube | Min 1,73 mm Max 3,73mm | yellow 1/5 |
| S0718310 | 12 mm heat shrink tube | Min 2,97 mm Max 5,13mm | yellow 1/5 |
| S0718340 | 19 mm heat shrink tube | Min 4,64 mm Max 8,70mm | yellow 1/5 |
| NON-ADHESIVE – Insert. Label holders, Patch panels, distribution blocks, faceplates, etc (L=5,5m) | | | |
| S0718350 | 6 mm non-adhesive tag | white | 1/5 |
| S0718360 | 9 mm non-adhesive tag | white | 1/5 |
| S0718380 | 12 mm non-adhesive tag | white | 1/5 |
| S0718390 | 19 mm non-adhesive tag | white | 1/5 |
| S0718400 | 6 mm non-adhesive tag | yellow | 1/5 |
| S0718410 | 9 mm non-adhesive tag | yellow | 1/5 |
| S0718420 | 12 mm non-adhesive tag | yellow | 1/5 |
| S0718430 | 19 mm non-adhesive tag | yellow | 1/5 |
| SELF-LAMINATING VINYL – Wire and cable. Protects vital information (L=5,5m) NEW! | | | |
| S0773860 | 24 mm self-laminating tape | white | 1/5 |