



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


SPC-F005.DWG

REVISIONS			DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1876	Α	RELEASED	EO	07/25/06	SA	07/25/06	но	07/25/06

RoHS
Compliant







Specifications:

1. Shell: Steel, Tin Plated

2. Insulator: PBT +30% Fiber Glass, Black

UL94V-0 Rated

3. Retention Springs: Stainless Steel

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

Unless Otherwise Specified .X ±0.35 [0.014] .XX ±0.15 [0.006]

DRAWN BY:	DATE:
EKLAS ODISH	07/25/0
CHECKED BY:	DATE:
SAMI ALNADI	07/25/0
APPROVED BY:	DATE:
HISHAM ODISH	07/25/0

DRAWING TITLE:

15 Pin High -Density D-Sub Crimp Type Socket

13 Thi Thigh Density D Sub Chilip Type Socker							21	
	SIZE	DWG. NO.		ELECT	FRONIC FIL	_E	REV	
	Α	SPC15367			79K4953.DWG			
	SCALI	E: NTS	U.O.M.: mm [INCHES]		SHEET:	1 OF	- 1	