



Specifications:

1. Shell: Steel, Tin Plated
2. Insulator: PBT +30% Fiber Glass, Black UL94V-0 Rated
3. Retention Springs: Stainless Steel

TOLERANCES: Unless Otherwise Specified		DRAWN BY: SAM ALNADI	DATE: 07/25/06	DRAWING TITLE: 62 Pin High Density D-Sub Crimp Type Plug		ELECTRONIC FILE		REV
.X ±0.35 [0.014]		CHECKED BY:	DATE:	SIZE	DWG. NO.			
.XX ±0.15 [0.006]		APPROVED BY: HISHAM ODISH	DATE: 07/25/06	A	SPC11			
U.O.M.:						SHEET: 1 OF		

DATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.