

Silicone Cover Stranded-Core Wire – 2m 26AWG Black

PRODUCT ID: 1881



DESCRIPTION

Silicone-sheathing wire is super-flexible and soft, and its also strong! Able to handle up to 200°C and up to 600V, it will do when PVC covered wire wimps out. We like this wire for being extremely supple and flexible, so it is great for



wearables or projects where the wire-harness has to be able to deal with a lot of bending.

Comes with 2m of black wire. The wire is 26AWG stranded with an outer diameter of 1.5mm.

TECHNICAL DETAILS

- Length: 2 meters / 78.7"
- Outer Diameter: 1.4mm / 0.06"
- Nominal Voltage: 600V
- Temperature Range: -60°C ~ 200°C
- OD Tolerance: ± 0.1 mm
- Resistance: 123 Ω /Km
- Current Handling Capability: ~3.5 A (depends on length!)