

4 CHANNEL USB CHARGER + 4AA 1300mAh

Product Code: C015
 EAN Code: 5060240212569

Infapower's 4 channel USB charger can be used worldwide. It comes complete with 4AA 1300mAh Ready to Use rechargeable batteries. It will charge 1, 2, 3 or 4 batteries at a time. Micro USB cable included. LEDs show which batteries are being charged

Features include:
 Worldwide use with USB plug (not included)
 Reverse polarity, bad cell and short circuit protection.

Will charge any brand of rechargeable batteries.



Product Description	Charger Name: Included Cells: Cell capacity: Product code: EAN Code:	4 Channel USB Charger 4 x AA 1300mAh Ready to Use Rechargeable Batteries 1300mAh C015 5060240212569
Charger Specifications	Charging Current: Battery Technology: No. Channels: Power Type: AC Input: Charging Indicator:	AA:160mA (1-4pcs) AAA: 60mA (1-4pcs) Ni-Mh Ready to Use 4 1A USB Power Adaptor (not included) 5V DC 0.7A (by Micro-USB/Type-C) Yes. 4 Blue LED indicators
Charging Times	AA 600mAh: AA 1300mAh: AA 2500mAh: AAA 550mAh: AAA 650mAh: AAA 1000mAh:	1-4pcs = 3.5 hours 1-4pcs = 8 hours 1-4pcs = 14 hours 1-4pcs = 9 hours 1-4pcs = 10 hours 1-4pcs = 15 hours
Safety Features	Reverse Polarity Detection: Short Circuit Protection: Bad Cell Detection: Thermal Cut-Off: Negative Delta V:	Yes Yes Yes No No
Logistics Information	Product Weight (g): Box Dimensions (mm): Box Weight (g): Boxes in Inner: Inner Dimensions (mm): Inner Weight (g): Boxes in Outer: Outer Dimensions (mm): Outer Weight (kg): Outer / Layers: Layers / Pallet: Blisters / Pallet: Height of Pallet (mm):	148 120 x 84 x 32 18 6 240 x 105 x 100 1064 36 330 x 265 x 220 7.4 TBA TBA TBA TBA