

Stock no 63539

Socket Set In Full Plus Drawer EVA Insert Tray, 1/4", 3/8" & 1/2" (96 Piece)

Expert Quality, 6pt (1/4") and 12pt (3/8" and 1/2") sockets manufactured from chrome vanadium steel, which is correctly hardened and tempered with a polished chrome plated finish. Each socket has a knurled ring for extra grip. Supplied with 72 tooth reversible soft grip ratchet and accessories. Supplied complete in a two tone full plus drawer EVA insert tray made from closed cell foam. Suitable to be used in Draper and Draper Expert roller cabinets and other manufacturers similar roller cabinets.

NOTE; This tray will only fit into a roller cabinet drawer.

Contents:

- 12 x 1/4" sockets: 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13mm
- 12 x 1/4" deep sockets: 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13mm
- 3 x 1/4" extension bars: 50, 100, 150mm
- 1 x Flexi extension 150mm
- 1 x 1/4" sliding T bar
- 1 x 1/4" coupler
- 1 x 1/4" (F) - 3/8" (M) adaptor
- 1 x Spinner handle
- 10 x 3/8" sockets: 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm
- 10 x 3/8" deep sockets: 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm
- 2 x 3/8" extension bars: 75, 200mm
- 3 x 3/8" spark plug sockets: 10, 12, 14mm
- 1 x 3/8" (F) - 1/4"(M) adaptor
- 1 x 3/8" (F) - 1/2" (M) adaptor
- 1 x 3/8" (F) - 1/2" (M) sliding T - bar adaptor
- 17 x 1/2" sockets: 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 30, 32mm
- 9 x 1/2" deep sockets: 17, 18, 19, 21, 22, 24, 27, 30, 32mm
- 2 x 1/2" Sq. Dr. extension bars: 75, 250mm
- 1 x 1/2" (F) - 3/8" (M) sliding T - bar adaptor (forms a sliding 'T' bar when used with an extension bar)
- 1 x 1/2" (F) - 3/8" (M) adaptor
- 1 x 1/4" sq. dr. 72 tooth reversible ratchets with quick release button
- 1 x 3/8" sq. dr. 72 tooth reversible ratchets with quick release button
- 1 x 1/2" sq. dr. 72 tooth reversible ratchets with quick release button
- 3 x Universal Joints: 1/4, 3/8, 1/2" Sq. Dr.

Dimensions	560 x 390 x 50mm
-------------------	------------------