

Stock no 63540

Socket Set In Full Drawer EVA Insert Tray, 1/4", 3/8", And 1/2" (84 Piece)

Manufactured from chrome vanadium steel, which is correctly hardened and tempered with a satin chrome plated finish. Each socket has a knurled ring for extra grip. Supplied with 72 tooth reversible soft grip ratchet and accessories. Supplied complete in a two tone full drawer EVA insert tray made from closed cell foam. Suitable to be used in Draper and Draper Expert tool chests and other manufacturers similar tool chests.

Contents:

- 12 x 1/4" sq. dr. sockets: 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13mm
- 12 x 1/4" sq. dr. deep sockets: 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13mm
- 1 x 1/4 sq. dr. 72 tooth reversible ratchets with soft grip and quick release button
- 1 x 3/8 sq. dr. 72 tooth reversible ratchets with soft grip and quick release button
- 1 x 1/2" sq. dr. 72 tooth reversible ratchets with soft grip and quick release button
- 1 x Spinner handle
- 3 x Universal joints: 1/4, 3/8, 1/2"
- 10 x 3/8" sq. dr. sockets: 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm
- 10 x 3/8" sq. dr. deep sockets: 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm
- 2 x 1/4" sq. dr. extension bars: 100, 150mm
- 1 x 1/4" sq. dr. sliding T - bar
- 3 x 3/8" sq. dr. spark plug sockets: 10, 12, 14mm
- 2 x 3/8" sq. dr. extension bars: 75, 150mm
- 16 x 1/2" sq. dr. sockets: 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 26, 27, 30, 32mm
- 7 x 1/2" sq. dr. deep sockets: 13, 14, 17, 18, 19, 21, 22mm
- 2 x 1/2" sq. dr. extension bars: 75, 250mm
- 1 x 1/2"(F) - 3/8"(M) sliding T - bar adaptor (forms a sliding 'T' bar when used with an extension bar)

Dimensions	550 x 270 x 46mm
-------------------	------------------