

## Han-Compact-HTE-M25-black



Image is for illustration purposes only. Please refer to product description.

Part number	19 12 008 0411
Specification	Han-Compact-HTE-M25-black
HARTING eCatalogue	<a href="https://b2b.harting.com/19120080411">https://b2b.harting.com/19120080411</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Hood
Description of hood/housing	for Han-Compact® half cable gland With separate PE terminating point for all inserts of size Han-Compact®

### Version

Locking type	Single locking lever
Size	Han-Compact®
Version	Top entry
Cable entry	1x M25
Field of application	Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Chromated
Colour (hood/housing)	RAL 9005 (jet black)



Pushing Performance

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	UL 2237 PVVA2.E318390
	CSA-C22.2 No. 182.3 ECBT8.E235076
	CSA-C22.2 No. 182.3 PVVA8.E318390
CE	Yes

## Commercial data

Packaging size	1
Net weight	205.5 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors