

Han 3A-AK-DICHTUNG SCHWARZ



Part number	09 20 003 5409
Specification	Han 3A-AK-DICHTUNG SCHWARZ
HARTING eCatalogue	https://b2b.harting.com/09200035409

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings Thermoplastic With seal

Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications
Details	for mounted female insert or for mounted Han-Brid [®] insert

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 9005 (jet black)



Material properties

Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

|--|

Commercial data	
Packaging size	10
Net weight	5 g
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors