

Han A Base Angled 1Lever



Part number	09 20 003 0810
Specification	Han A Base Angled 1Lever
HARTING eCatalogue	https://b2b.harting.com/09200030810

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Angled 4 fixing screws

Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection and to IEC 60520	IP44
Degree of protection acc. to IEC 60529	IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Steel
Surface (locking)	Zinc plated



Material properties

RoHS	compliant with exemption
RoHS exemptions	6(a) / $6(a)$ -I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Approvals	DNV GL
CE	Yes

Commercial data

Packaging size	10
Net weight	66.98 g
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors