

Han 3A Housing Angled bulkhead mounting



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 003 0811
Specification	Han 3A Housing Angled bulkhead mounting
HARTING eCatalogue	https://b2b.harting.com/09200030811

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Angled 4 fixing screws Square mounting flange

Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Steel



Pushing Performance

Material properties

Surface (locking)	Zinc plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
CE	Yes

Commercial data

Packaging size	10
Net weight	92 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors