



Pushing Performance

## Acces. Special Cable Clamp EMC M32



Part number	19 62 000 5094
Specification	Acces. Special Cable Clamp EMC M32
HARTING eCatalogue	<a href="https://b2b.harting.com/19620005094">https://b2b.harting.com/19620005094</a>

### Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	EMC version

### Technical characteristics

Wrench size	35
Degree of protection acc. to IEC 60529	IP68
Size	M32
Clamping range	11.5 ... 15.5 mm
Shielding diameter	8 ... 13.5 mm
Width across corners	38.5 mm

### Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance

## Commercial data

Packaging size	10
Net weight	102.41 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)