

# Han-Yellock 30M carrier hood button slot



Part number	11 13 300 0110
Specification	Han-Yellock 30M carrier hood button slot
HARTING eCatalogue	https://b2b.harting.com/11133000110

Image is for illustration purposes only. Please refer to product description.

#### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock <sup>®</sup>
Type of hood/housing	Carrier hood
Description of hood/housing	Push button, slot

#### Version

Locking type	Push button
Size	Han-Yellock <sup>®</sup> 30
Field of application	Hoods/housings for outdoor applications

### Technical characteristics

Limiting temperature	-40 +125 °C
Un-/locking temperature	-10 +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Passivated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Polyamide (PA)
	Stainless steel



## Material properties

Colour (locking)	Melon yellow
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
CE	Yes

## Commercial data

Packaging size	1
Net weight	211.42 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors