

[Home](#) › [Products](#) › [Cooling Fans](#) › [DC Centrifugal Blowers](#) › [05020GA-12M-AA-00](#)[Back To DC Centrifugal Blowers](#)

Have a question about this product?

[Ask Our Experts](#)

DC Centrifugal Blowers - 05020GA-12M-AA-00

We use cookies. We may place these for analysis of our visitor data, to improve our website, show personalized content and to give you a great customer experience. For more information about how we use your personal data and our cookies, please see our privacy policy.

Privacy Policy

[Accept](#)

Get a sample

Specifications

Category	DC Centrifugal Blowers
Part Number	05020GA-12M-AA-00
Legacy Part Number	BM5020-04W-B40-L00
Frame Size [mm]	50
Frame Width [mm]	20
Nominal Voltage [V]	12
Max. Air Flow [CFM]	5.6
Max. Static Pressure [In H2O]	0.73
Speed [min-1]	5600
Noise [dB]	32

We use cookies. We may place these for analysis of our visitor data, to improve our website, show personalized content and to give you a great customer experience. For more information about how we use your personal data and our cookies, please see our privacy policy.

Privacy Policy

Accept

Operating Voltage Upper [V]	13.8
Nominal Current [A]	0.18
Input Power [W]	2.16
Mass [g]	30

Have A Question?

Our precision component experts can help you find the right solutions.

Contact Us Today

Find A Distributor

Find Sales Rep For Fans

PRODUCTS

See All Products

Find A Distributor

Find a Sales Representative

We use cookies. We may place these for analysis of our visitor data, to improve our website, show personalized content and to give you a great customer experience. For more information about how we use your personal data and our cookies, please see our privacy policy.

Privacy Policy

Accept