1825140-2 ✓ ACTIVE

Alcoswitch | Alcoswitch DIP, Alcoswitch DIP MGD LP

TE Internal #: 1825140-2


Alcoswitch DIP, DIP & SIP Switches, Switch, Gold, Black DIP & SIP

Switch Housing Color, Polyphenylene Sulfide (PPS), 4 Switch

View on TE.com >



Relays, Contactors & Switches > Switches > DIP & SIP Switches



DIP & SIP Switch Product Type: Switch

DIP & SIP Switch Contact Mating Area Plating Material: Gold

DIP & SIP Switch Housing Color: Black

DIP & SIP Switch Housing Material: Polyphenylene Sulfide (PPS)

Auto-Insertable: No

Features

Product Type Features

DIP & SIP Switch Product Type	Switch
Sealed DIP & SIP Switch	No
DIP & SIP Switch Type	DIP
Actuator Style	Slide

Configuration Features

Number of Switches	4
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

DIP & SIP Switch Voltage Rating	50 VDC
---------------------------------	--------

Body Features

Seal Type	Tape
Actuator Color	White

Contact Features

	10 μin
Solder Tail Contact Plating	Gold over Nickel
DIP & SIP Switch Contact Mating Area Plating Material	Gold
Auto-Insertable	No
DIP & SIP Switch Contact Current Rating	.1 A



Contact Base Material	Copp	per Alloy

Mechanical Attachment

Housing Features

Low Profile	Yes
DIP & SIP Switch Housing Color	Black
DIP & SIP Switch Housing Material	Polyphenylene Sulfide (PPS)
DIP & SIP Switch Centerline	1.27 mm[.05 in]

Dimensions

Length	6.2 mm[.244 in]
Height	1.7 mm[.067 in]

Usage Conditions

Industry Standards

UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Tape & Reel
Packaging Quantity	2000

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts



Also in the Series | Alcoswitch DIP







Also in the Series | Alcoswitch DIP MGD LP



Customers Also Bought





TE Part #1-2040832-4
EMBOSS TAPING 0.25FPC BF-L-1.3




TE Part #1410270-2 MULTIGIG RT PWR .8" VRT RCP 4P PBFR




TE Part #1-1761465-1
PCI Express RA assy 5.8mm slot 3.1
mm pc



TE Part #1318164-1
BATTERY HOLDER ASSY FOR ML614



TE Part #1410147-2 MULTIGIG RT T2 .8 DC DF CT 7 ROW




TE Part #104346-2 04 MODII HDR SRST B/A W/HD

TE Part #HPP845E034R5
HTU20D RH/T SENSOR IC DIGITAL

TE Part #1-2000713-3 RA Keyed Guide Mod, Vita 46, Machined



TE Part #1410137-2 MULTIGIG RT T2 .8" DC DF F-CTR



TE Part #1410139-2 MULTIGIG RT T2 .8 DC DF F-RGT

Documents

Product Drawings

MGDH04STR04=1/2 PITCH LOW P DIP T&R

English

CAD Files

Customer View Model

ENG_CVM_CVM_1825140-2_O.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1825140-2_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1825140-2_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Environmental Compliance

Alcoswitch DIP, DIP & SIP Switches, Switch, Gold, Black DIP & SIP Switch Housing Color, Polyphenylene Sulfide (PPS), 4 Switch



MD_1825140-2_06282016115_dmtec

English

MD_1825140-2_06282016115_dmtec

English