

AMPLIMITE | AMPLIMITE Kit

TE Internal #: 5205979-1

AMPLIMITE Kit, D-Sub Locking & Mounting, Retainer Screw, Screw

Length .22 in [5.59 mm]

View on TE.com >




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting











D-Shaped Connector Accessories: Retainer Screw

Screw Length: 5.59 mm [.22 in]

Features

Product Type Features

| Product Type | Accessory |
|--------------------------------|-----------------|
| D-Shaped Connector Accessories | Retainer Screw |
| Mechanical Attachment | |
| Screw Finish | Yellow Chromate |
| Screw & Hole Thread Size | 4-40 |
| Screw Length | 5.59 mm[.22 in] |
| Packaging Features | |
| Packaging Quantity | 1 |
| Packaging Method | Box |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
|---|---|
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) |



Candidate List Declared Against: JAN 2021

(211)

SVHC > Threshold:

Pb (.35% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




Also in the Series | AMPLIMITE Kit









Customers Also Bought





TE Part #1-5177986-5 0.8FH,P06H.5,120,08/Sn,TR,SC




TE Part #1571563-9 FSM8JSMATR=TACT,SMT,T&R



TE Part #1532215-1 M83513/01-GN, MCKS-N1-B-51PS





TE Part #1-353081-2 DYNAMIC D-5200 HDR H ASSY 3P



TE Part #1461103-1 OJE-SS-103HM,000




TE Part #DTS26F25-19SN PLUG ASSY





TE Part #1-770970-1 08P MINI UMNL R/A HDR ASSY LF



Documents

Product Drawings

FILLISTER HEAD SCREW,ZN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5205979-1_0_c-5205979-1-0.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5205979-1_0_c-5205979-1-0.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5205979-1_0_c-5205979-1-0.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications

AMPLIMITE Kit, D-Sub Locking & Mounting, Retainer Screw, Screw Length .22 in [5.59 mm]



Product Specification

English