

## Detailed Specifications

<b>Frame Size:</b>	250[mm]
<b>Frame Depth:</b>	99[mm]
<b>Nominal Voltage:</b>	48[V]
<b>Max. Air Flow:</b>	862[CFM]
<b>Max. Static Pressure:</b>	3.1[In H2O]
<b>Speed:</b>	3100[rpm]
<b>Noise:</b>	81[dB]
<b>Life Expectancy:</b>	40 degree C 70,000 Hours[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Operating Voltage - Lower:</b>	36[V]
<b>Operating Voltage - Upper:</b>	72[V]
<b>Nominal Current:</b>	3.4[A]
<b>Input Power:</b>	163.2[W]
<b>Mass:</b>	2400[g]