## Twist-Lock® Devices

# 20A, 3 Phase 250V AC, 3 Pole, 4 Wire Grounding

## **Spring Termination Single Flush Receptacle**

#### **Features**

- Faster termination time
- · No need for screwdriver and torque wrench
- · Spring Termination eliminates strand relaxation
- · High-impact, abuse-resistant nylon face
- · Face color coding by voltage facilitates locating and mating of proper devices

**Ordering Information** 

Description **Device Color** UPC **Catalog Number** Nylon face, back wire 783585788586 HBL2420ST Black

#### Listings

Listed to UL 498 Certified to CSA C22.2 No.42

#### **Specifications**

Nylon
Nylon
Brass
Steel
Brass

#### **Performance**

**Electrical** 

Certified for current interrupting at full rated current **Current Interrupting** 

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Solid/Stranded #14 AWG to #12 AWG Terminal Accommodation

Terminal Identification Terminals identified in accordance with UL 498

**Environmental** 

V2 or better per UL94/CSA 22.2 No.0.17 Flammability

Moisture Resistance IP20 Suitability

**Operating Temperatures** Maximum Continuous 75°C; Minimum -40°C (w/o impact)







### **Accessories**

Plug	HBL2421
Wallplate or Weatherproof Cover	1.60" Opening
Switched Enclosure	SETL3

