


AT4X35 | AT - PROTWIST® screwdrivers for slotted head screws - short blades





Standards:

NF ISO 2380-1, NF ISO 2380-2, ISO 2380-1, ISO 2380-2, DIN ISO 2380-1, DIN ISO 2380-2, ASME B107.600

Description:

- Short round blade and ball handle for use in confined spaces.
- Inline Hardening Process +50% Tip Life and +100% Bar Strength.
- Handle Material Softer for more Comfort and still Chemical Resistant.
- Blade " tri-coating " treatment (Zinc-Nickel-Chromium) 4x Corrosion Resistance.
- Handle 'Channel' +10% Torque.
- Laser Marking gives virtually Permanent Marking.
- CNC tip machining gives better Screw Fit increasing Torque Transfer and Reducing Wear.



=0	AT4X35
A [mm]	4.0
Diameter [mm]	36.0
Diameter D1 [mm]	4.0
Length L1 [mm]	35.0
Length L [mm]	91.0
Length L2 [mm]	56.0
Thickness E [mm]	0.8
Width [mm]	4.0
Weight [g]	36.0