


## AT5.5X100 | AT - PROTWIST® screwdrivers for slotted head screws - milled blades





## Standards:

NF ISO 2380-1, NF ISO 2380-2, ISO 2380-1, ISO 2380-2, DIN ISO 2380-1, DIN ISO 2380-2, ASME B107.600

## **Description:**

- Round shank for access in holes.
- Extra-long shank up to 300 mm for difficult and remote access.
- Inline Hardening Process +100%
  Tip Life and +100% Bar Strength.
- Handle Material Softer for more Comfort and still Chemical Resistant.
- Blade "tri-coating "treatment (Zinc-Nickel-Chromium) 4x Corrosion Resistance.
- Handle 'Channel' +10% Torque.
- Laser Marking gives virtually Permanent Marking.
- CNC tip machining gives better Screw Fit increasing Torque Transfer and Reducing Wear.



=0	AT5.5X100
A [mm]	5.5
Diameter [mm]	30.0
Diameter D1 [mm]	3.5
Length L1 [mm]	100.0
Length L [mm]	209.0
Length L2 [mm]	109.0
Thickness E [mm]	1.0
Width [mm]	5.5
Weight [g]	82.0