


ATWH12X200 | ATWH - PROTWIST® screwdrivers for slotted head screws - POWER series





Standards:

NF ISO 2380-1, NF ISO 2380-2, ISO 2380-1, ISO 2380-2, DIN ISO 2380-1, DIN ISO 2380-2, ASME B107.600

Description:

- Hexagonal blade with shoulder to take a wrench.
- Extra-long shank up to 250 mm for difficult and remote access.
- Inline Hardening Process +50% Tip Life and +100% Bar Strength.
- Handle Material Softer for more Comfort and still Chemical Resistant.
- Blade "tri-coating "treatment (Zinc-Nickel-Chromium) 4x Corrosion Resistance.
- Handle 'Channel' +10% Torque.
- Laser Marking gives virtually Permanent Marking.
- CNC tip machining gives better Screw Fit increasing Torque Transfer and Reducing Wear.



=0	ATWH12X200
A [mm]	12.0
Diameter [mm]	40.0
Diameter D1 [mm]	10.0
Length L1 [mm]	200.0
Length L [mm]	325.0
Length L2 [mm]	125.0
Thickness E [mm]	2.0
Width [mm]	12.0
Weight [g]	350.0