


ATWH12X200CK | ATWH.CK - PROTWIST® SHOCK screwdrivers for slotted head screws





Standards:

NF ISO 2380-1, NF ISO 2380-2, ISO 2380-1, ISO 2380-2, DIN ISO 2380-1, DIN ISO 2380-2, ASME B107.600

Description:

- Impact Zone with Steel Strike hexagonal blade with 73MO steel.
- Hexagonal blade with shoulder to take a wrench.
- Extra-long blade for use in confined spaces.
- Inline Hardening Process +100%
 Tip Life and +100% Bar Strength.
- Handle Material Softer for more Comfort and still Chemical Resistant.
- Golden electroplated Tip 4x Corrosion Resistance.
- Handle 'Channel' +10% Torque.
- Laser Marking gives virtually Permanent Marking.
- CNC tip machining gives better Screw Fit increasing Torque Transfer and Reducing Wear.



=0	ATWH12X200CK
Diameter [mm]	40.0
Diameter D1 [mm]	1.0
Length L1 [mm]	200.0
Length L [mm]	325.0
Length L2 [mm]	125.0
Weight [g]	292.0