
ATWH5.5X125 | ATWH - PROTWIST® screwdrivers for slotted head screws - POWER series





Standards:

NF ISO 2380-1, NF ISO 2380-2, ISO 2380-1, ISO 2380-2, DIN ISO 2380-1, DIN ISO 2380-2, ASME B107.600

Description:

• Hexagonal blade with shoulder to take a wrench.

• Extra-long shank up to 250 mm for difficult and remote access.

• Inline Hardening Process – +50% Tip Life and +100% Bar Strength.

• Handle Material - Softer for more Comfort and still Chemical Resistant.

• Blade " tri-coating " treatment (Zinc-Nickel-Chromium) - 4x Corrosion Resistance.

- Handle 'Channel' +10% Torque.
- Laser Marking gives virtually Permanent Marking.

• CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.

	ATWH5.5X125
A [mm]	5.5
Diameter [mm]	30.0
Diameter D1 [mm]	5.0
Length L1 [mm]	125.0
Length L [mm]	234.0
Length L2 [mm]	109.0
Thickness E [mm]	1.0
Width [mm]	5.5
Weight [g]	90.0