
ATWH8X175 | AW - PROTWIST® screwdrivers for slotted head screws - hexagonal blades



Standards:

NF ISO 2380-1, NF ISO 2380-2, ISO 2380-1, ISO 2380-2, DIN ISO 2380-1, DIN ISO 2380-2, ASME B107.600

Description:


• Hexagonal blade for optimum reliability and performance.

• Extra-long shank up to 250 mm for difficult and remote access.

• Silicon carbon blade: strong and resistant to flexion.

• Bi-material grip resists to impacts, abrasion, and chemicals.

• Finish: black tipped mat chromed blade.



	ATWH8X175
A [mm]	8.0
Diameter [mm]	40.0
Diameter D1 [mm]	7.0
Length L1 [mm]	175.0
Length L [mm]	300.0
Length L2 [mm]	125.0
Thickness E [mm]	1.2
Width [mm]	8.0
Weight [g]	160.0